

## Data sheet

## 6EP4295-8HB00-0XY0



SITOP BUF8600/10S/40A

SITOP BUF8600 10s buffer module for PSU8600 buffer capacity 10 s/40 A with dual-layer capacitors maintenance-free

Technical Product Detail Page		<a href="https://i.siemens.com/1P6EP4295-8HB00-0XY0">https://i.siemens.com/1P6EP4295-8HB00-0XY0</a>
<b>memory</b>		
type of energy storage	Double-layer capacitors	
design of the mains power cut bridging-connection	Backup time with 40 A load current: 10 s	
buffering time for rated value of the output current in the event of power failure	10 000 ms	
load time typical	10 min; at 400 V	
<b>output</b>		
output current		
• rated value	40 A	
<b>protection and monitoring</b>		
display version	3-color LED for operating state module	
• for normal operation	LED green for "buffer standby exist"	
• in buffering mode	LED yellow for "buffered mode"	
<b>interfaces</b>		
product function communication function	Yes	
design of the interface	Ethernet/PROFINET via power supply unit PSU8600	
<b>safety</b>		
operating resource protection class	Class III	
protection class IP	IP20	
standard		
• for emitted interference	EN 55022 Class B	
• for interference immunity	EN 61000-6-2	
<b>standards, specifications, approvals</b>		
certificate of suitability		
• CE marking	Yes	
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259	
• EAC approval	Yes	
• SEMI F47	Yes	
type of certification CB-certificate	Yes	
MTBF at 40 °C	1 190 747 h	
<b>standards, specifications, approvals hazardous environments</b>		
certificate of suitability		
• ATEX	No	
<b>standards, specifications, approvals marine classification</b>		
shipbuilding approval	Yes	
Marine classification association		
• American Bureau of Shipping Europe Ltd. (ABS)	Yes	
• Det Norske Veritas (DNV)	Yes	

standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	<ul style="list-style-type: none"> <li>total 150.7 kg</li> <li>during manufacturing 30.9 kg</li> <li>during operation 118.4 kg</li> <li>after end of life 0.58 kg</li> </ul>
<b>ambient conditions</b>	
ambient temperature	<ul style="list-style-type: none"> <li>during operation -25 ... +60 °C; with natural convection</li> <li>during transport -40 ... +70 °C</li> <li>during storage -40 ... +70 °C</li> </ul>
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
<b>connection method</b>	
type of electrical connection	Plug-in terminal with screw connectors
• for control circuit and status message	X1, X2 (control contact) and 13,14, 23, 24 (message signals): 1 screw terminal each for 0.2 ... 1.5 mm <sup>2</sup>
suitability for interaction modular system	Yes
type of connection to system components	Via integrated connector
<b>mechanical data</b>	
width x height x depth of the enclosure	125 x 125 x 150 mm
installation width x mounting height	125 mm x 225 mm
required spacing	<ul style="list-style-type: none"> <li>top 50 mm</li> <li>bottom 50 mm</li> <li>left 0 mm</li> <li>right 0 mm</li> </ul>
fastening method	<ul style="list-style-type: none"> <li>DIN-rail mounting Snaps onto DIN rail EN 60715 35x15</li> <li>S7 rail mounting Yes</li> <li>wall mounting No</li> </ul>
housing can be lined up	Yes
net weight	1.95 kg
<b>accessories</b>	
mechanical accessories	Device identification label 20 mm x 7 mm, TI-grey 3RT2900-1SB20
<b>further information internet links</b>	
internet link	<ul style="list-style-type: none"> <li>to website: Industry Mall <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a></li> <li>to web page: selection aid TIA Selection Tool <a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a></li> <li>to web page: power supplies <a href="https://siemens.com/sitop">https://siemens.com/sitop</a></li> <li>to website: CAx-Download-Manager <a href="https://siemens.com/cax">https://siemens.com/cax</a></li> <li>to website: Industry Online Support <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a></li> </ul>
<b>additional information</b>	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
<b>security information</b>	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit <a href="http://www.siemens.com/cybersecurity-industry">www.siemens.com/cybersecurity-industry</a>. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates,</p>

## Classifications

	Version	Classification
eClass	14	27-04-07-05
eClass	12	27-04-07-05
eClass	9.1	27-04-07-05
eClass	9	27-04-07-05
eClass	8	27-04-06-90
eClass	7.1	27-04-06-90
eClass	6	27-04-06-90
ETIM	10	EC000382
ETIM	9	EC000382
ETIM	8	EC000382
ETIM	7	EC000382
IDEA	4	4149
UNSPSC	15	39-12-10-11

## Approvals Certificates

### General Product Approval

[Manufacturer Declaration](#)[Declaration of Conformity](#)[China RoHS](#)

CB

[General Product Approval](#)[Maritime application](#)[Environment](#)

last modified:

12/4/2025