


Siemens  
EcoTech



Mushroom pushbutton, 22 mm, round, metal, shiny, red, 40 mm, latching, pull-to-unlatch mechanism, with holder, 1 NO+1 NC, Spring-type terminal

|                                                 |                                    |
|-------------------------------------------------|------------------------------------|
| product brand name                              | SIRIUS ACT                         |
| product designation                             | Mushroom pushbuttons               |
| design of the product                           | Complete unit                      |
| product type designation                        | 3SU1                               |
| product line                                    | Metal, shiny, 22 mm                |
| manufacturer's article number                   |                                    |
| • of supplied contact module at position 1      | <a href="#">3SU1400-1AA10-3FA0</a> |
| • of the supplied holder                        | <a href="#">3SU1550-0AA10-0AA0</a> |
| • of the supplied actuator                      | <a href="#">3SU1050-1BA20-0AA0</a> |
| <b>Enclosure</b>                                |                                    |
| number of command points                        | 1                                  |
| <b>Actuator</b>                                 |                                    |
| principle of operation of the actuating element | latching                           |
| product extension optional light source         | No                                 |
| color of the actuating element                  | red                                |
| material of the actuating element               | plastic                            |
| shape of the actuating element                  | round                              |
| outer diameter of the actuating element         | 40 mm                              |
| number of contact modules                       | 1                                  |
| type of unlocking device                        | pull-to-unlatch mechanism          |
| number of switching positions                   | 2                                  |
| <b>Front ring</b>                               |                                    |
| product component front ring                    | Yes                                |
| design of the front ring                        | Standard                           |
| material of the front ring                      | Metal, high gloss                  |
| color of the front ring                         | silver                             |
| <b>Holder</b>                                   |                                    |
| material of the holder                          | Plastic                            |
| <b>Display</b>                                  |                                    |
| number of LEDs                                  | 0                                  |
| <b>General technical data</b>                   |                                    |
| product function                                |                                    |
| • positive opening                              | Yes                                |
| • EMERGENCY OFF function                        | No                                 |
| • EMERGENCY STOP function                       | No                                 |
| product component light source                  | No                                 |

|                                                                |                                                                                                                                               |
|----------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>insulation voltage rated value</b>                          | 500 V                                                                                                                                         |
| <b>degree of pollution</b>                                     | 3                                                                                                                                             |
| type of voltage of the operating voltage                       | AC/DC                                                                                                                                         |
| <b>surge voltage resistance rated value</b>                    | 6 kV                                                                                                                                          |
| <b>protection class IP</b>                                     | IP66, IP67, IP69(IP69K)                                                                                                                       |
| protection class IP of the terminal                            | IP20                                                                                                                                          |
| <b>degree of protection NEMA rating</b>                        | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                                                                    |
| <b>shock resistance</b>                                        |                                                                                                                                               |
| • according to IEC 60068-2-27                                  | sinusoidal half-wave 15 g / 11 ms                                                                                                             |
| <b>vibration resistance</b>                                    |                                                                                                                                               |
| • according to IEC 60068-2-6                                   | 10 ... 500 Hz: 5 g                                                                                                                            |
| <b>operating frequency maximum</b>                             | 1 800 1/h                                                                                                                                     |
| <b>mechanical service life (operating cycles) typical</b>      | 500 000                                                                                                                                       |
| electrical endurance (operating cycles) typical                | 10 000 000                                                                                                                                    |
| <b>thermal current</b>                                         | 10 A                                                                                                                                          |
| <b>reference code according to IEC 81346-2</b>                 | P                                                                                                                                             |
| <b>continuous current of the C characteristic MCB</b>          | 10 A; for a short-circuit current smaller than 400 A                                                                                          |
| <b>continuous current of the quick DIAZED fuse link</b>        | 10 A                                                                                                                                          |
| <b>continuous current of the DIAZED fuse link gG</b>           | 10 A                                                                                                                                          |
| <b>Substance Prohibittance (Date)</b>                          | 10/01/2014                                                                                                                                    |
| <b>Net Weight</b>                                              | 100 g                                                                                                                                         |
| <b>operating voltage</b>                                       |                                                                                                                                               |
| • at AC                                                        |                                                                                                                                               |
| — at 50 Hz rated value                                         | 5 ... 500 V                                                                                                                                   |
| — at 60 Hz rated value                                         | 5 ... 500 V                                                                                                                                   |
| • at DC rated value                                            | 5 ... 500 V                                                                                                                                   |
| <b>Power Electronics</b>                                       |                                                                                                                                               |
| <b>contact reliability</b>                                     | One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)                                                    |
| <b>Auxiliary circuit</b>                                       |                                                                                                                                               |
| <b>design of the contact of auxiliary contacts</b>             | Silver alloy                                                                                                                                  |
| <b>number of NC contacts for auxiliary contacts</b>            | 1                                                                                                                                             |
| <b>number of NO contacts for auxiliary contacts</b>            | 1                                                                                                                                             |
| <b>Connections/ Terminals</b>                                  |                                                                                                                                               |
| type of electrical connection of modules and accessories       | Spring-type terminal                                                                                                                          |
| <b>type of connectable conductor cross-sections</b>            |                                                                                                                                               |
| • solid without core end processing                            | 2x (0.25 ... 1.5 mm <sup>2</sup> )                                                                                                            |
| • finely stranded with core end processing                     | 2x (0.25 ... 0.75 mm <sup>2</sup> )                                                                                                           |
| • finely stranded without core end processing                  | 2x (0.25 ... 1.5 mm <sup>2</sup> )                                                                                                            |
| • for AWG cables                                               | 2x (24 ... 16)                                                                                                                                |
| <b>tightening torque of the screws in the bracket</b>          | 1 ... 1.2 N·m                                                                                                                                 |
| <b>Ambient conditions</b>                                      |                                                                                                                                               |
| <b>ambient temperature</b>                                     |                                                                                                                                               |
| • during operation                                             | -25 ... +70 °C                                                                                                                                |
| • during storage                                               | -40 ... +80 °C                                                                                                                                |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted for all devices behind front panel) |
| <b>Installation/ mounting/ dimensions</b>                      |                                                                                                                                               |
| <b>fastening method</b>                                        |                                                                                                                                               |
| • of modules and accessories                                   | Front plate mounting                                                                                                                          |
| <b>height</b>                                                  | 40 mm                                                                                                                                         |
| <b>width</b>                                                   | 40 mm                                                                                                                                         |
| <b>shape of the installation opening</b>                       | round                                                                                                                                         |
| <b>mounting diameter</b>                                       | 22.3 mm                                                                                                                                       |
| <b>positive tolerance of installation diameter</b>             | 0.4 mm                                                                                                                                        |
| <b>mounting height</b>                                         | 27.5 mm                                                                                                                                       |
| <b>installation width</b>                                      | 40 mm                                                                                                                                         |
| <b>installation depth</b>                                      | 71.7 mm                                                                                                                                       |
| <b>Approvals Certificates</b>                                  |                                                                                                                                               |

## Environmental Product Declaration

- global warming potential [CO<sub>2</sub> eq] / during manufacturing 0.625 kg
- global warming potential [CO<sub>2</sub> eq] / during operation 0.235 kg
- global warming potential [CO<sub>2</sub> eq] / after end of life -0.267 kg
- global warming potential [CO<sub>2</sub> eq] / total 0.593 kg

## Environment

## General Product Approval

[Environmental Confirmations](#)



## General Product Approval

## Test Certificates

## Maritime application



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



## Maritime application

## other



[Confirmation](#)

[Confirmation](#)



## Further information

### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1150-1BA20-3FA0>

### Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1150-1BA20-3FA0>


### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1150-1BA20-3FA0>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1150-1BA20-3FA0&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1150-1BA20-3FA0&lang=en)





last modified:

4/4/2026 