



SIMATIC ET 200SP, Relay module, RQ NO 4x 120V DC..230VAC/5A ST. 4 normally open contacts, isolated contacts, packing unit: 10 pieces, fits to BU-type B0 and B1, Colour Code CC40, substitute value output, module diagnostics for: supply voltage

General information	
Product type designation	RQ 4x120 VDC ... 230 VAC/5 A NO ST
HW functional status	From FS02
Firmware version	V0.0
• FW update possible	No
usable BaseUnits	BU type B0, B1
Color code for module-specific color-coded label	CC40
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14
• STEP 7 configurable/integrated from version	V5.5 SP3
• PCS 7 configurable/integrated from version	V8.1 SP1
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Redundancy	
• Redundancy capability	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	55 mA; without load
Output voltage	
Rated value (AC)	230 V
Power loss	
Power loss, typ.	1.5 W
Address area	

Address space per module	
• Inputs	+ 1 byte for QI information
• Outputs	1 byte
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	type C
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type B1
• 3-wire connection	BU type B0
Digital outputs	
Type of digital output	Relays
Number of digital outputs	4
Current-sinking	Yes
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	No
Parallel switching of two outputs	
• for logic links	Yes
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	2 Hz
• with inductive load, max.	0.5 Hz
• on lamp load, max.	2 Hz
Total current of the outputs	
• Current per channel, max.	5 A
• Current per module, max.	20 A
Total current of the outputs (per module)	
horizontal installation	
— up to 50 °C, max.	20 A
— up to 60 °C, max.	16 A
vertical installation	
— up to 40 °C, max.	20 A
— up to 50 °C, max.	16 A
Relay outputs	
• Number of relay outputs	4
• Rated supply voltage of relay coil L+ (DC)	24 V
• Current consumption of relays (coil current of all relays), max.	40 mA
• external protection for relay outputs	Yes, with 6A
• Number of operating cycles, max.	7 000 000; see additional description in the manual
Switching capacity of contacts	
— with inductive load, max.	2 A; see additional description in the manual
— with resistive load, max.	5 A; see additional description in the manual
— Thermal continuous current, max.	5 A; Max. 1 385 VA, 150 W
— Switching current, min.	100 mA; 5 V DC
— Rated switching voltage (DC)	24 V DC to 120 V DC
— Rated switching voltage (AC)	24V AC to 230V AC
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	200 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes

• Wire-break	No	
• Short-circuit	No	
Diagnostics indication LED		
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED	
• Channel status display	Yes; green LED	
• for channel diagnostics	No	
• for module diagnostics	Yes; green/red DIAG LED	
Potential separation		
Potential separation channels		
• between the channels	Yes	
• between the channels and backplane bus	Yes	
• between the channels and the power supply of the electronics	Yes	
Permissible potential difference		
between channels and backplane bus/supply voltage	240 V AC	
Isolation		
Isolation tested with	2 500 V DC (type test)	
tested with		
• between channels and backplane bus/supply voltage	2 500 V DC	
• between backplane bus and supply voltage	707 V DC (type test)	
Standards, approvals, certificates		
Suitable for safety functions	No	
Ecological footprint		
• environmental product declaration	Yes	
Global warming potential		
— global warming potential, (total) [CO ₂ eq]	25.5 kg	
— global warming potential, (during production) [CO ₂ eq]	3.54 kg	
— global warming potential, (during operation) [CO ₂ eq]	22.1 kg	
— global warming potential, (after end of life cycle) [CO ₂ eq]	-0.137 kg	
Ambient conditions		
Ambient temperature during operation		
• horizontal installation, min.	-30 °C	
• horizontal installation, max.	60 °C	
• vertical installation, min.	-30 °C	
• vertical installation, max.	50 °C	
Altitude during operation relating to sea level		
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m	
Dimensions		
Width	20 mm	
Height	73 mm	
Depth	58 mm	
Weights		
Weight, approx.	40 g	
Classifications		
	Version	Classification
	eClass	14
	eClass	12
	eClass	9.1
	eClass	9
	eClass	8
	eClass	7.1
	eClass	6
	ETIM	10
	ETIM	9
	ETIM	8

ETIM	7	EC001599
IDEA	4	3566
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Miscellaneous](#)



[Manufacturer Declaration](#)

[China RoHS](#)



[Maritime application](#)

[Environment](#)



Siemens
EcoTech



last modified:

10/23/2025