



SIMATIC ET 200SP, analog input module, AI Energy Meter CT HF, for 1A or 5A current transformer, with network analysis functions, suitable for BU type U0, channel diagnostics

| General information                                      |   |
|--|---|
| Product type designation                                 | AI Energy Meter CT HF   |
| Firmware version   | V8.0  |
| • FW update possible                                     | Yes   |
| usable BaseUnits   | BU type U0  |
| Color code for module-specific color-coded label         | CC20  |
| Supported power supply systems                           | TT, TN, IT  |
| Product function   |   |
| • Voltage measurement                                    | Yes   |
| — without voltage transformer                            | Yes   |
| — with voltage transformer                               | Yes   |
| • Current measurement                                    | Yes; Max. 4   |
| — without current transformer                            | No  |
| — with current transformer                               | Yes; 1 A or 5 A current transformer   |
| — With Rogowski coil                                     | No  |
| — With current-voltage-converter                         | No  |
| • Energy measurement                                     | Yes   |
| • Frequency measurement                                  | Yes   |
| • Power measurement                                      | Yes   |
| • Active power measurement                               | Yes   |
| • Reactive power measurement                             | Yes   |
| • Power factor measurement                               | Yes   |
| • Active factor measurement                              | Yes   |
| • Reactive power compensation                            | Yes   |
| • Line analysis  | Yes   |
| — Monitoring of instantaneous and half-wave values       | Yes   |
| — THD measurement for current and voltage                | Yes   |
| — Harmonics for current and voltage                      | Yes   |
| — Voltage dip (DIP)                                      | Yes   |
| — Voltage swell  | Yes   |
| • I&M data   | Yes; I&M0 to I&M3   |
| • Isochronous mode                                       | No  |
| Engineering with   |   |
| • STEP 7 TIA Portal configurable/integrated from version | STEP 7 V16 or higher with HSP   |
| • STEP 7 configurable/integrated from version            | V5.5 SP3 or higher  |
| • PROFIBUS from GSD version/GSD revision                 | One GSD file each, Revision 3 and 5 and higher                                  |
| • PROFINET from GSD version/GSD revision                 | V2.3  |
| Operating mode   |   |
| • Switching between operating modes in RUN               | Yes; For module version 32 I/20 Q, it is possible to dynamically switch between |

|  |   |
|--|---|
| • Cyclic measured value access                   | 25 user data variants, 23 of which are pre-defined and 2 of which can be defined by the specific user |
| • Acyclic measured value access                  | Yes   |
| • Fixed measured value sets                      | Yes   |
| • Freely definable measured value sets           | Yes; For cyclic and acyclic measured value access   |
| <b>CiR - Configuration in RUN</b>                |   |
| Reparameterization possible in RUN               | Yes   |
| Calibration possible in RUN                      | Yes   |
| <b>Installation type/mounting</b>                |   |
| Mounting position                                | any   |
| <b>Supply voltage</b>                            |   |
| Rated value (DC)                                 | 24 V  |
| permissible range, lower limit (DC)              | 19.2 V  |
| permissible range, upper limit (DC)              | 28.8 V  |
| <b>Input current</b>                             |   |
| Current consumption (rated value)                | 12.5 mA   |
| Current consumption, max.                        | 17 mA   |
| <b>Power loss</b>                                |   |
| Power loss, typ.                                 | 1.4 W; 4x 6 A input current, 3x 230 V AC  |
| <b>Address area</b>                              |   |
| Address space per module                         |   |
| • Inputs   | 256 byte  |
| • Outputs  | 20 byte   |
| <b>Hardware configuration</b>                    |   |
| Automatic encoding                               | Yes   |
| • Mechanical coding element                      | Yes   |
| • Type of mechanical coding element              | type C  |
| Selection of BaseUnit for connection variants    |   |
| • 2-wire connection                              | BU type U0  |
| <b>Time of day</b>                               |   |
| Operating hours counter                          |   |
| • present  | Yes   |
| <b>Analog inputs</b>                             |   |
| Cycle time (all channels), typ.                  | 50 ms; Time for consistent update of all measured and calculated values (cyclic und acyclic data)     |
| <b>Cable length</b>                              |   |
| • shielded, max.                                 | 200 m   |
| • unshielded, max.                               | 200 m   |
| <b>Analog value generation for the inputs</b>    |   |
| Sampling frequency, max.                         | 2 048 kHz   |
| <b>Interrupts/diagnostics/status information</b> |   |
| Alarms   |   |
| • Diagnostic alarm                               | Yes   |
| • Limit value alarm                              | Yes   |
| • Hardware interrupt                             | Yes; Monitoring of up to 16 freely selectable process values (exceeding or undershooting of value)    |
| <b>Diagnoses</b>                                 |   |
| • Line quality                                   | Yes   |
| • Supply voltage                                 | Yes   |
| • Hardware interrupt lost                        | Yes   |
| • Parameter assignment error                     | Yes   |
| • Module fault                                   | Yes   |
| • Channel not available                          | Yes   |
| • Overflow/underflow                             | Yes   |
| • Overload current                               | Yes   |
| <b>Diagnostics indication LED</b>                |   |
| • Monitoring of the supply voltage (PWR-LED)     | Yes   |
| • Channel status display                         | Yes; green LED  |

|   |  |
|---|--|
| • for channel diagnostics   | Yes; red Fn LED  |
| • for module diagnostics  | Yes; green/red DIAG LED                                      |
| <b>Integrated Functions</b>   |  |
| Measuring functions   |  |
| • Measuring procedure for voltage measurement                                     | TRMS   |
| • Measuring procedure for current measurement                                     | TRMS   |
| • Type of measured value acquisition  | seamless   |
| • Curve shape of voltage  | Sinusoidal or distorted                                      |
| • Buffering of measured variables   | Yes  |
| • Parameter length  | 128 byte   |
| • Bandwidth of measured value acquisition   | 3.2 kHz; Harmonics: 63 / 50 Hz, 52 / 60 Hz                   |
| Measuring range   |  |
| — Frequency measurement, min.   | 40 Hz  |
| — Frequency measurement, max.   | 70 Hz  |
| Measuring inputs for voltage  |  |
| — Measurable line voltage between phase and neutral conductor                     | 277 V  |
| — Measurable line voltage between the line conductors                             | 480 V  |
| — Measurable line voltage between phase and neutral conductor, min.               | 3 V  |
| — Measurable line voltage between phase and neutral conductor, max.               | 300 V  |
| — Measurable line voltage between the line conductors, min.                       | 6 V  |
| — Measurable line voltage between the line conductors, max.                       | 519 V  |
| — Internal resistance line conductor and neutral conductor                        | 1.5 MΩ   |
| — Power consumption per phase   | 60 mW; 300 V AC  |
| — Impulse voltage resistance 1,2/50μs   | 2.5 kV   |
| — Measurement category for voltage measurement in accordance with IEC 61010-2-030 | CAT II   |
| Measuring inputs for current  |  |
| — measurable relative current (AC), min.  | 1 %; Relative to measuring range; 1 A, 5 A                   |
| — measurable relative current (AC), max.  | 120 %; Relative to the secondary rated current 5 A           |
| — Continuous current with AC, maximum permissible                                 | 5 A; 6 A permanent thermal overload                          |
| — Apparent power consumption per phase for measuring range 5 A                    | 0.6 VA   |
| — Rated value short-time withstand current restricted to 1 s                      | 100 A  |
| — Input resistance measuring range 0 to 5 A                                       | 25 mΩ; At the terminal                                       |
| — Surge strength  | 10 A; for 1 minute   |
| — Zero point suppression  | 0 ... 20%, referred to the nominal current                   |
| Accuracy class according to IEC 61557-12  |  |
| — Measured variable voltage   | 0,2  |
| — Measured variable current   | 0,2  |
| — Measured variable apparent power  | 0,5  |
| — Measured variable active power  | 0,5  |
| — Measured variable reactive power  | 1  |
| — Measured variable power factor  | 0,5  |
| — Measured variable active energy   | 0,5  |
| — Measured variable reactive energy   | 1  |
| — Measured variable neutral current   | 0,2  |
| — Measured variable phase angle   | ±0,5 °; not covered by IEC 61557-12                          |
| — Measured variable frequency   | 0,05; only valid for the permissible voltage measuring range |
| — Measured variable harmonic  | 1  |
| — Measured variable THDU  | 1  |
| — Measured variable THDI  | 1  |
| Accuracy class line analysis acc. to IEC 61000-4-30                               |  |
| — Measured variable voltage   | Class S  |
| — Measured variable current   | Class S  |

| — Measured variable frequency  | Class S  |                |             |
|--|--|----------------|-------------|
| — Measured variable voltage interruption                                   | Class S  |                |             |
| — Measured variable voltage dip and swell                                  | Class S  |                |             |
| — Measured variable harmonic voltage                                       | Class S  |                |             |
| — Measured variable harmonic current                                       | Class S  |                |             |
| <b>Potential separation</b>  |  |                |             |
| Potential separation channels  |  |                |             |
| • between the channels   | No   |                |             |
| • between the channels and backplane bus                                   | Yes  |                |             |
| • Between the channels and load voltage L+                                 | Yes; Including FEE   |                |             |
| <b>Isolation</b>   |  |                |             |
| Isolation tested with  | Between channels and backplane bus, 24 V supply: Routine test, 1 920 V AC, 2 s; between backplane bus and 24 V supply: Type test, 707 V DC |                |             |
| <b>Standards, approvals, certificates</b>                                  |  |                |             |
| Ecological footprint   |  |                |             |
| • environmental product declaration  | Yes  |                |             |
| Global warming potential   |  |                |             |
| — global warming potential, (total) [CO <sub>2</sub> eq]                   | 9.32 kg  |                |             |
| — global warming potential, (during production) [CO <sub>2</sub> eq]       | 4.97 kg  |                |             |
| — global warming potential, (during operation) [CO <sub>2</sub> eq]        | 4.79 kg  |                |             |
| — global warming potential, (after end of life cycle) [CO <sub>2</sub> eq] | -0.449 kg  |                |             |
| <b>Ambient conditions</b>  |  |                |             |
| Ambient temperature during operation                                       |  |                |             |
| • horizontal installation, min.  | -30 °C   |                |             |
| • horizontal installation, max.  | 60 °C  |                |             |
| • vertical installation, min.  | -30 °C   |                |             |
| • vertical installation, max.  | 50 °C  |                |             |
| Altitude during operation relating to sea level                            |  |                |             |
| • Installation altitude above sea level, max.                              | 3 000 m; Restrictions for installation altitudes > 2 000 m, see manual   |                |             |
| <b>Dimensions</b>  |  |                |             |
| Width  | 20 mm  |                |             |
| Height   | 73 mm  |                |             |
| Depth  | 58 mm  |                |             |
| <b>Weights</b>   |  |                |             |
| Weight, approx.  | 45 g   |                |             |
| <b>Other</b>   |  |                |             |
| Data for selecting a voltage transformer                                   |  |                |             |
| • Secondary side, max.   | 300 V  |                |             |
| Data for selecting a current transformer                                   |  |                |             |
| • Burden power current transformer x/1A, min.                              | As a function of cable length and cross section, see device manual   |                |             |
| • Burden power current transformer x/5A, min.                              | As a function of cable length and cross section, see device manual   |                |             |
| <b>Classifications</b>   |  |                |             |
|  | Version  | Classification |             |
|  | eClass   | 14             | 27-24-26-01 |
|  | eClass   | 12             | 27-24-26-01 |
|  | eClass   | 9.1            | 27-24-26-01 |
|  | eClass   | 9              | 27-24-26-01 |
|  | eClass   | 8              | 27-24-26-01 |
|  | eClass   | 7.1            | 27-24-26-01 |
|  | eClass   | 6              | 27-24-26-01 |
|  | ETIM   | 10             | EC001596    |
|  | ETIM   | 9              | EC001596    |
|  | ETIM   | 8              | EC001596    |
|  | ETIM   | 7              | EC001596    |

|        |    |             |
|--------|----|-------------|
| IDEA   | 4  | 3562        |
| UNSPSC | 15 | 32-15-17-05 |

### Approvals / Certificates

General Product Approval

EMV



|                   |                   |                      |       |                 |
|-------------------|-------------------|----------------------|-------|-----------------|
| Functional Safety | Test Certificates | Maritime application | other | Dangerous goods |
|-------------------|-------------------|----------------------|-------|-----------------|



[Type Test Certificates/Test Report](#)



Confirmation



[Transport Information](#)

### Environment

[Environmental Confirmations](#)

last modified:

9/19/2025