



SIMATIC ET 200SP, analog input module, AI Energy Meter RC ST, for Rogowski coils or current/voltage transformer 333 mV, suitable for BU type U0, channel diagnostics

General information	
Product type designation	AI Energy Meter RC ST
Firmware version	V8.0
• FW update possible	Yes
usable BaseUnits	BU type U0
Color code for module-specific color-coded label	CC20
Supported power supply systems	TT, TN, IT
Product function	
• Voltage measurement	Yes
— without voltage transformer	Yes
— with voltage transformer	Yes
• Current measurement	Yes; max. 3 + neutral conductor
— without current transformer	No
— with current transformer	No
— With Rogowski coil	Yes
— With current-voltage-converter	Yes; 333 mV interface
• Energy measurement	Yes
• Frequency measurement	Yes
• Power measurement	Yes
• Active power measurement	Yes
• Reactive power measurement	Yes
• Power factor measurement	Yes
• Active factor measurement	Yes
• Reactive power compensation	Yes
• Line analysis	No
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	STEP 7 V16 or higher with HSP
• STEP 7 configurable/integrated from version	Configurable via GSD file
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	V2.3
Operating mode	
• Switching between operating modes in RUN	Yes; For module version 32 I/20 Q, it is possible to dynamically switch between 25 user data variants, 23 of which are pre-defined and 2 of which can be defined by the specific user
• Cyclic measured value access	Yes
• Acyclic measured value access	Yes
• Fixed measured value sets	Yes
• Freely definable measured value sets	Yes; For cyclic and acyclic measured value access

CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes
Installation type/mounting	
Mounting position	any
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption (rated value)	12.5 mA
Current consumption, max.	17 mA
Power loss	
Power loss, typ.	400 mW; 3x 230 V AC
Address area	
Address space per module	
• Inputs	256 byte
• Outputs	20 byte
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	type C
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type U0
Time of day	
Operating hours counter	
• present	Yes
Analog inputs	
Cycle time (all channels), typ.	50 ms; Time for consistent update of all measured and calculated values (cyclic und acyclic data)
Cable length	
• shielded, max.	200 m
• unshielded, max.	200 m
Analog value generation for the inputs	
Sampling frequency, max.	2 048 kHz
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	Yes
• Limit value alarm	Yes
• Hardware interrupt	Yes; Monitoring of up to 16 freely selectable process values (exceeding or undershooting of value)
Diagnoses	
• Supply voltage	Yes
• Hardware interrupt lost	Yes
• Parameter assignment error	Yes
• Module fault	Yes
• Channel not available	Yes
• Overflow/underflow	Yes
• Overload current	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red Fn LED
• for module diagnostics	Yes; green/red DIAG LED
Integrated Functions	
Measuring functions	
• Measuring procedure for voltage measurement	TRMS
• Measuring procedure for current measurement	TRMS
• Type of measured value acquisition	seamless

• Curve shape of voltage	Sinusoidal or distorted	
• Buffering of measured variables	Yes	
• Parameter length	128 byte	
• Bandwidth of measured value acquisition	3.2 kHz; Harmonics: 63 / 50 Hz, 52 / 60 Hz	
Measuring range		
— Frequency measurement, min.	40 Hz	
— Frequency measurement, max.	70 Hz	
Measuring inputs for voltage		
— Measurable line voltage between phase and neutral conductor	277 V	
— Measurable line voltage between the line conductors	480 V	
— Measurable line voltage between phase and neutral conductor, min.	3 V	
— Measurable line voltage between phase and neutral conductor, max.	300 V	
— Measurable line voltage between the line conductors, min.	6 V	
— Measurable line voltage between the line conductors, max.	519 V	
— Internal resistance line conductor and neutral conductor	1.5 MΩ	
— Power consumption per phase	60 mW; 300 V AC	
— Impulse voltage resistance 1,2/50μs	2.5 kV	
— Overvoltage category	CAT II according to IEC 61010 Part 1	
Measuring inputs for current (Rog. or I/U converter)		
— Measurable current at AC, max.	424 mV	
— Continuous voltage, maximum permissible	2 V	
— Rated value, short-time withstand voltage restricted to 1 s	30 V	
— Input resistance	120 kΩ	
— Zero point suppression	Yes; 0 ... 20%, referred to the nominal current	
Accuracy class according to IEC 61557-12		
— Measured variable voltage	0,2	
— Measured variable current	0,2	
— Measured variable apparent power	0,5	
— Measured variable active power	0,5	
— Measured variable reactive power	1	
— Measured variable power factor	0,5	
— Measured variable active energy	0,5	
— Measured variable reactive energy	1	
— Measured variable neutral current	0,2	
— Measured variable phase angle	±0,5 °; not covered by IEC 61557-12	
— Measured variable frequency	0,05; only valid for the permissible voltage measuring range	
Potential separation		
Potential separation channels		
• between the channels	No	
• between the channels and backplane bus	Yes	
• Between the channels and load voltage L+	Yes; Including FE	
Isolation		
Isolation tested with	Between channels and backplane bus, 24 V supply: Routine test, 1 920 V AC, 2 s; between backplane bus and 24 V supply: Type test, 707 V DC	
Standards, approvals, certificates		
Ecological footprint		
• environmental product declaration	Yes	
Global warming potential		
— global warming potential, (total) [CO ₂ eq]	9.32 kg	
— global warming potential, (during production) [CO ₂ eq]	4.97 kg	
— global warming potential, (during operation) [CO ₂ eq]	4.79 kg	
— global warming potential, (after end of life cycle)	-0.449 kg	

[CO2 eq]

Ambient conditions

Ambient temperature during operation

• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C

Altitude during operation relating to sea level

• Installation altitude above sea level, max.	3 000 m; Restrictions for installation altitudes > 2 000 m, see manual
---	--

Dimensions

Width	20 mm
Height	73 mm
Depth	58 mm

Weights

Weight, approx.	45 g
-----------------	------

Other

Data for selecting a voltage transformer

• Secondary side, max.	300 V
------------------------	-------

Classifications

	Version	Classification
eClass	14	27-24-26-01
eClass	12	27-24-26-01
eClass	9.1	27-24-26-01
eClass	9	27-24-26-01
eClass	8	27-24-26-01
eClass	7.1	27-24-26-01
eClass	6	27-24-26-01
ETIM	10	EC001596
ETIM	9	EC001596
ETIM	8	EC001596
ETIM	7	EC001596
IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates**General Product Approval**[Miscellaneous](#)[Manufacturer Declaration](#)[China RoHS](#)**General Product Approval**[FM](#)**For use in hazardous locations****Maritime application****Maritime application**[NK / Nippon Kaiji Kyokai](#)[CCS \(China Classification Society\)](#)**Maritime application****Maritime application****Environment**



last modified:

9/19/2025 