



SIMATIC DP, Electronics module for ET 200SP, F-DQ 4x24 V DC/2A, 15 mm width, up to PL E (ISO 13849) up to SIL 3 (IEC 61508)

General information	
Product type designation	F-DQ 4x24VDC/2A PM HF
usable BaseUnits	BU type A0
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V12
• STEP 7 configurable/integrated from version	V5.5 SP3 / -
• PROFINET from GSD version/GSD revision	V2.31
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
power supply according to NEC Class 2 required	No
Input current	
Current consumption (rated value)	75 mA; without load
Current consumption, max.	21 mA; From the backplane bus
Output voltage	
Rated value (DC)	24 V
Power	
Power consumption from the backplane bus	70 mW
Power loss	
Power loss, typ.	4 W
Address area	
Address space per module	
• Inputs	5 byte
• Outputs	5 byte
Hardware configuration	
Automatic encoding	Yes
• Electronic coding element type F	Yes
Digital outputs	
Type of digital output	Transistor
Number of digital outputs	4
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes
• Response threshold, typ.	> 3.3 A
Open-circuit detection	Yes
• Response threshold, typ.	8 mA

Overload protection	Yes
• Response threshold, typ.	2.9 A
Limitation of inductive shutdown voltage to	Typ. -2x 47 V
Controlling a digital input	Yes; digital output, according to IEC 61131-2, type 2
Switching capacity of the outputs	
• with resistive load, max.	2 A
• on lamp load, max.	10 W
Load resistance range	
• lower limit	12 Ω
• upper limit	2 000 Ω
Output voltage	
• for signal "1", min.	24 V; L+ (-0.5 V)
Output current	
• for signal "1" rated value	2 A
• for signal "0" residual current, max.	0.5 mA
Switching frequency	
• with resistive load, max.	30 Hz; Symmetrical
• with inductive load, max.	0.1 Hz; according to IEC 60947-5-1, DC-13, symmetrical
• on lamp load, max.	10 Hz; Symmetrical
Total current of the outputs	
• Current per channel, max.	2 A; note derating data in the manual
• Current per module, max.	6 A; note derating data in the manual
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	500 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes; See Chapter "Alarms/diagnostic messages" in the manual
Substitute values connectable	No
Alarms	
• Diagnostic alarm	Yes
• Hardware interrupt	No
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red LED
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	No
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Suitable for safety functions	Yes
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	88.3 kg
— global warming potential, (during production) [CO2 eq]	13.1 kg
— global warming potential, (during operation) [CO2 eq]	76.6 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-1.37 kg
Highest safety class achievable in safety mode	
• Performance level according to ISO 13849-1	PLe

• SIL acc. to IEC 61508	SIL 3
Probability of failure (for service life of 20 years and repair time of 100 hours)	
— Low demand mode: PFDavg in accordance with SIL2	< 2.00E-04
— Low demand mode: PFDavg in accordance with SIL3	< 2.00E-05
— High demand/continuous mode: PFH in accordance with SIL2	< 1.00E-08 1/h
— High demand/continuous mode: PFH in accordance with SIL3	< 1.00E-09 1/h

Ambient conditions

Ambient temperature during operation	
• horizontal installation, min.	0 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	0 °C
• vertical installation, max.	50 °C

Altitude during operation relating to sea level

• Installation altitude above sea level, max.	4 000 m; Restrictions for installation altitudes > 2 000 m, see manual
---	--

Dimensions

Width	15 mm
Height	73 mm
Depth	58 mm

Weights

Weight, approx.	57 g
-----------------	------

Classifications

	Version	Classification
eClass	14	27-24-26-04
eClass	12	27-24-26-04
eClass	9.1	27-24-26-04
eClass	9	27-24-26-04
eClass	8	27-24-26-04
eClass	7.1	27-24-26-04
eClass	6	27-24-26-04
ETIM	10	EC001599
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599
IDEA	4	3566
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)



[Miscellaneous](#)

[China RoHS](#)



General Product Approval

For use in hazardous locations



[FM](#)

[CCC-Ex](#)



For use in hazardous locations	Functional Safety	Maritime application
--------------------------------	-------------------	----------------------

[Type Examination Certificate](#)

[Miscellaneous](#)

[TUEV](#)

[Type Examination Certificate](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)



Environment

Industrial Communication



[PROFIsafe](#)

last modified:

10/23/2025 