



SIMATIC DP, electronic module ET 200SP, F-DQ 8x24VDC/0.5A PP HF, 15 mm width, up to PL E (ISO 13849) up to SIL 3 (IEC 61508)

General information	
Product type designation	F-DQ 8x24 V DC/0.5 A PP HF
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC02
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14 SP1 with HSP 202
• STEP 7 configurable/integrated from version	V5.5 SP4 HF5
• PROFINET from GSD version/GSD revision	V2.31
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
power supply according to NEC Class 2 required	No
Input current	
Current consumption (rated value)	75 mA; without load
Current consumption, max.	21 mA; From the backplane bus
Output voltage	
Rated value (DC)	24 V
Power	
Power consumption from the backplane bus	70 mW
Power loss	
Power loss, typ.	3 W
Address area	
Address space per module	
• Inputs	6 byte; 5 bytes non-RIOforFA; 6 bytes RIOforFA
• Outputs	6 byte; 5 bytes non-RIOforFA; 6 bytes RIOforFA
Hardware configuration	
Automatic encoding	Yes
• Electronic coding element type F	Yes
Digital outputs	
Type of digital output	Transistor
Number of digital outputs	8
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes

• Response threshold, typ.	Min. 0.7 A
Open-circuit detection	No
Limitation of inductive shutdown voltage to	Typ. -39 V
Controlling a digital input	Yes; digital output, according to IEC 61131-2, type 0.5
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
• on lamp load, max.	2 W
Load resistance range	
• lower limit	48 Ω
• upper limit	12 000 Ω
Output voltage	
• for signal "1", min.	24 V; L+ (-0.5 V)
Output current	
• for signal "1" rated value	0.5 A
• for signal "0" residual current, max.	0.5 mA
Switching frequency	
• with resistive load, max.	30 Hz; Symmetrical
• with inductive load, max.	0.1 Hz; according to IEC 60947-5-1, DC-13, symmetrical
• with capacitive load, max.	2 Hz; Symmetrical
• on lamp load, max.	10 Hz; Symmetrical
Total current of the outputs	
• Current per channel, max.	0.5 A; note derating data in the manual
• Current per module, max.	3 A; note derating data in the manual
Total current of the outputs (per module)	
horizontal installation	
— up to 40 °C, max.	3 A
— up to 50 °C, max.	2.5 A
— up to 60 °C, max.	2 A
vertical installation	
— up to 50 °C, max.	2 A
Cable length	
• shielded, max.	100 m
• unshielded, max.	100 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes; See Chapter "Alarms/diagnostic messages" in the manual
Substitute values connectable	No
Alarms	
• Diagnostic alarm	Yes
• Hardware interrupt	No
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red LED
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	No
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Suitable for safety functions	Yes
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	

— global warming potential, (total) [CO2 eq]	88.3 kg																																										
— global warming potential, (during production) [CO2 eq]	13.1 kg																																										
— global warming potential, (during operation) [CO2 eq]	76.6 kg																																										
— global warming potential, (after end of life cycle) [CO2 eq]	-1.37 kg																																										
Highest safety class achievable in safety mode																																											
• Performance level according to ISO 13849-1	PLe																																										
• Category according to ISO 13849-1	Cat. 4																																										
• SIL acc. to IEC 61508	SIL 3																																										
Probability of failure (for service life of 20 years and repair time of 100 hours)																																											
— Low demand mode: PFDavg in accordance with SIL3	< 6.00E-05																																										
— High demand/continuous mode: PFH in accordance with SIL3	< 2.00E-09 1/h																																										
Ambient conditions																																											
Ambient temperature during operation																																											
• horizontal installation, min.	0 °C																																										
• horizontal installation, max.	60 °C																																										
• vertical installation, min.	0 °C																																										
• vertical installation, max.	50 °C																																										
Altitude during operation relating to sea level																																											
• Installation altitude above sea level, max.	4 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP System Manual																																										
Dimensions																																											
Width	15 mm																																										
Height	73 mm																																										
Depth	58 mm																																										
Weights																																											
Weight, approx.	48 g																																										
Classifications																																											
	<table><tr><th></th><th>Version</th><th>Classification</th></tr><tr><td>eClass</td><td>14</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-04</td></tr><tr><td>ETIM</td><td>10</td><td>EC001599</td></tr><tr><td>ETIM</td><td>9</td><td>EC001599</td></tr><tr><td>ETIM</td><td>8</td><td>EC001599</td></tr><tr><td>ETIM</td><td>7</td><td>EC001599</td></tr><tr><td>IDEA</td><td>4</td><td>3566</td></tr><tr><td>UNSPSC</td><td>15</td><td>32-15-17-05</td></tr></table>		Version	Classification	eClass	14	27-24-26-04	eClass	12	27-24-26-04	eClass	9.1	27-24-26-04	eClass	9	27-24-26-04	eClass	8	27-24-26-04	eClass	7.1	27-24-26-04	eClass	6	27-24-26-04	ETIM	10	EC001599	ETIM	9	EC001599	ETIM	8	EC001599	ETIM	7	EC001599	IDEA	4	3566	UNSPSC	15	32-15-17-05
	Version	Classification																																									
eClass	14	27-24-26-04																																									
eClass	12	27-24-26-04																																									
eClass	9.1	27-24-26-04																																									
eClass	9	27-24-26-04																																									
eClass	8	27-24-26-04																																									
eClass	7.1	27-24-26-04																																									
eClass	6	27-24-26-04																																									
ETIM	10	EC001599																																									
ETIM	9	EC001599																																									
ETIM	8	EC001599																																									
ETIM	7	EC001599																																									
IDEA	4	3566																																									
UNSPSC	15	32-15-17-05																																									
Approvals / Certificates																																											
General Product Approval	EMV	Test Certificates																																									
 EG-Konf.		 UL		 RCM	Special Test Certificate																																						
Maritime application					other																																						



[Confirmation](#)

other		Railway		Environment
	Miscellaneous	Type Test Certificates/Test Report		Confirmation
		Environmental Confirmations		

last modified:

10/23/2025 