



*** spare part *** SIMATIC DP, ET 200eco PN, 4 AO U/I; 4xM12, degree of protection IP67

General information	
Vendor identification (VendorID)	002AH
Device identifier (DeviceID)	0306H
Supply voltage	
Rated value (DC)	24 V
Reverse polarity protection	Yes
power supply according to NEC Class 2 required	Yes
Input current	
Current consumption, typ.	280 mA
Actuator supply	
Number of outputs	4
Short-circuit protection	Yes; Electronic at 1.4 A
Output current	
• Rated value	1 A; Maximum
Power loss	
Power loss, typ.	5.5 W
Analog outputs	
Number of analog outputs	4
Voltage output, short-circuit protection	Yes
Voltage output, short-circuit current, max.	30 mA
Current output, no-load voltage, max.	20 V
Output ranges, voltage	
• 0 to 10 V	Yes
• 1 V to 5 V	Yes
• -10 V to +10 V	Yes
Output ranges, current	
• 0 to 20 mA	Yes
• -20 mA to +20 mA	Yes
• 4 mA to 20 mA	Yes
Connection of actuators	
• for voltage output two-wire connection	Yes
• for current output two-wire connection	Yes
Load impedance (in rated range of output)	
• with voltage outputs, min.	1 kΩ
• with voltage outputs, capacitive load, max.	1 μF
• with current outputs, max.	600 Ω
• with current outputs, inductive load, max.	1 mH
Destruction limits against externally applied voltages and currents	
• Voltages at the outputs towards MANA	28.8 V permanent, 35 V for max. 500 ms

Cable length	
• shielded, max.	30 m
Analog value generation for the outputs	
Analog value display	SIMATIC S7 format
Conversion principle	Resistor network
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Conversion time (per channel)	1 ms
Settling time	
• for resistive load	2 ms
• for capacitive load	1.8 ms
• for inductive load	2 ms
Errors/accuracies	
Output ripple (relative to output range, bandwidth 0 to 50 kHz), (+/-)	U: ± 0.6 mVrms; I: ± 0.4 nArms
Linearity error (relative to output range), (+/-)	0.02 %
Temperature error (relative to output range), (+/-)	U: 0.001%/°C; I: 0.0025%/°C
Crosstalk between the outputs, min.	70 dB
Repeat accuracy in steady state at 25 °C (relative to output range), (+/-)	0.008 %
Interfaces	
Transmission procedure	100BASE-TX
Number of PROFINET interfaces	1
1. Interface	
Interface types	
• M12 port	Yes
• integrated switch	Yes
PROFINET IO Device	
Services	
— IRT with the option "high flexibility"	Yes
— Prioritized startup	Yes
Interface types	
M12 port	
• Autonegotiation	Yes
• Autocrossing	Yes
• Transmission rate, max.	100 Mbit/s
Protocols	
Supports protocol for PROFINET IO	Yes
PROFINET CBA	No
PROFIsafe	No
Redundancy mode	
Media redundancy	
— MRP	Yes
Open IE communication	
• TCP/IP	No
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
• ping	Yes
• ARP	Yes
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes; green "ON" LED
• Wire-break	Yes; Channel-by-channel with current output

• Short-circuit • Group error		Yes; Channel-by-channel with voltage output																																										
		Yes; Red/yellow "SF/MT" LED																																										
Potential separation																																												
between the load voltages	Yes																																											
between load voltage and all other switching components	No																																											
between Ethernet and electronics	Yes																																											
Potential separation channels																																												
• between the channels	No																																											
Permissible potential difference																																												
between M internally and the outputs	10 Vpp AC																																											
Isolation																																												
tested with																																												
• 24 V DC circuits • Test voltage for interface, rms value [Vrms]	707 V DC (type test) 1 500 V; According to IEEE 802.3																																											
Degree and class of protection																																												
IP degree of protection	IP65/67																																											
Standards, approvals, certificates																																												
Use in hazardous areas																																												
• Explosion protection category for gas • Explosion protection category for dust	ATEX gas explosion protection, Zone 2 ATEX dust explosion protection, Zone 22																																											
Connection method																																												
Design of electrical connection	4/5-pin M12 circular connectors																																											
Dimensions																																												
Width	60 mm																																											
Height	175 mm																																											
Depth	49 mm																																											
Weights																																												
Weight, approx.	930 g																																											
Classifications																																												
		<table><tr><th></th><th>Version</th><th>Classification</th></tr><tr><td>eClass</td><td>14</td><td>27-24-26-01</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-01</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-01</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-01</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-01</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-01</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-01</td></tr><tr><td>ETIM</td><td>10</td><td>EC001596</td></tr><tr><td>ETIM</td><td>9</td><td>EC001596</td></tr><tr><td>ETIM</td><td>8</td><td>EC001596</td></tr><tr><td>ETIM</td><td>7</td><td>EC001596</td></tr><tr><td>IDEA</td><td>4</td><td>3562</td></tr><tr><td>UNSPSC</td><td>15</td><td>32-15-17-05</td></tr></table>		Version	Classification	eClass	14	27-24-26-01	eClass	12	27-24-26-01	eClass	9.1	27-24-26-01	eClass	9	27-24-26-01	eClass	8	27-24-26-01	eClass	7.1	27-24-26-01	eClass	6	27-24-26-01	ETIM	10	EC001596	ETIM	9	EC001596	ETIM	8	EC001596	ETIM	7	EC001596	IDEA	4	3562	UNSPSC	15	32-15-17-05
	Version	Classification																																										
eClass	14	27-24-26-01																																										
eClass	12	27-24-26-01																																										
eClass	9.1	27-24-26-01																																										
eClass	9	27-24-26-01																																										
eClass	8	27-24-26-01																																										
eClass	7.1	27-24-26-01																																										
eClass	6	27-24-26-01																																										
ETIM	10	EC001596																																										
ETIM	9	EC001596																																										
ETIM	8	EC001596																																										
ETIM	7	EC001596																																										
IDEA	4	3562																																										
UNSPSC	15	32-15-17-05																																										
Approvals / Certificates																																												
General Product Approval		EMV																																										
 CCC  EG-Konf.   UL   RCM																																												
For use in hazardous locations	Functional Safety	Test Certificates	other	Railway																																								



[Type Examination Certificate](#)

[Type Test Certificates/Test Report](#)



[Confirmation](#)

[Special Test Certificate](#)

Environment

[Environmental Confirmations](#)

last modified:

10/23/2025