



SITOP BUF1200/300MS/40A/EX

SITOP BUF1200 buffer module Buffer time 300 ms at 40 A buffer time dependent on load current 24V DC input

General information	
Technical Product Detail Page	https://l.siemens.com/1P6EP4231-7HC00-0AX0
input	
supply voltage at DC rated value	24 V
supply voltage at DC	24 ... 28 V
input voltage at DC	20 ... 30 V
memory	
design of the mains power cut bridging-connection	Module for buffering during short power interruptions; parallel connection at the output of 24 V power supplies. Buffer time of 300 ms at 40 A up to 2.4 s at 5 A load current; multiplication possible by parallel connection
buffering time in the event of power failure	0.3 min
output	
output current	40 A
• rated value	
protection and monitoring	
display version	LED green for "buffer standby exist"
• for normal operation	
interfaces	
product component PC interface	No
product function communication function	No
design of the interface	without
safety	
galvanic isolation between input and output	Yes
operating resource protection class	Class III
protection class IP	IP20
standard	EN 61000-6-2
• for interference immunity	
standards, specifications, approvals	
certificate of suitability	Yes
• CE marking	
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
• UKCA marking	Yes
type of certification CB-certificate	Yes
standards, specifications, approvals hazardous environments	
certificate of suitability	Yes; IECEx Ex ec IIC T4 Gc
• IECEx	
• ATEX	Yes; ATEX (Ex) II 3G Ex ec IIC T4 Gc
• ULhazloc approval	Yes
• CCC for hazardous zone according to GB standard	Yes

standards, specifications, approvals marine classification	
shipbuilding approval	No
Marine classification association	
<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) Det Norske Veritas (DNV) 	No No; in preparation
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
<ul style="list-style-type: none"> total during manufacturing during operation after end of life 	68.9 kg 19 kg 49.1 kg 0.36 kg
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during transport during storage 	-40 ... +70 °C; with natural convection -40 ... +85 °C -40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	push-in terminals
<ul style="list-style-type: none"> at input at output 	+: push-in for 0.75 ... 16 mm ² -: push-in for 0.5 ... 6 mm ²
mechanical data	
width × height × depth of the enclosure	70 × 135 × 155 mm
installation width × mounting height	70 mm × 225 mm
required spacing	
<ul style="list-style-type: none"> top bottom left right 	45 mm 45 mm 0 mm 0 mm
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
<ul style="list-style-type: none"> DIN-rail mounting S7 rail mounting wall mounting 	Yes No No
housing can be lined up	Yes
net weight	1.2 kg
further information internet links	
internet link	
<ul style="list-style-type: none"> to website: Industry Mall to web page: selection aid TIA Selection Tool to web page: power supplies to website: CAX-Download-Manager to website: Industry Online Support 	https://mall.industry.siemens.com https://www.siemens.com/tstcloud https://siemens.com/sitop https://siemens.com/cax https://support.industry.siemens.com
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are

no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Classifications

	Version	Classification
eClass	14	27-04-07-05
eClass	12	27-04-07-05
eClass	9.1	27-04-07-05
eClass	9	27-04-07-05
eClass	8	27-04-06-90
eClass	7.1	27-04-06-90
eClass	6	27-04-06-90
ETIM	10	EC000382
ETIM	9	EC000382
ETIM	8	EC000382
ETIM	7	EC000382

Approvals Certificates

General Product Approval



[Manufacturer Declaration](#)



[China RoHS](#)



For use in hazardous locations

Maritime application



[Miscellaneous](#)

[CCC-Ex](#)



Environment



last modified:

5/5/2026