

Siemens
EcoTech



SIMATIC ET 200SP, BaseUnit BU15-P16+A0+2D/T, BU type A1, Push-in terminals, without AUX terminals, New load group, WxH: 15x 117 mm, with temperature acquisition



General information	
Product type designation	BU type A1
HW functional status	FS10 and higher
Supply voltage	
Rated value (DC)	24 V
external protection for power supply lines	Yes; 24 V DC/10 A miniature circuit breaker with type B or C tripping characteristic
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For process terminals, max.	2 A
Hardware configuration	
Temperature sensor	Yes
Formation of potential groups	
• New potential group	Yes
• Potential group continued from the left	No
Slots	
• Number of slots	1; Type A1
Potential separation	
between the potential groups	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	0.873 kg
— global warming potential, (during production) [CO2 eq]	0.866 kg
— global warming potential, (during operation) [CO2 eq]	0 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.0011 kg
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C

vertical installation, max.	50 °C																																										
Altitude during operation relating to sea level																																											
Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual																																										
Accessories																																											
Color coding labels																																											
- for process terminals - for AUX terminals - for add-on terminals	CC00 to CC09 does not exist does not exist																																										
Connection method																																											
Terminals																																											
- Terminal type - system-integrated shield connection - Conductor cross-section, min. - Conductor cross-section, max. - Number of process terminals to I/O module - Number of terminals to AUX bus - Number of add-on terminals - Number of terminals with connection to P1 and P2 bus	Push-in terminal Yes; Optional 0.14 mm²; AWG 26 2.5 mm²; AWG 14 16 0 0 2																																										
Dimensions																																											
Width	15 mm																																										
Height	117 mm																																										
Depth	35 mm																																										
Weights																																											
Weight, approx.	40 g																																										
Classifications																																											
	<table><tr><th></th><th>Version</th><th>Classification</th></tr><tr><td>eClass</td><td>14</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-03</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-03</td></tr><tr><td>ETIM</td><td>10</td><td>EC001598</td></tr><tr><td>ETIM</td><td>9</td><td>EC001598</td></tr><tr><td>ETIM</td><td>8</td><td>EC001598</td></tr><tr><td>ETIM</td><td>7</td><td>EC001598</td></tr><tr><td>IDEA</td><td>4</td><td>3560</td></tr><tr><td>UNSPSC</td><td>15</td><td>32-15-17-04</td></tr></table>		Version	Classification	eClass	14	27-24-26-03	eClass	12	27-24-26-03	eClass	9.1	27-24-26-03	eClass	9	27-24-26-03	eClass	8	27-24-26-03	eClass	7.1	27-24-26-03	eClass	6	27-24-26-03	ETIM	10	EC001598	ETIM	9	EC001598	ETIM	8	EC001598	ETIM	7	EC001598	IDEA	4	3560	UNSPSC	15	32-15-17-04
	Version	Classification																																									
eClass	14	27-24-26-03																																									
eClass	12	27-24-26-03																																									
eClass	9.1	27-24-26-03																																									
eClass	9	27-24-26-03																																									
eClass	8	27-24-26-03																																									
eClass	7.1	27-24-26-03																																									
eClass	6	27-24-26-03																																									
ETIM	10	EC001598																																									
ETIM	9	EC001598																																									
ETIM	8	EC001598																																									
ETIM	7	EC001598																																									
IDEA	4	3560																																									
UNSPSC	15	32-15-17-04																																									
Approvals / Certificates																																											
General Product Approval																																											
 EG-Konf.  Manufacturer Declaration  UL   RCM																																											
For use in hazardous locations																																											
 UL CCC-Ex FM  ATEX Type Examination Certificate  IECEX																																											
For use in hazardous locations	Maritime application																																										

Miscellaneous



[NK / Nippon Kaiji Kyokai](#)

Maritime application

Environment



[CCS \(China Classification Society\)](#)



Siemens EcoTech



last modified:

10/23/2025 