



SCALANCE XB008 Unmanaged Industrial Ethernet Switch for 10/100 Mbit/s; for setting up small star and line topologies; LED diagnostics, IP20, 24 V AC/DC power supply, with 8x 10/100 Mbit/s twisted pair ports with RJ45 sockets; Manual available as a download .

product type designation	
product brand name	SCALANCE
product type designation	XB008
Technical Product Detail Page	<a href="https://i.siemens.com/1P6GK5008-0BA10-1AB2">https://i.siemens.com/1P6GK5008-0BA10-1AB2</a>
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	8; RJ45
number of 100 Mbit/s SC ports	
• for multimode	0
interfaces / other	
number of electrical connections	
• for power supply	1
type of electrical connection	
• for power supply	3-pole terminal block
supply voltage, current consumption, power loss	
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	DC
• power loss [W] / 1 / rated value	24 V
• supply voltage / 1 / voltage range	2.88 W
• consumed current / 1 / maximum	19.2 ... 28.8
• type of electrical connection / 1 / for power supply	0.12 A
• product component / 1 / fusing at power supply input	3-pole terminal block
• fuse protection type / 1 / at input for supply voltage	Yes
	0.6 A / 60 V
type of voltage / 2 / of the supply voltage	
• supply voltage / 2 / voltage range	AC
	19.2 ... 28.8
ambient conditions	
ambient temperature	
• during operation	-10 ... +60 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	Box
width	45 mm

height	100 mm
depth	87 mm
net weight	0.18 kg
fastening method	
• 35 mm DIN-rail mounting	Yes
• wall mounting	Yes
• S7-1500 rail mounting	No
<b>product functions / management, configuration, engineering</b>	
product function	
• multiport mirroring	No
• CoS	Yes
• switch-managed	No
PROFINET conformity class	A
<b>product functions / redundancy</b>	
product function	
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
<b>standards, specifications, approvals</b>	
certificate of suitability	
• CE marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4 (Class A)
• for immunity to EMC	EN 61000-6-2
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
<b>standards, specifications, approvals / hazardous environments</b>	
certificate of suitability	
• ATEX	Yes
• UKEx	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
<b>standards, specifications, approvals / other</b>	
certificate of suitability	
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
<b>standards, specifications, approvals / Environmental Product Declaration</b>	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	114.08 kg
• during manufacturing	7.42 kg
• during operation	106.52 kg
• after end of life	0.14 kg
<b>product functions / general</b>	
MTBF	214 a
warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
<b>further information / internet links</b>	
internet link	
• to website: Selection guide for cables and connectors	<a href="https://support.industry.siemens.com/cs/ww/en/view/109766358">https://support.industry.siemens.com/cs/ww/en/view/109766358</a>
• to web page: selection aid TIA Selection Tool	<a href="https://www.siemens.com/tiacloud">https://www.siemens.com/tiacloud</a>
• to website: Industrial communication	<a href="https://www.siemens.com/simatic-net">https://www.siemens.com/simatic-net</a>
• to web page: SiePortal	<a href="https://sieportal.siemens.com/">https://sieportal.siemens.com/</a>

- to website: Image database
- to website: CAx-Download-Manager
- to website: Industry Online Support

<https://www.automation.siemens.com/bilddb>

<https://www.siemens.com/cax>

<https://support.industry.siemens.com>

#### security information

##### security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit [www.siemens.com/cybersecurity-industry](https://www.siemens.com/cybersecurity-industry). Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

#### Approvals / Certificates

##### General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)



General Product Approval

EMV

For use in hazardous locations



EM

[CCC-Ex](#)

Test Certificates

Environment

Industrial Communication

[Type Test Certificates/Test Report](#)



[PROFINET](#)

last modified:

1/23/2026