



SCALANCE XP216EEC, managed IE switch, with railway approval IEC 62443-4-2 certified; (EN 50155, EN45545); 12x 10/100 Mbit/s M12 ports, 4x 10/100/1000 Mbit/s M12 ports IP65, LED diagnostics, error signaling contact, redundant power supply, PROFINET IO device, network management, can be operated in redundant ring, incl. dust caps, including electronic manual on CD-ROM, C-PLUG optional.

product type designation	
product brand name	SCALANCE
product type designation	XP216EEC
Technical Product Detail Page	https://i.siemens.com/1P6GK5216-0HA00-2ES6
transfer rate	
transfer rate	10, 100, 1000 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	16; M12
number of 10/100 Mbit/s M12-ports (D-coded)	12
number of 10/100/1000 Mbit/s M12-ports (X-coded)	4
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for power supply	2
type of electrical connection	
• for operator console	5-pole M12 socket (A-coded)
• for signaling contact	5-pole M12 plug (B-coded)
• for power supply	4-pole M12 plug (A-coded)
design of the removable storage	
• C-PLUG	Yes
product function / device replacement with replacement of the storage medium	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	24 V; XP-200EEC with EN 50155 supports the voltage range 16.8 ... 30 V DC
• power loss [W] / 1 / rated value	8 W
• consumed current / 1 / at rated supply voltage / maximum	0.4 A
• supply voltage / 1 / voltage range	19.2 ... 28.8
• consumed current / 1 / maximum	0.335 A
• type of electrical connection / 1 / for power supply	4-pole M12 plug (A-coded)
• product component / 1 / fusing at power supply input	Yes
ambient conditions	

ambient temperature		
• during operation	-40 ... +70 °C	
• during storage	-40 ... +70 °C	
• during transport	-40 ... +70 °C	
• note	EEC variants with EN 50155 support for 10 minutes: -40 °C ... +85 °C	
relative humidity		
• at 25 °C / without condensation / during operation / maximum	95 %	
protection class IP	IP65	
design, dimensions and weights		
design	compact	
width	280 mm	
height	200 mm	
depth	49 mm	
net weight	2.5 kg	
product feature / conformal coating	Yes	
material / of the enclosure	Aluminum	
fastening method	ET200pro module carrier	
• wall mounting	Yes	
product features, product functions, product components / general		
cascading in the case of a redundant ring / at reconfiguration time of <~0.3~s	50	
cascading in cases of star topology	any (depending only on signal propagation time)	
product function		
• QoS according to DSCP	Yes	
product feature		
• Cut Through switching method	No	
• Store & Forward switching method	Yes	
product functions / management, configuration, engineering		
product function		
• CLI	Yes	
• web-based management	Yes	
• MIB support	Yes	
• TRAPs via email	Yes	
• configuration with STEP 7	Yes	
• RMON	Yes	
• SMTP server	No	
• port mirroring	Yes	
• multiport mirroring	Yes	
• CoS	Yes	
• with IRT / PROFINET IO switch	No	
• PROFINET IO diagnosis	Yes	
• switch-managed	Yes	
PROFINET conformity class	B	
network load class / according to PROFINET	II	
telegram length / for Ethernet / maximum	1518 byte	
protocol / is supported		
• Telnet	Yes	
• HTTP	Yes	
• HTTPS	Yes	
• TFTP	Yes	
• SFTP	Yes	
• BOOTP	No	
• GMRP	Yes	
• DCP	Yes	
• LLDP	Yes	
• EtherNet/IP	Yes	
• SNMP v1	Yes	
• SNMP v2	Yes	

• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
product functions / DHCP	
product function	
• DHCP server	Yes
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes
• of the PROFINET IO device / is supported / H-Sync forwarding	Yes
• of the PROFINET IO device / is supported / PROFINET system redundancy	Yes
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure RSTP+	Yes
• redundancy procedure MSTP	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	Yes
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• RADIUS client	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
• SSL	Yes

product functions / time	
product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UKCA marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4 (Class A)
• for immunity to EMC	EN 61000-6-2
• for safety / from CSA and UL	UL 60950-1 E115352, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50155	Yes; OT4, ST1, H1, S2, C1, L4, PC2
• railway application in accordance with EN 50121-4	Yes
• railway application in accordance with EN 50124-1	Yes
• fire protection in accordance with EN 45545-2	Yes; Class HL1 - HL3
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
standards, specifications, approvals / marine classification	
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Det Norske Veritas (DNV)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	283.14 kg
• during manufacturing	61.47 kg
• during operation	220.84 kg
• after end of life	0.27 kg
product functions / general	
MTBF	39 a
reference temperature / for MTBF determination	40 °C
warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud

- to website: Industrial communication
- to web page: SiePortal
- to website: Image database
- to website: CAx-Download-Manager
- to website: Industry Online Support

<https://www.siemens.com/simatic-net>
<https://sieportal.siemens.com/>
<https://www.automation.siemens.com/bilddb>
<https://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under [https://www.siemens.com/cert. \(V4.7\)](https://www.siemens.com/cert. (V4.7))

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)



General Product Approval

EMV

For use in hazardous locations



[Declaration of Conformity](#)



[TUEV](#)



For use in hazardous locations

Test Certificates

Maritime application



FM

[CCC-Ex](#)

[Type Test Certificates/Test Report](#)

[Inspection certificate](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



Railway

Environment

Industrial Communication

[Confirmation](#)



[PROFINET](#)

last modified:

12/15/2025

