

Article No. : 6SL3210-5BE22-2CV0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data	
------------	--

Input	
Number of phases	3 AC
Line voltage	380 ... 480 V -15 % +10 %
Line frequency	47 ... 63 Hz

Output	
Number of phases	3 AC
Rated voltage	400V IEC 480V NEC ¹⁾
Rated power (LO)	2.20 kW 3.00 hp
Rated power (HO)	2.20 kW 3.00 hp
Rated current (LO)	5.60 A 4.80 A
Rated current (HO)	5.60 A 4.80 A
Rated current (IN)	5.60 A
Pulse frequency	4.00 kHz
Output frequency	0 ... 550 Hz

Overload capability	
Low Overload (LO)	
110 % rated output current for 60 s, cycle time 300 s	
High Overload (HO)	
150 % rated output current for 60 s, cycle time 300 s	

General tech. specifications	
------------------------------	--

Power factor λ	0.72
Offset factor $\cos \varphi$	0.95
Efficiency η	0.98
Filter class (integrated)	Class A
With integrated braking chopper	No

Communication	
---------------	--

Communication	USS, Modbus RTU
---------------	-----------------

Inputs / outputs	
------------------	--

Standard digital inputs	
-------------------------	--

Number	4
--------	---

Digital outputs	
-----------------	--

Number as relay changeover contact	1
Number as transistor	1

Analog inputs	
---------------	--

Number	2 (Can be used as additional digital input)
--------	---

Analog outputs	
----------------	--

Number	1
--------	---

Ambient conditions	
--------------------	--

Cooling	External fan
Installation altitude	1,000 m (3,280.84 ft)

Ambient temperature	
---------------------	--

Operation ²⁾	-10 ... 60 °C (14 ... 140 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

Relative humidity	
-------------------	--

Max. operation	95 %
----------------	------

Connections	
-------------	--

Max. motor cable length	
-------------------------	--

Shielded	10 m (32.81 ft)
Unshielded	50 m (164.04 ft)

Mechanical data	
-----------------	--

Mounting position	Wall mounting / side-by-side mounting
Degree of protection	IP20 / UL open type
Frame size	FSA
Net weight	1.10 kg (2.43 lb)

Dimensions	
------------	--

Width	90.0 mm (3.54 in)
Height	166.0 mm (6.54 in)
Depth	145.5 mm (5.73 in)


Standards	
-----------	--

Compliance with standards	CE, cULus, C-Tick (RCM), KC
CE marking	EN 61800-5-1 /EN 60204-1 and EN 61800-3

Data sheet for SINAMICS V20

Article No. : 6SL3210-5BE22-2CV0

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	31.0 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

¹⁾ The output current and HP ratings are valid for the voltage range 440V-480V

²⁾ Please observe derating at temperatures of 40 °C or above