

## Data sheet


6XV1830-5FH10

product type designation

FC PROFIBUS Process Cable GP / Ethernet-APL Cable GP 2-WISE (IEC TS 60079-47) APL Type A

product description

Bus cable (2-core), sold by the meter, unassembled



PB FC Process Cable GP/ Ethernet-APL cable GP, bus cable for IEC 61158-2 (PB) and IEC TS 60079-47 (2-WISE) sheath color black for Ex applications 2-core shielded, sold by the meter delivery unit max. 1000 m minimum order quantity 20 m.

Technical Product Detail Page

<https://i.siemens.com/1P6XV1830-5FH10>

suitability for use

Use in fieldbus systems according to IEC 61158-2 (e.g. PROFIBUS PA) and IEC TS 60079-47 (2-WISE) / for APL (cable type A), suitable for non-Ex applications

cable designation

02YSY (ST) CY 1x2x1,0/2,55-100 SW OE FR

wire length

sold by the meter

**electrical data**

attenuation factor per length

• at 38.4 kHz / maximum 0.003 dB/m

return loss

• at 3 MHz 19 dB

impedance

- rated value 100 Ω
- at 31.25 kHz 100 Ω
- at 3 MHz ... 20 MHz 100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 31.25 kHz 20 %
- of the characteristic impedance at 3 MHz ... 20 MHz 15 %

loop resistance per length / maximum

44 mΩ/m

shield resistance per length / maximum

6.5 Ω/km

capacity per length / at 1 kHz

92 pF/m

inductance per length

0.65 µH/m

operating voltage

• RMS value 80 V

**mechanical data**

number of electrical cores

2

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

type of electrical connection / FastConnect

Yes

outer diameter

- of inner conductor 1.05 mm
- of the wire insulation 2.55 mm
- of the inner sheath of the cable 5.4 mm
- of cable sheath 8 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.4 mm

material

- of the wire insulation polyethylene (PE)

• of the inner sheath of the cable	PVC
• of cable sheath	PVC
color	
• of the insulation of data wires	red/green
• of cable sheath	Black
bending radius	
• with single bend / minimum permissible	40 mm
• with multiple bends / minimum permissible	80 mm
tensile load / maximum	150 N
weight per length	103 kg/km
<b>ambient conditions</b>	
ambient temperature	
• during operation	-40 ... +80 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
• during installation	-20 ... +80 °C
ambient condition / for operation	Transfer rate of cable: 31.25 Kbit/s
fire behavior	flame resistant according to IEC 60332-3-24 (Category C)
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	conditional resistance
• to grease	Conditional resistance
• to water	conditional resistance
radiological resistance / to UV radiation	resistant
<b>product features, product functions, product components / general</b>	
product feature	
• halogen-free	No
• silicon-free	Yes
<b>standards, specifications, approvals</b>	
UL/ETL listing / 300 V Rating	Yes; c(UL)us, CMG / CL3 / Sun Res
UL/ETL style / 600 V Rating	Yes
certificate of suitability	
• EAC approval	Yes
• CE marking	Yes
• RoHS conformity	Yes
product conformity	
• IEC TS 60079-47 (2-WISE) / for APL (cable type A)	Yes
• resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statków (PRS)	No
<b>further information / internet links</b>	
internet link	
• to website: Selection guide for cables and connectors	<a href="https://support.industry.siemens.com/cs/ww/en/view/109766358">https://support.industry.siemens.com/cs/ww/en/view/109766358</a>
• to web page: selection aid TIA Selection Tool	<a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a>
• to web page: SiePortal	<a href="https://sieportal.siemens.com/">https://sieportal.siemens.com/</a>
• to website: Image database	<a href="https://www.automation.siemens.com/bilddb">https://www.automation.siemens.com/bilddb</a>
• to website: CAx-Download-Manager	<a href="https://www.siemens.com/cax">https://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks.

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit [www.siemens.com/cybersecurity-industry](http://www.siemens.com/cybersecurity-industry). Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

## Approvals / Certificates

### General Product Approval

[Manufacturer Declaration](#)



[Declaration of Conformity](#)



[China RoHS](#)



### General Product Approval

[Fire safety / Physical security](#)



other

[Miscellaneous](#)

Environment

[Environmental Confirmations](#)

last modified:

1/12/2026