

## Data sheet

6XV1841-2B

product type designation	IE FC TP Robust Flexible Cable GP 2x2 (Type B)
product description	Flexible bus cable (4-core), sold by the meter, unassembled
	Industrial Ethernet FastConnect TP robust flexible GP cable 2x2 (PROFINET Type B), TPE protective jacket, with flexible cores, for connection to FC RJ45 plug and FC outlet RJ45, 4-core, shielded, Cat5e, sold by the meter, delivery unit max. 1000 m minimum order quantity 20 m.
	
Technical Product Detail Page	<a href="https://i.siemens.com/1P6XV1841-2B">https://i.siemens.com/1P6XV1841-2B</a>
suitability for use	For occasionally moved machine parts
cable designation	SF/UTP, 2YH (ST) C99Y 2x2x0,75/1,5-100 LI GN
wire length	sold by the meter
<b>electrical data</b>	
attenuation factor per length	
• at 10 MHz / maximum	0.065 dB/m
• at 100 MHz / maximum	0.22 dB/m
impedance	
• at 1 MHz ... 100 MHz	100 Ω
relative symmetrical tolerance	
• of the characteristic impedance at 1 MHz ... 100 MHz	15 %
near-end crosstalk per length	
• at 1 MHz ... 100 MHz	0.5 dB/m
transfer impedance per length / at 10 MHz	20 mΩ/m
loop resistance per length / maximum	120 mΩ/m
operating voltage	
• RMS value	80 V
NVP value in percent	69 %
<b>mechanical data</b>	
number of electrical cores	4
design of the shield	SF/UTP, overlapped aluminum-clad foil, sheathed in a protective braided shield of tinned copper wires
type of electrical connection / FastConnect	Yes
core diameter	
• of AWG22 insulated conductor	0.75 mm
outer diameter	
• of inner conductor	0.75 mm
• of the wire insulation	1.5 mm
• of the inner sheath of the cable	3.9 mm
• of cable sheath	6.5 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
material	
• of the wire insulation	polyethylene (PE)
• of the inner sheath of the cable	FRNC
• of cable sheath	TPE (FR-TPE)
color	

• of the insulation of data wires	white/yellow/blue/orange
• of cable sheath	green
bending radius	
• with single bend / minimum permissible	32.5 mm
• with multiple bends / minimum permissible	52 mm
tensile load / maximum	150 N
weight per length	68 kg/km
<b>ambient conditions</b>	
ambient temperature	
• during operation	-40 ... +75 °C
• during storage	-40 ... +75 °C
• during transport	-40 ... +75 °C
• during installation	-20 ... +60 °C
fire behavior	flame resistant according to IEC 60332-1-2
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	oil resistant according to DIN EN 50290-2-22 (VDE 0819), (7x24h/90°C), UL13 Sec.40 (96h/100°C)
• to grease	Conditional resistance
• to water	conditional resistance
radiological resistance / to UV radiation	resistant
<b>product features, product functions, product components / general</b>	
product feature	
• halogen-free	No
• PoE capability	Yes
• PoE+ capability	Yes
• silicon-free	Yes
wire length / for Industrial Ethernet	
• with 100BaseTX	85 m
test voltage	
• at AC / core-to-core	2000 V
• at AC / core shield	2000 V
<b>standards, specifications, approvals</b>	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CM, PLTC, SUN RES
UL/ETL style / 600 V Rating	No
certificate of suitability	
• EAC approval	Yes
• CE marking	Yes
• RoHS conformity	Yes
standard for structured cabling	Cat5e
• resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statków (PRS)	No
<b>further information / internet links</b>	
internet link	
• to website: Selection guide for cables and connectors	<a href="https://support.industry.siemens.com/cs/ww/en/view/109766358">https://support.industry.siemens.com/cs/ww/en/view/109766358</a>
• to web page: selection aid TIA Selection Tool	<a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a>
• to web page: SiePortal	<a href="https://sieportal.siemens.com/">https://sieportal.siemens.com/</a>
• to website: Image database	<a href="https://www.automation.siemens.com/bilddb">https://www.automation.siemens.com/bilddb</a>
• to website: CAx-Download-Manager	<a href="https://www.siemens.com/cax">https://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

## security information

### security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit [www.siemens.com/cybersecurity-industry](http://www.siemens.com/cybersecurity-industry). Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under [https://www.siemens.com/cert. \(V4.7\)](https://www.siemens.com/cert. (V4.7))

## Approvals / Certificates

### General Product Approval



[Confirmation](#)



### Test Certificates

### Maritime application

### other

### Environment

#### Miscellaneous



[Confirmation](#)



#### Miscellaneous

[Environmental Confirmations](#)

### Environment



[Environmental Confirmations](#)

last modified:

12/20/2025