


Data sheet

6XV1860-2S

product type designation

product description



PROFIBUS Hybrid Robust Cable

Hybrid cable (data and energy wires), product sold by meter, unassembled

PROFIBUS hybrid robust cable, trailable, welding bead-resistant cable with 2xCU (1.5 mm²) and 2xCU 0.64 mm) shielded, ET 200 sold by the meter, delivery unit max. 1000 m minimum order quantity: 20 m .

Technical Product Detail Page

<https://i.siemens.com/1P6XV1860-2S>

suitability for use

Rugged cable for supplying data and power to ET 200pro under conditions of high mechanical loading. Cable resistance to weld spatter according to HD22.2 S3 / 5

cable designation

02Y(ST)C 1x2x0.65/2.56-150LI LIH-Z 11Y 2x1x1.5 VI FRNC

electrical data

attenuation factor per length

- at 9.6 kHz / maximum 0.004 dB/m
- at 38.4 kHz / maximum 0.004 dB/m
- at 4 MHz / maximum 0.025 dB/m
- at 16 MHz / maximum 0.049 dB/m

impedance

- rated value 150 Ω
- at 9.6 kHz 270 Ω
- at 38.4 kHz 185 Ω
- at 3 MHz ... 20 MHz 150 Ω

relative symmetrical tolerance

- of the characteristic impedance at 9.6 kHz 10 %
- of the characteristic impedance at 38.4 kHz 10 %
- of the characteristic impedance at 3 MHz ... 20 MHz 10 %

loop resistance per length / maximum

138 Ω/km

shield resistance per length / maximum

10 Ω/km

operating voltage / maximum

80 V

capacity per length / at 1 kHz

30 pF/m

operating voltage / RMS value

300 V

conductor cross section / of the power line

1.5 mm²

continuous current / of the power lines

7.5 A

mechanical data

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

number of electrical cores

4

type of electrical connection / FastConnect

No

outer diameter

- of inner conductor 0.67 mm
- of the wire insulation 2.56 mm
- of cable sheath 11 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.5 mm

material

• of the wire insulation	polyethylene (PE)
• of cable sheath	PUR
color	
• of the insulation of data wires	red / green
• of the power line insulation	Black
• of cable sheath	Violet
bending radius	
• with single bend / minimum permissible	44 mm
• with multiple bends / minimum permissible	125 mm
number of bending cycles	3000000; For use in cable carriers, for 3 million bending cycles with a bending radius of 125 mm and an acceleration of 2.5 m/s ²
tensile load / maximum	450 N
weight per length	135 kg/km
ambient conditions	
ambient temperature	
• during operation	-40 ... +75 °C
• during storage	-40 ... +75 °C
• during transport	-40 ... +75 °C
• during installation	-40 ... +75 °C
• note	Electrical properties measured at 20 Cel, verification according to DIN 47250 part 4 respectively DIN VDE 0490
fire behavior	flame-retardant according to IEC 60332-1-2
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	Resistant
• to grease	Resistant
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
• halogen-free	Yes
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; CMX
UL/ETL style / 600 V Rating	No
certificate of suitability	
• EAC approval	Yes
• RoHS conformity	Yes
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAx-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase

customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert.> (V4.7)

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)



[Declaration of Conformity](#)



[Fire safety / Physical security](#)

General Product Approval

other

Environment

[China RoHS](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

last modified:

1/12/2026