




Siemens Low Voltage Circuit Protection Heavy Duty Safety Switch. 3-Pole Non-Fused in a type 3R enclosure (outdoor). Rated 600VAC (200A).

| General technical data                             |                                                 |
|----------------------------------------------------|-------------------------------------------------|
| mechanical service life (operating cycles) typical | 8000                                            |
| fastening method                                   | SURFACE                                         |
| product function note                              |                                                 |
| number of poles                                    | 3                                               |
| suitability for operation                          | DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS |
| Electricity                                        |                                                 |
| ampacity                                           | 200 A                                           |
| supply voltage frequency rated value 50/60 Hz      | Yes                                             |
| Model                                              |                                                 |
| product brand name                                 | SIEMENS                                         |
| product type designation                           | HEAVY DUTY SWITCH                               |
| type of electrical connection                      | MECHANICAL LUGS                                 |
| Mechanical Design                                  |                                                 |
| design of the housing                              | TYPE 3R                                         |
| design of the actuating element                    | SINGLE THROW                                    |
| material                                           | STEEL                                           |
| General product approval                           |                                                 |
| certificate of suitability                         | UL98                                            |



last modified:

10/22/2025



