

DP/AS-Interface F-Link, gateway PROFIBUS DP/AS-i for safety-oriented data transmission from ASIsafe to PROFIBUS-DP-PROFIsafe. Master profile M3/M4 according to AS-i specification V3.0. degree of protection IP20. screw terminals

General technical data		
product designation		PROFIsafe/ASIsafe F-Link
product type designation		DP/AS-i F-Link
protection class IP		IP20
type of electrical connection of the AS-Interface		Screw-type connection
type of voltage supply		via 24 V DC
consumed current		
<ul style="list-style-type: none"> <li>from profile conductors of the AS-Interface</li> <li>— at 24 V with AS-i Power24V maximum</li> </ul>	mA	100
power loss [W]	W	3
insulation voltage rated value	V	500
product feature redundancy capability		No
product function suitable for AS-i Power24V		No
product function		
<ul style="list-style-type: none"> <li>web-based management</li> <li>diagnostics via email</li> <li>galvanic isolation</li> </ul>		No No Yes
display version		
<ul style="list-style-type: none"> <li>as status display by LED</li> <li>as status indication through display</li> </ul>		DEVICE, ASi, BF, SF Dot-matrix display, 2-line
type of configuration of the AS-Interface		Set pushbutton on device, STEP7, GSD, command interface
Communication/ Protocol		
version of the AS-Interface specification		V 3.0
AS-Interface master profile is supported		M4 (in acc. with AS-interface specification V 3.0)
type of data transmission		PROFIBUS
number of interfaces		
<ul style="list-style-type: none"> <li>as AS-Interface</li> <li>according to RS 485</li> <li>according to Industrial Ethernet</li> <li>according to PROFINET</li> <li>according to wireless</li> <li>according to USB</li> <li>other</li> </ul>		1 1 0 0 0 0 0
product component optical interface		No
protocol is supported		
<ul style="list-style-type: none"> <li>ASIsafe (Safety at work) protocol</li> <li>PROFIsafe protocol</li> <li>PROFIBUS protocol</li> <li>PROFINET IO protocol</li> <li>PROFINET CBA protocol</li> <li>TCP/IP</li> <li>SNMP</li> </ul>		Yes Yes Yes No No No No
standard for wireless communication IEEE 802.11		No
Inputs/ Outputs		
number of inputs for AS-Interface maximum		496
number of outputs for AS-Interface maximum		496
number of AS-i devices per AS-Interface maximum		62
bus cycle time of the AS-Interface		

• for 31 devices	ms	5
• for 62 devices	ms	10
access to digital I/O data		via process image/peripheral addresses
access to analog I/O data		via process diagram/peripheral addresses and data record transfer

Mechanical data		
width	mm	45
height	mm	111
depth	mm	124
fastening method		snap-on fastening on 35 mm DIN rail or screw fastening using an additional push-in lug
module format		IP20

Ambient conditions		
ambient temperature		
• if installed on horizontal mounting rail during operation	°C	0 ... 50
• during transport	°C	-40 ... +85
• during storage	°C	-40 ... +85
relative humidity at 25 °C during operation maximum	%	95
installation altitude at height above sea level maximum	m	2 000

Safety related data		
suitability for use safety-related function		Yes
category according to EN 954-1		4
Safety Integrity Level (SIL) according to IEC 61508		SIL 3
SIL Claim Limit (subsystem) according to EN 62061		3
performance level (PL) according to EN ISO 13849-1		e
requirement class according to DIN V 19250		AK7, AK8
explosion protection marking for intrinsic safety of related equipment		
• EEx ia		No
• EEx ib		No
explosion protection category for gas		none
explosion protection category for dust		none

Certificates/ approvals			
General Product Approval	EMV	Functional Safety	Test Certificates



[Type Examination Certificate](#)

[Type Test Certificates/Test Report](#)

other	Environment	Industrial Communication
-------	-------------	--------------------------



[Confirmation](#)

[Environmental Confirmations](#)



#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK3141-1CD10>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK3141-1CD10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK3141-1CD10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RK3141-1CD10&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK3141-1CD10&lang=en)

---

last modified:

9/5/2025 