



Load disconnecter 3LD3, Iu 25 A Main switch 3-pole Rated operating capacity at AC-23 A at 400V 9.0kW Front plate mounting Basic switch with Central hole mounting 22.5mm Toggle drive black 48x48 mm

| Model                                                                               |                                |
|-------------------------------------------------------------------------------------|--------------------------------|
| product brand name                                                                  | SETRON                         |
| product designation                                                                 | Switch disconnecter            |
| design of the product                                                               | Main switch                    |
| display version for switch position indicator manual operation                      | 1 ON - 0 OFF                   |
| type of switch                                                                      | front mounted                  |
| design of the actuating element                                                     | selector switch                |
| color of the actuating element                                                      | black                          |
| design of handle                                                                    | knob-operated mechanism, black |
| type of the driving mechanism motor drive                                           | No                             |
| General technical data                                                              |                                |
| number of poles                                                                     | 3                              |
| number of poles note                                                                | 3                              |
| mechanical service life (operating cycles) typical                                  | 100 000                        |
| electrical endurance (operating cycles)                                             |                                |
| • at AC-23 A at 690 V                                                               | 6 000                          |
| operating frequency maximum                                                         | 50 1/h                         |
| degree of pollution                                                                 | 3                              |
| Voltage                                                                             |                                |
| insulation voltage rated value                                                      | 690 V                          |
| surge voltage resistance rated value                                                | 6 kV                           |
| operating voltage                                                                   |                                |
| • at AC rated value                                                                 | 690 V                          |
| operating frequency rated value                                                     |                                |
| • minimum                                                                           | 50 Hz                          |
| • maximum                                                                           | 60 Hz                          |
| Protection class                                                                    |                                |
| protection class IP                                                                 | IP65                           |
| degree of protection NEMA rating                                                    | 1, 3R, 4X, 12                  |
| protection class IP on the front                                                    | IP65                           |
| Dissipation                                                                         |                                |
| power loss [W] for rated value of the current at AC in hot operating state per pole | 1.1 W                          |
| Main circuit                                                                        |                                |
| operational current                                                                 |                                |
| • at AC-21 at 690 V rated value                                                     | 25 A                           |
| • at AC-21 A at 240 V rated value                                                   | 25 A                           |
| • at AC-21 A at 400 V rated value                                                   | 25 A                           |

|                                                                                                                                                                                                                                                                                                                                              |                                                                      |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at AC-21 A at 440 V rated value</li> <li>• at AC-23 A at 400 V rated value</li> </ul>                                                                                                                                                                                                               | 25 A<br>20 A                                                         |
| <b>operating power</b>                                                                                                                                                                                                                                                                                                                       |                                                                      |
| <ul style="list-style-type: none"> <li>• at AC-23 A at 240 V rated value</li> <li>• at AC-23 A at 400 V rated value</li> <li>• at AC-23 A at 440 V rated value</li> <li>• at AC-23 A at 690 V rated value</li> <li>• at AC-3 at 240 V rated value</li> <li>• at AC-3 at 400 V rated value</li> <li>• at AC-3 at 690 V rated value</li> </ul> | 4 kW<br>10 kW<br>9 kW<br>9 kW<br>4 kW<br>8 kW<br>7.5 kW              |
| <b>Auxiliary circuit</b>                                                                                                                                                                                                                                                                                                                     |                                                                      |
| number of CO contacts for auxiliary contacts                                                                                                                                                                                                                                                                                                 | 0                                                                    |
| number of NC contacts for auxiliary contacts                                                                                                                                                                                                                                                                                                 | 0                                                                    |
| number of NO contacts for auxiliary contacts                                                                                                                                                                                                                                                                                                 | 0                                                                    |
| operating voltage of auxiliary contacts at AC maximum                                                                                                                                                                                                                                                                                        | 500 V                                                                |
| continuous current of the auxiliary contact rated value                                                                                                                                                                                                                                                                                      | 10 A                                                                 |
| insulation voltage of the auxiliary switch rated value                                                                                                                                                                                                                                                                                       | 500 V                                                                |
| <b>Suitability</b>                                                                                                                                                                                                                                                                                                                           |                                                                      |
| suitability for use main switch                                                                                                                                                                                                                                                                                                              | Yes                                                                  |
| suitability for use switch disconnecter                                                                                                                                                                                                                                                                                                      | Yes                                                                  |
| suitability for use EMERGENCY OFF switch                                                                                                                                                                                                                                                                                                     | No                                                                   |
| suitability for use safety switch                                                                                                                                                                                                                                                                                                            | Yes                                                                  |
| suitability for use maintenance/repair switch                                                                                                                                                                                                                                                                                                | Yes                                                                  |
| <b>Product details</b>                                                                                                                                                                                                                                                                                                                       |                                                                      |
| special product feature                                                                                                                                                                                                                                                                                                                      | Can be locked in zero position                                       |
| product feature can be locked into OFF position                                                                                                                                                                                                                                                                                              | Yes                                                                  |
| <b>Accessories</b>                                                                                                                                                                                                                                                                                                                           |                                                                      |
| product extension optional                                                                                                                                                                                                                                                                                                                   |                                                                      |
| <ul style="list-style-type: none"> <li>• motor drive</li> <li>• voltage trigger</li> </ul>                                                                                                                                                                                                                                                   | No<br>No                                                             |
| number of connectable NC contacts for auxiliary contacts attachable maximum                                                                                                                                                                                                                                                                  | 2                                                                    |
| number of connectable NO contacts for auxiliary contacts attachable maximum                                                                                                                                                                                                                                                                  | 4                                                                    |
| number of connectable CO contacts for auxiliary contacts attachable maximum                                                                                                                                                                                                                                                                  | 0                                                                    |
| number of bracket locks maximum                                                                                                                                                                                                                                                                                                              | 2                                                                    |
| hasp thickness of the bracket locks                                                                                                                                                                                                                                                                                                          | 4 ... 6 mm                                                           |
| <b>Short circuit</b>                                                                                                                                                                                                                                                                                                                         |                                                                      |
| conditional short-circuit current with line-side fuse protection                                                                                                                                                                                                                                                                             |                                                                      |
| <ul style="list-style-type: none"> <li>• at 440 V by gG fuse rated value</li> <li>• at 690 V by gG fuse rated value</li> </ul>                                                                                                                                                                                                               | 10 kA<br>6 kA                                                        |
| let-through current with closed switch                                                                                                                                                                                                                                                                                                       |                                                                      |
| <ul style="list-style-type: none"> <li>• at 240 V for combination switch + gG fuse maximum</li> <li>• at 440 V for combination switch + gG fuse maximum</li> <li>• at 690 V for combination switch + gG fuse maximum permissible</li> </ul>                                                                                                  | 3.5 kA<br>3.5 kA<br>4 kA                                             |
| I <sup>2</sup> t value with closed switch                                                                                                                                                                                                                                                                                                    |                                                                      |
| <ul style="list-style-type: none"> <li>• at 240 V for combination switch + gG fuse maximum</li> <li>• at 440 V for combination switch + gG fuse maximum</li> <li>• at 690 V for combination switch + gG fuse maximum</li> </ul>                                                                                                              | 4 kA <sup>2</sup> ·s<br>4 kA <sup>2</sup> ·s<br>4 kA <sup>2</sup> ·s |
| design of the fuse link                                                                                                                                                                                                                                                                                                                      |                                                                      |
| <ul style="list-style-type: none"> <li>• for short-circuit protection of the main circuit required</li> <li>• for short-circuit protection of the auxiliary switch required</li> </ul>                                                                                                                                                       | fuse gL/gG: 25 A<br>fuse gL/gG: 10 A                                 |
| operational current of upstream fuse rated value                                                                                                                                                                                                                                                                                             | 25 A                                                                 |
| <b>according UL</b>                                                                                                                                                                                                                                                                                                                          |                                                                      |
| operational current at AC according to UL 508/UL 60947-4-1 rated value                                                                                                                                                                                                                                                                       | 25 A                                                                 |
| operating voltage at AC at 50/60 Hz according to UL 508/UL 60947-4-1 rated value                                                                                                                                                                                                                                                             | 600 V                                                                |

|                                                                               |      |
|-------------------------------------------------------------------------------|------|
| active power [hp] at AC at 480 V according to UL 508/UL 60947-4-1 rated value | 10   |
| active power [hp] at AC at 600 V according to UL 508/UL 60947-4-1 rated value | 15   |
| short-time withstand current (SCCR) at 600 V according to UL 508/UL 60947-4-1 | 5 kA |
| continuous current of upstream fuse according to UL rated value               | 50 A |
| type of fuse according to UL                                                  | RK5  |

#### Connections

|                                                                       |                                                            |
|-----------------------------------------------------------------------|------------------------------------------------------------|
| AWG number as coded connectable conductor cross section solid maximum |                                                            |
| •                                                                     | 6                                                          |
| •                                                                     | 14                                                         |
| type of connectable conductor cross-sections for copper conductor     |                                                            |
| • solid                                                               | 1x (2.5 to 16 mm <sup>2</sup> )                            |
| • finely stranded with core end processing                            | 1x (2.5...16 mm <sup>2</sup> )                             |
| • stranded                                                            | 1x (2.5 to 16 mm <sup>2</sup> )                            |
| type of connectable conductor cross-sections for auxiliary contacts   |                                                            |
| • solid                                                               | 2x (0.75 ... 2.5 mm <sup>2</sup> ), 1x 4 mm <sup>2</sup>   |
| • finely stranded with core end processing                            | 2x (0.75 ... 1.5 mm <sup>2</sup> ), 1x 2.5 mm <sup>2</sup> |
| • stranded                                                            | 2x (0.75 ... 2.5 mm <sup>2</sup> ), 1x 4 mm <sup>2</sup>   |
| type of electrical connection                                         |                                                            |
| • for main current circuit                                            | box terminal                                               |
| • for auxiliary contacts                                              | Box terminals                                              |

#### Mechanical Design

|                                          |                                     |
|------------------------------------------|-------------------------------------|
| height                                   | 60 mm                               |
| width                                    | 36 mm                               |
| depth                                    | 114 mm                              |
| type of device                           | fixed mounting                      |
| fastening method                         | Built-in unit fixed-mounted version |
| fastening method                         |                                     |
| • 4-hole front mounting                  | No                                  |
| • front mounting with central attachment | Yes                                 |
| • rail mounting                          | No                                  |
| Net Weight                               | 202 g                               |

#### Environmental conditions

|                                      |        |
|--------------------------------------|--------|
| ambient temperature during operation |        |
| • minimum                            | -25 °C |
| • maximum                            | 55 °C  |
| ambient temperature during storage   |        |
| • minimum                            | -25 °C |
| • maximum                            | 55 °C  |

#### Approvals Certificates

|             |                          |
|-------------|--------------------------|
| Environment | General Product Approval |
|-------------|--------------------------|

[Environmental Con-  
firmations](#)

[Environmental Con-  
firmations](#)



[Confirmation](#)

|                          |       |
|--------------------------|-------|
| General Product Approval | other |
|--------------------------|-------|



[Confirmation](#)



#### Further information

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information for data generation and storage**

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<https://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3150-0TK11>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3LD3150-0TK11>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[https://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3LD3150-0TK11](https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD3150-0TK11)

**CAX-Online-Generator**





<https://www.siemens.com/cax>

**Tender specifications**

<https://www.siemens.com/specifications>

**Characteristic curves**

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP='HAUPT'></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>)



last modified:

10/14/2025

