
















Keyed selector switch, metal Maintained C Cam 1NO-1NC left, 1NO-1NC right 3 position Complete device Key type 501CH (standard) Key removable all positions UL file E22655 in Vol. 6 (7) Sec. 13 (2)



product brand name	SIEMENS Pilot Devices
design of the product	Complete unit round
Enclosure	
number of command points	1
delivery state as a kit	No
Actuator	
design of the actuating element	Key-operated switch
product extension optional light source	No
color of the actuating element	silver
material of the actuating element	metal
number of contact modules	2
type of unlocking device	key unlatching
number of switching positions	3
switch position for key distraction	removable in every position
lock make	ILLINOIS
key number	501CH
Front ring	
product component front ring	Yes
design of the front ring	standard
material of the front ring	metal
color of the front ring	chrome
Holder	
material of the holder	Metal
General technical data	
product function positive opening	Yes
product component light source	No
insulation voltage rated value	600 V
degree of pollution	1
type of voltage of the operating voltage	AC/DC
surge voltage resistance rated value	4 kV
protection class IP	IP66
protection class IP of the terminal	IP20
vibration resistance according to IEC 60068-2-6	0 ... 2000 Hz, 1.52 mm displacement (peak-to-peak) max./ 10g max.
operating frequency maximum	600 1/h
thermal current	10 A
Net Weight	4.536 g
operating voltage	
• at AC at 60 Hz rated value	5 ... 600 V
• at DC rated value	5 ... 600 V

Power Electronics		
contact reliability	one incorrect switching operation of 100 million switching operations (5 V, 1 mA)	
Auxiliary circuit		
number of NC contacts for auxiliary contacts	2	
number of NO contacts for auxiliary contacts	2	
operational current at AC-15		
• at 110 V rated value	60 A	
• at 230 V rated value	30 A	
• at 400 V rated value	15 A	
• at 500 V rated value	12 A	
Connections/ Terminals		
type of electrical connection	screw terminal	
type of connectable conductor cross-sections for AWG cables for auxiliary contacts	1x (18 ... 12), 2x (18 ... 16), 2x (16 ... 14), 2x 12	
tightening torque of the screws in the bracket maximum	20 N·m	
tightening torque [lbf·in] with screw-type terminals minimum	8 lbf·in	
Electrical Safety		
touch protection against electrical shock	finger-safe	
Ambient conditions		
ambient temperature		
• during operation	-35 ... +70 °C	
• during storage	-40 ... +85 °C	
Installation/ mounting/ dimensions		
shape of the installation opening	round	
Approvals Certificates		
Environment	General Product Approval	
  Environmental Confirmations Environmental Confirmations  Confirmation		
General Product Approval		
   Miscellaneous  		
EMV	Test Certificates	Maritime application
	Special Test Certificate Type Test Certificates/Test Report	Miscellaneous  
Maritime application		other
  	CCS (China Classification Society)	Confirmation 
other		
Miscellaneous		

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52SC6CEA2>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52SC6CEA2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:52SC6CEA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52SC6CEA2&lang=en

last modified:

10/23/2025 