



SCALANCE XC116, Unmanaged IE switch, 16x 10/100 Mbit/s RJ45 ports, LED diagnostics, error-signaling contact with set pushbutton, redundant power supply
Manual available as a download .

product type designation	
product brand name	SCALANCE
product type designation	XC116
Technical Product Detail Page	https://i.siemens.com/1P6GK5116-0BA00-2AC2
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
<ul style="list-style-type: none"> for network components or terminal equipment 	16; RJ45
interfaces / other	
number of electrical connections	
<ul style="list-style-type: none"> for signaling contact for power supply 	1 1
type of electrical connection	
<ul style="list-style-type: none"> for signaling contact for power supply 	2-pole terminal block 4-pole terminal block
operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> at DC / rated value 	24 V
operational current / of the signaling contacts	
<ul style="list-style-type: none"> at DC / maximum 	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
<ul style="list-style-type: none"> supply voltage / 1 / rated value power loss [W] / 1 / rated value supply voltage / 1 / voltage range consumed current / 1 / maximum type of electrical connection / 1 / for power supply product component / 1 / fusing at power supply input fuse protection type / 1 / at input for supply voltage 	24 V 5.4 W 9.6 ... 31.2 0.45 A 4-pole terminal block Yes 2,5 A / 125 V
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport 	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C
relative humidity	
<ul style="list-style-type: none"> at 25 °C / without condensation / during operation / maximum 	95 %
protection class IP	IP20

design, dimensions and weights	
design	compact
width	120 mm
height	147 mm
depth	125 mm
net weight	0.775 kg
material / of the enclosure	Polycarbonate (PC-GF10)
fastening method	
• 35 mm DIN-rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	Yes
product features, product functions, product components / general	
number of automatically learnable MAC addresses	2048
product functions / management, configuration, engineering	
product function	
• multiport mirroring	No
• CoS	Yes
• switch-managed	No
PROFINET conformity class	A
product functions / redundancy	
product function	
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• EC Declaration of Conformity EN 61010, IEC 61010-1, UL 61010A-1	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4 (Class B)
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEX	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
standards, specifications, approvals / marine classification	
certificate of suitability / shipbuilding approval / note	Certifications marked 'No' are currently under renewal.
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Chinese Classification Society (CCS)	No
• Det Norske Veritas (DNV)	No
• Korean Register of Shipping (KRS)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No

- Polski Rejestr Statkow (PRS) No
- Royal Institution of Naval Architects (RINA) Yes

standards, specifications, approvals / Environmental Product Declaration

Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
<ul style="list-style-type: none"> • total 	441.1 kg
<ul style="list-style-type: none"> • during manufacturing 	47.67 kg
<ul style="list-style-type: none"> • during operation 	392.81999 kg
<ul style="list-style-type: none"> • after end of life 	0.57 kg

product functions / general

laser protection class	LED Class 1
warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022

further information / internet links

internet link	
<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support 	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com

security information

security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>
----------------------	---

Approvals / Certificates

Environmental Product Declaration	
<ul style="list-style-type: none"> • global warming potential [CO2 eq] / during manufacturing • global warming potential [CO2 eq] / during operation • global warming potential [CO2 eq] / after end of life • global warming potential [CO2 eq] / total 	47.67 kg 392.82 kg 0.57 kg 441.1 kg

Environment General Product Approval



[China RoHS](#)



[Declaration of Conformity](#)

General Product Approval EMV



[China RoHS](#)



For use in hazardous locations Maritime application



ATEX



IECEX

[FM](#)

[CCC-Ex](#)



ABS



BUREAU
VERITAS

Maritime application

Industrial Commu-
nication



DNV



LRS

[NK / Nippon Kaiji Ky-
okai](#)



PRS



RINA

[PROFINET](#)

last modified:

4/23/2026