



reversing contactor assembly, AC-3e/AC-3, 95 A, 45 kW / 400 V, 3-pole, 20-33 V AC/DC, 50/60 Hz, screw terminal, electrical and mechanical interlock, auxiliary contacts: 2 x 1 NO, with voltage tap for 3RA27

product brand name	SIRIUS
product designation	Reversing contactor assembly
product type designation	3RA23
manufacturer's article number	• 1 of the supplied contactor 3RT2046-1NB30-0CC0 • 2 of the supplied contactor 3RT2046-1NB30 • of the supplied RS assembly kit 3RA2943-2AA1
General technical data	
size of contactor	S3
product extension auxiliary switch	Yes
shock resistance at rectangular impulse	• at AC 6.7 g / 5 ms, 4.0 g / 10 ms • at DC 6.7 g / 5 ms, 4 g / 10 ms
shock resistance with sine pulse	• at AC 10.6 g / 5 ms, 6.3 g / 10 ms • at DC 10.6 g / 5 ms, 6.3 g / 10 ms
mechanical service life (operating cycles)	• of contactor typical 10 000 000 • of the contactor with added auxiliary switch block typical 10 000 000
reference code according to IEC 81346-2	Q
Substance Prohibitance (day/month/year)	03/01/2017
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1
Net Weight	4.307 kg
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	• during operation -25 ... +60 °C • during storage -55 ... +80 °C
Main circuit	
number of poles for main current circuit	3
number of NO contacts for main contacts	0
number of NC contacts for main contacts	0
operating voltage	• at AC-3 rated value maximum 1 000 V • at AC-3e rated value maximum 1 000 V
operational current	

• at AC-3 — at 400 V rated value — at 500 V rated value — at 690 V rated value • at AC-3e — at 400 V rated value — at 500 V rated value — at 690 V rated value	95 A 95 A 78 A 95 A 95 A 78 A
operating power • at AC-3 — at 400 V rated value — at 500 V rated value — at 690 V rated value • at AC-3e — at 400 V rated value — at 690 V rated value • at AC-4 at 400 V rated value	45 kW 55 kW 75 kW 45 kW 75 kW 45 kW
operating frequency • at AC-3 maximum • at AC-3e maximum	850 1/h 850 1/h
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage 1 at AC • at 50 Hz • at 60 Hz	20 ... 33 V 20 ... 33 V
control supply voltage 1 at DC	20 ... 33 V
operating range factor control supply voltage rated value of magnet coil at AC • at 50 Hz • at 60 Hz	0.8 ... 1.1 0.8 ... 1.1
design of the surge suppressor	with varistor
apparent pick-up power of magnet coil at AC • at 50 Hz • at 60 Hz	163 VA 163 VA
apparent holding power of magnet coil at AC • at 50 Hz • at 60 Hz	3.1 VA 3.1 VA
closing power of magnet coil at DC	76 W
holding power of magnet coil at DC	1.8 W
Auxiliary circuit	
number of NC contacts for auxiliary contacts • per direction of rotation	0
number of NO contacts for auxiliary contacts • per direction of rotation • instantaneous contact	1 2
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor • at 480 V rated value • at 600 V rated value	96 A 77 A
yielded mechanical performance [hp] for 3-phase AC motor • at 200/208 V rated value • at 220/230 V rated value • at 460/480 V rated value • at 575/600 V rated value	30 hp 30 hp 75 hp 75 hp
contact rating of auxiliary contacts according to UL	A600 / Q600
Short-circuit protection	
design of the fuse link • for short-circuit protection of the main circuit — with type of coordination 1 required	gG NH 3NA, DIAZED 5SB, NEOZED 5SE: 355 A

— with type of coordination 2 required		gG NH 3NA, DIAZED 5SB, NEOZED 5SE: 160 A
• for short-circuit protection of the auxiliary switch required		fuse gG: 10 A
Installation/ mounting/ dimensions		
mounting position	+/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface	
fastening method	screw and snap-on mounting onto 35 mm DIN rail	
height	160 mm	
width	150 mm	
depth	152 mm	
required spacing		
• with side-by-side mounting		
— forwards	10 mm	
— backwards	0 mm	
— upwards	10 mm	
— downwards	10 mm	
— at the side	10 mm	
• for grounded parts		
— forwards	10 mm	
— backwards	0 mm	
— upwards	10 mm	
— at the side	10 mm	
— downwards	10 mm	
• for live parts		
— forwards	10 mm	
— backwards	0 mm	
— upwards	10 mm	
— downwards	10 mm	
— at the side	10 mm	
Connections/ Terminals		
type of electrical connection		
• for main current circuit	screw-type terminals	
• for auxiliary and control circuit	screw-type terminals	
• at contactor for auxiliary contacts	Screw-type terminals	
• of magnet coil	Screw-type terminals	
type of connectable conductor cross-sections for main contacts		
• solid or stranded	2x (2.5 ... 16 mm²), 2x (10 ... 50 mm²), 1x (10 ... 70 mm²)	
• finely stranded with core end processing	2x (2.5 ... 35 mm²), 1x (2.5 ... 50 mm²)	
• finely stranded without core end processing	2x (10 ... 35 mm²), 1x (10 ... 50 mm²)	
type of connectable conductor cross-sections		
• for auxiliary contacts		
— solid or stranded	2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²)	
— finely stranded with core end processing	2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²)	
• for AWG cables for auxiliary contacts	2x (20 ... 16), 2x (18 ... 14)	
Safety related data		
product function suitable for safety function	Yes	
Electrical Safety		
protection class IP on the front according to IEC 60529	IP20	
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front	
Communication/ Protocol		
product function bus communication	Yes	
protocol is supported AS-Interface protocol	No	
product function control circuit interface with IO link	No	
Approvals Certificates		
Environment	General Product Approval	Test Certificates

[Environmental Con-
firmations](#)



[Type Test Certifi-
cates/Test Report](#)

Maritime application



other

[Confirmation](#)

[Confirmation](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2346-8XE30-1NB3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2346-8XE30-1NB3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)




https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2346-8XE30-1NB3&lang=en


Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2346-8XE30-1NB3>

Characteristic curves

https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>





last modified:

4/4/2026 