



\*\*\*phase-out type\*\*\* solid-state contactor 1-phase 3RF2 AC 15 / 12 A / 40 °C 24-230 V / 24 V DC instantaneous switching

|                                                                                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| product brand name                                                                                                                                                                                                                                                                                      | SIRIUS                                                                                                                                                                                                                                           |
| product designation                                                                                                                                                                                                                                                                                     | solid-state contactor                                                                                                                                                                                                                            |
| design of the product                                                                                                                                                                                                                                                                                   | 1-pole                                                                                                                                                                                                                                           |
| product type designation                                                                                                                                                                                                                                                                                | 3RF23                                                                                                                                                                                                                                            |
| manufacturer's article number                                                                                                                                                                                                                                                                           |                                                                                                                                                                                                                                                  |
| <ul style="list-style-type: none"> <li>_1 of the accessories that can be ordered</li> <li>_2 of the accessories that can be ordered</li> <li>_3 of the accessories that can be ordered</li> <li>_4 of the accessories that can be ordered</li> <li>_5 of the accessories that can be ordered</li> </ul> | <a href="#">3RF2900-3PA88</a><br><a href="#">3RF2920-0HA13</a><br><a href="#">3RF2900-0EA18</a><br><a href="#">3RF2920-0GA13</a><br><a href="#">3RF2920-0FA08</a>                                                                                |
| product designation                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                                  |
| <ul style="list-style-type: none"> <li>_1 of the accessories that can be ordered</li> <li>_2 of the accessories that can be ordered</li> <li>_3 of the accessories that can be ordered</li> <li>_4 of the accessories that can be ordered</li> <li>_5 of the accessories that can be ordered</li> </ul> | terminal cover<br>power regulator<br>converter<br>load monitoring<br>load monitoring, basis                                                                                                                                                      |
| General technical data                                                                                                                                                                                                                                                                                  |                                                                                                                                                                                                                                                  |
| product function                                                                                                                                                                                                                                                                                        | instantaneous switching                                                                                                                                                                                                                          |
| power loss [W] for rated value of the current                                                                                                                                                                                                                                                           |                                                                                                                                                                                                                                                  |
| <ul style="list-style-type: none"> <li>at AC in hot operating state</li> <li>at AC in hot operating state per pole</li> <li>without load current share typical</li> </ul>                                                                                                                               | 20 W<br>20 W<br>0.4 W                                                                                                                                                                                                                            |
| insulation voltage rated value                                                                                                                                                                                                                                                                          | 600 V                                                                                                                                                                                                                                            |
| degree of pollution                                                                                                                                                                                                                                                                                     | 3                                                                                                                                                                                                                                                |
| surge voltage resistance of main circuit rated value                                                                                                                                                                                                                                                    | 6 kV                                                                                                                                                                                                                                             |
| protection class IP                                                                                                                                                                                                                                                                                     | IP20                                                                                                                                                                                                                                             |
| protection class IP on the front according to IEC 60529                                                                                                                                                                                                                                                 | IP20                                                                                                                                                                                                                                             |
| shock resistance according to IEC 60068-2-27                                                                                                                                                                                                                                                            | 15 g / 11 ms                                                                                                                                                                                                                                     |
| vibration resistance according to IEC 60068-2-6                                                                                                                                                                                                                                                         | 2 g                                                                                                                                                                                                                                              |
| reference code according to IEC 81346-2                                                                                                                                                                                                                                                                 | Q                                                                                                                                                                                                                                                |
| Substance Prohibitance (day/month/year)                                                                                                                                                                                                                                                                 | 05/28/2009                                                                                                                                                                                                                                       |
| SVHC substance name                                                                                                                                                                                                                                                                                     | Lead CAS-No. 7439-92-1<br>Lead monoxide (lead oxide) CAS-No. 1317-36-8<br>2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5<br>Melamine CAS-No. 108-78-1<br>Dibutylbis(pentane-2,4-dionato-O,O')tin CAS-No. 22673-19-4 |
| Net Weight                                                                                                                                                                                                                                                                                              | 0.165 g                                                                                                                                                                                                                                          |
| Main circuit                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                  |
| number of poles for main current circuit                                                                                                                                                                                                                                                                | 1                                                                                                                                                                                                                                                |

|                                                                                                                                                                                                                                                                       |                                                                                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| number of NO contacts for main contacts                                                                                                                                                                                                                               | 1                                                                                                                                                                               |
| number of NC contacts for main contacts                                                                                                                                                                                                                               | 0                                                                                                                                                                               |
| type of voltage of the operating voltage                                                                                                                                                                                                                              | AC                                                                                                                                                                              |
| operating voltage <ul style="list-style-type: none"> <li>at AC <ul style="list-style-type: none"> <li>at 50 Hz rated value</li> <li>at 60 Hz rated value</li> </ul> </li> </ul>                                                                                       | 24 ... 230 V<br>24 ... 230 V                                                                                                                                                    |
| operating frequency rated value                                                                                                                                                                                                                                       | 50 ... 60 Hz                                                                                                                                                                    |
| operating range relative to the operating voltage at AC <ul style="list-style-type: none"> <li>at 50 Hz</li> <li>at 60 Hz</li> </ul>                                                                                                                                  | 20 ... 253 V<br>20 ... 253 V                                                                                                                                                    |
| operational current <ul style="list-style-type: none"> <li>at AC-1 at 400 V rated value</li> <li>at AC-51 rated value</li> <li>at AC-51 according to IEC 60947-4-3</li> <li>according to UL 508 rated value</li> </ul>                                                | 20 A<br>20 A<br>13.2 A<br>12 A                                                                                                                                                  |
| operational current minimum                                                                                                                                                                                                                                           | 500 mA                                                                                                                                                                          |
| rate of voltage rise at the thyristor for main contacts maximum permissible                                                                                                                                                                                           | 1 000 V/ $\mu$ s                                                                                                                                                                |
| blocking voltage at the thyristor for main contacts maximum permissible                                                                                                                                                                                               | 800 V                                                                                                                                                                           |
| reverse current of the thyristor                                                                                                                                                                                                                                      | 10 mA                                                                                                                                                                           |
| derating temperature                                                                                                                                                                                                                                                  | 40 °C                                                                                                                                                                           |
| surge current resistance rated value                                                                                                                                                                                                                                  | 600 A                                                                                                                                                                           |
| I <sup>2</sup> t value maximum                                                                                                                                                                                                                                        | 1 800 A <sup>2</sup> ·s                                                                                                                                                         |
| <b>Control circuit/ Control</b>                                                                                                                                                                                                                                       |                                                                                                                                                                                 |
| type of voltage of the control supply voltage                                                                                                                                                                                                                         | DC                                                                                                                                                                              |
| control supply voltage 1 at DC rated value maximum permissible                                                                                                                                                                                                        | 30 V                                                                                                                                                                            |
| control supply voltage 1 at DC                                                                                                                                                                                                                                        | 15 ... 24 V                                                                                                                                                                     |
| control supply voltage at DC <ul style="list-style-type: none"> <li>initial value for signal &lt;1&gt; detection</li> <li>full-scale value for signal&lt;0&gt; recognition</li> </ul>                                                                                 | 15 V<br>5 V                                                                                                                                                                     |
| control current at minimum control supply voltage <ul style="list-style-type: none"> <li>at DC</li> </ul>                                                                                                                                                             | 13 mA                                                                                                                                                                           |
| control current at DC rated value                                                                                                                                                                                                                                     | 15 mA                                                                                                                                                                           |
| ON-delay time                                                                                                                                                                                                                                                         | 1 ms                                                                                                                                                                            |
| OFF-delay time                                                                                                                                                                                                                                                        | 1 ms; additionally max. one half-wave                                                                                                                                           |
| <b>Installation/ mounting/ dimensions</b>                                                                                                                                                                                                                             |                                                                                                                                                                                 |
| fastening method side-by-side mounting                                                                                                                                                                                                                                | Yes                                                                                                                                                                             |
| fastening method                                                                                                                                                                                                                                                      | screw fixing and snap-on mounting on standard mounting rail 35 mm according to IEC 60715                                                                                        |
| design of the thread of the screw for securing the equipment                                                                                                                                                                                                          | M4                                                                                                                                                                              |
| height                                                                                                                                                                                                                                                                | 95 mm                                                                                                                                                                           |
| width                                                                                                                                                                                                                                                                 | 22.5 mm                                                                                                                                                                         |
| depth                                                                                                                                                                                                                                                                 | 120 mm                                                                                                                                                                          |
| <b>Connections/ Terminals</b>                                                                                                                                                                                                                                         |                                                                                                                                                                                 |
| product component removable terminal for auxiliary and control circuit                                                                                                                                                                                                | Yes                                                                                                                                                                             |
| type of electrical connection <ul style="list-style-type: none"> <li>for main current circuit</li> <li>for auxiliary and control circuit</li> </ul>                                                                                                                   | screw-type terminals<br>screw-type terminals                                                                                                                                    |
| type of connectable conductor cross-sections <ul style="list-style-type: none"> <li>for main contacts <ul style="list-style-type: none"> <li>solid</li> <li>finely stranded with core end processing</li> </ul> </li> <li>for AWG cables for main contacts</li> </ul> | 2x (1.5 ... 2.5 mm <sup>2</sup> ), 2x (2.5 ... 6 mm <sup>2</sup> )<br>2x (1 ... 2.5 mm <sup>2</sup> ), 2x (2.5 ... 6 mm <sup>2</sup> ), 1x 10 mm <sup>2</sup><br>2x (14 ... 10) |
| connectable conductor cross-section for main contacts <ul style="list-style-type: none"> <li>solid or stranded</li> </ul>                                                                                                                                             | 1.5 ... 6 mm <sup>2</sup>                                                                                                                                                       |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |                                                                                                                                                                                                                                  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>finely stranded with core end processing</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | 1 ... 10 mm <sup>2</sup>                                                                                                                                                                                                         |
| <b>type of connectable conductor cross-sections</b> <ul style="list-style-type: none"> <li>for auxiliary and control contacts <ul style="list-style-type: none"> <li>solid</li> <li>finely stranded with core end processing</li> <li>finely stranded without core end processing</li> </ul> </li> <li>for AWG cables for auxiliary and control contacts</li> </ul>                                                                                                                                                                                                                                                                             | 1x (0.5 ... 2.5 mm <sup>2</sup> ), 2x (0.5 ... 1 mm <sup>2</sup> )<br>1x (0.5 ... 2.5 mm <sup>2</sup> ), 2x (0.5 ... 1 mm <sup>2</sup> )<br>1x (0.5 ... 2.5 mm <sup>2</sup> ), 2x (0.5 ... 1 mm <sup>2</sup> )<br>1x (20 ... 12) |
| <b>AWG number as coded connectable conductor cross section for main contacts</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | 10 ... 14                                                                                                                                                                                                                        |
| <b>tightening torque</b> <ul style="list-style-type: none"> <li>for main contacts with screw-type terminals</li> <li>for auxiliary and control contacts with screw-type terminals</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                    | 2 ... 2.5 N·m<br>0.5 ... 0.6 N·m                                                                                                                                                                                                 |
| <b>tightening torque [lbf·in]</b> <ul style="list-style-type: none"> <li>for main contacts with screw-type terminals</li> <li>for auxiliary and control contacts with screw-type terminals</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                           | 18 ... 22 lbf·in<br>4.5 ... 5.3 lbf·in                                                                                                                                                                                           |
| <b>design of the thread of the connection screw</b> <ul style="list-style-type: none"> <li>for main contacts</li> <li>of the auxiliary and control contacts</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | M4<br>M3                                                                                                                                                                                                                         |
| <b>stripped length of the cable</b> <ul style="list-style-type: none"> <li>for main contacts</li> <li>for auxiliary and control contacts</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | 10 mm<br>7 mm                                                                                                                                                                                                                    |
| <b>UL/CSA ratings</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                                                                                                                                                                                  |
| <b>operational current according to UL 508 rated value</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | 12 A                                                                                                                                                                                                                             |
| <b>Electrical Safety</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                  |
| <b>touch protection on the front according to IEC 60529</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | finger-safe, for vertical contact from the front                                                                                                                                                                                 |
| <b>Ambient conditions</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                                                                                                                                                                                                                  |
| installation altitude at height above sea level maximum                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | 1 000 m                                                                                                                                                                                                                          |
| <b>ambient temperature</b> <ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | -25 ... +60 °C<br>-55 ... +80 °C                                                                                                                                                                                                 |
| <b>Electromagnetic compatibility</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                  |
| <b>conducted interference</b> <ul style="list-style-type: none"> <li>due to burst according to IEC 61000-4-4</li> <li>due to conductor-earth surge according to IEC 61000-4-5</li> <li>due to conductor-conductor surge according to IEC 61000-4-5</li> <li>due to high-frequency radiation according to IEC 61000-4-6</li> </ul>                                                                                                                                                                                                                                                                                                               | 2 kV / 5 kHz, behavior criterion 2<br>2 kV, behavior criterion 2<br>1 kV, behavior criterion 2<br>140 dBuV in the frequency range 0.15 ... 80 MHz, behavior criterion 1                                                          |
| <b>field-based interference according to IEC 61000-4-3</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | 80 MHz ... 1 GHz 10 V/m, behavior criterion 1                                                                                                                                                                                    |
| <b>electrostatic discharge according to IEC 61000-4-2</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | 4 kV contact discharging / 8 kV air discharging, behavior criterion 2                                                                                                                                                            |
| <b>conducted HF interference emissions according to CISPR11</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | Class A for industrial environment                                                                                                                                                                                               |
| <b>field-bound HF interference emission according to CISPR11</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | Class B for the domestic, business and commercial environments                                                                                                                                                                   |
| <b>Short-circuit protection, design of the fuse link</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                  |
| <b>manufacturer's article number</b> <ul style="list-style-type: none"> <li>of gS fuse for semiconductor protection at NH design usable</li> <li>of full range R fuse link for semiconductor protection at cylindrical design usable</li> <li>of back-up R fuse link for semiconductor protection at NH design usable</li> <li>of back-up R fuse link for semiconductor protection at cylindrical design 10 x 38 mm usable</li> <li>of back-up R fuse link for semiconductor protection at cylindrical design 14 x 51 mm usable</li> <li>of back-up R fuse link for semiconductor protection at cylindrical design 22 x 58 mm usable</li> </ul> | <a href="#">3NE1814-0</a><br><a href="#">5SE1325</a><br><a href="#">3NE8015-1</a><br><a href="#">3NC1032</a><br><a href="#">3NC1450</a><br><a href="#">3NC2263</a>                                                               |
| <b>manufacturer's article number of the gG fuse</b> <ul style="list-style-type: none"> <li>at NH design usable</li> <li>at cylindrical design 10 x 38 mm usable</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | <a href="#">3NA6807</a><br><a href="#">3NW6007-1</a>                                                                                                                                                                             |

- at cylindrical design 14 x 51 mm usable
- at cylindrical design 22 x 58 mm usable
- at cylindrical design 22 x 58 mm usable note

[3NW6107-1](#)

[3NW6207-1: These fuses have a smaller rated current than the semiconductor relays](#)

These fuses have a smaller rated current than the semiconductor relays

manufacturer's article number

- of DIAZED fuse usable
- of NEOZED fuse usable

[5SB2711](#)

[5SE2320](#)

## Approvals Certificates

| Environment | General Product Approval |
|-------------|--------------------------|
|-------------|--------------------------|

[Environmental Confirmations](#)



| EMV | Test Certificates | other |
|-----|-------------------|-------|
|-----|-------------------|-------|



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

[Confirmation](#)

[Miscellaneous](#)

[Confirmation](#)

| other | Railway |
|-------|---------|
|-------|---------|



[Special Test Certificate](#)

## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RF2320-1BA02>

Cax online generator



<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RF2320-1BA02>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RF2320-1BA02>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RF2320-1BA02&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RF2320-1BA02&lang=en)





last modified:

4/4/2026