



Positively driven coupling relay in industrial enclosure 4 NO contacts / 1 NC contact
24 V to 240 V AC/DC SIL 2 / PL c Screw terminals

product brand name	SIRIUS
product designation	force-guided coupling relay
design of the product	fail-safe up to SIL 2/PL c
product type designation	3RQ1
General technical data	
product feature protective coating on printed-circuit board	No
consumed active power	2.3 W
insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value	300 V
degree of pollution	3
surge voltage resistance rated value	4 kV
shock resistance	
• according to IEC 60068-2-27	11 g / 15 ms
vibration resistance	
• according to IEC 60068-2-6	10 ... 55 Hz: 0.35 mm
operating frequency maximum	360 1/h
switching behavior	monostable
mechanical service life (operating cycles) typical	10 000 000
thermal current of the switching element with contacts maximum	5 A
reference code according to IEC 81346-2	K
Substance Prohibitance (day/month/year)	05/31/2018
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol CAS-No. 119-47-1 4,4'-isopropylidenediphenol (Bisphenol A, BPA) CAS-No. 80-05-7
Net Weight	0.18 kg
Product Function	
suitability for operation device connector 3ZY12	No
Control circuit/ Control	
control supply voltage at AC	
• at 50 Hz rated value	24 ... 240 V
• at 50 Hz	24 ... 240 V
• at 60 Hz rated value	24 ... 240 V
• at 60 Hz	24 ... 240 V
control supply voltage at DC rated value	24 ... 240 V
control supply voltage at DC	24 ... 240 V
operating range factor control supply voltage rated value at DC	

initial value	0.7
full-scale value	1.1
operating range factor control supply voltage rated value at AC at 50 Hz	
initial value	0.85
full-scale value	1.1
operating range factor control supply voltage rated value at AC at 60 Hz	
initial value	0.85
full-scale value	1.1
ON-delay time	
at AC maximum	50 ms
at DC maximum	50 ms
OFF-delay time maximum	60 ms
Switching Function	
design of the switching function	NC contact and NO contact
Mechanical data	
product component plug-in socket	No
Short-circuit protection	
design of the fuse link for short-circuit protection of the auxiliary switch required	fuse gL/gG: 6 A
Auxiliary circuit	
material of switching contacts	AgSnO ₂ + Au flash
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	4
number of CO contacts for auxiliary contacts	0
type of voltage	AC/DC
Inputs/ Outputs	
output current minimum	10 mA
ampacity of the output relay at AC-15	
at 250 V at 50/60 Hz	1.5 A
ampacity of the output relay at DC-13	
at 24 V	1 A
at 125 V	0.2 A
at 250 V	0.1 A
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	ambience A (industrial sector)
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
due to burst according to IEC 61000-4-4	2 kV
due to conductor-earth surge according to IEC 61000-4-5	2 kV (line to ground)
due to conductor-conductor surge according to IEC 61000-4-5	1 kV (line to line)
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	4 kV contact discharging, 8 kV air discharging
Display	
product component LED	Yes
Safety related data	
product function	
positively driven operation according to IEC 60947-5-1	Yes
suitability for use	
safety-related switching on	No
safety-related switching OFF	Yes
safe state	safe shutdown
test wear-related service life necessary	Yes
stop category according to IEC 60204-1	0
MTTFd	470 a
IEC 62061	
Safety Integrity Level (SIL)	
according to IEC 62061	SIL 2

ISO 13849	
performance level (PL) according to ISO 13849-1	PL c
category according to ISO 13849-1	1
device type according to ISO 13849-1	1
overdimensioning according to ISO 13849-2 necessary	No
IEC 61508	
Safety Integrity Level (SIL) according to IEC 61508	SIL 2
safety device type according to IEC 61508-2	Type A
PFHD with high demand rate according to IEC 61508	9.5E-7 1/h
PFDavg with low demand rate according to IEC 61508	0.002
Safe failure fraction (SFF)	85 %
hardware fault tolerance according to IEC 61508	0
T1 value of service life according to IEC 61508	20 a
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes
type of electrical connection	screw terminal
wire length at DC maximum	2 000 m
type of connectable conductor cross-sections - solid - finely stranded with core end processing - for AWG cables solid	1x (0.5 ... 4 mm ²), 2x (0.5 ... 2.5 mm ²) 1x (0.5 ... 4 mm ²), 2x (0.5 ... 1.5 mm ²) 1x (20 ... 12), 2x (20 ... 14)
connectable conductor cross-section - solid - finely stranded with core end processing maximum - finely stranded without core end processing minimum	0.5 ... 4 mm ² 4 mm ² 0.5 mm ²
AWG number as coded connectable conductor cross section - solid - stranded	12 ... 20 12 ... 20
tightening torque with screw-type terminals	0.6 ... 0.8 N·m
stripped length of the cable for auxiliary and control contacts	10 mm
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting onto 35 mm DIN rail
height	100 mm
width	22.5 mm
depth	90 mm
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature - during operation - during storage - during transport	-25 ... +60 °C -40 ... +80 °C -40 ... +80 °C
relative humidity during operation	10 ... 95 %
Approvals Certificates	
Environment	General Product Approval

[Environmental Confirmations](#)



[TUEV](#)



General Product Approval	EMV	Maritime application	other	Railway
--------------------------	-----	----------------------	-------	---------



[Confirmation](#)



[Confirmation](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RQ1000-1LW00>

Cax online generator


<https://support.automation.siemens.com/WW/CAxorder/default.aspx?lang=en&mlfb=3RQ1000-1LW00>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RQ1000-1LW00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RQ1000-1LW00&lang=en





last modified:

5/16/2026 