

SIMATIC HMI KP300 Basic mono PN, Basic Panel, key operation, 3" FSTN LCD display, black/white, PROFINET interface, configurable from WinCC Basic V11/STEP 7 Basic V11, contains open-source software, which is provided free of charge see enclosed CD




Figure similar

General information	
Product type designation	KP300 Basic mono PN
Display	
Design of display	FSTN
Screen diagonal	3.6 in
Display width	87 mm
Display height	31 mm
Number of colors	4; backlit display only (white, red, green, yellow)
Resolution (pixels)	
• Horizontal image resolution	240 pixel
• Vertical image resolution	80 pixel
Backlighting	
• MTBF backlighting (at 25 °C)	50 000 h
• Backlight dimmable	No
Control elements	
Keyboard fonts	
• Function keys	
— Number of function keys	10
— Number of function keys with LEDs	0
• Keys with LED	No
• System keys	Yes
• Numeric keyboard	Yes; Keyboard
• alphanumeric keyboard	Yes; Keyboard
Touch operation	
• Design as touch screen	No; without
Installation type/mounting	
Mounting position	vertical
Rack mounting	No
Wall mounting/direct mounting	No
Mounting in portrait format possible	No
Mounting in landscape format possible	Yes
maximum permissible angle of inclination without external ventilation	35°
Supply voltage	
Type of supply voltage	DC
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V

Input current	
Current consumption (rated value)	0.1 A
Starting current inrush I <sup>2</sup> t	0.5 A <sup>2</sup> ·s
Power	
Active power input, typ.	3 W
Processor	
Processor type	RISC 32 bit
Memory	
Flash	Yes
RAM	Yes
Memory available for user data	1 Mbyte
Type of output	
Acoustics	
• Buzzer	No
• Speaker	No
Time of day	
Clock	
• Hardware clock (real-time)	No
• Software clock	Yes
• retentive	No
• synchronizable	Yes
Interfaces	
Number of industrial Ethernet interfaces	1
Number of RS 485 interfaces	0
Number of RS 422 interfaces	0
Number of RS 232 interfaces	0
Number of USB interfaces	0
Number of 20 mA interfaces (TTY)	0
Number of parallel interfaces	0
Number of other interfaces	0
Number of SD card slots	0
With software interfaces	No
Industrial Ethernet	
• Industrial Ethernet status LED	2
Protocols	
PROFINET	Yes
Supports protocol for PROFINET IO	No
IRT	No
PROFIBUS	No
EtherNet/IP	Yes
MPI	No
Protocols (Ethernet)	
• TCP/IP	Yes
• DHCP	Yes
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
WEB characteristics	
• HTTP	No
• HTML	No
Further protocols	
• CAN	No
• MODBUS	Yes; Modicon (MODBUS TCP/IP)
Interrupts/diagnostics/status information	
Diagnoses	
• Diagnostic information readable	No
EMC	
Emission of radio interference acc. to EN 55 011	

<ul style="list-style-type: none"> <li>• Limit class A, for use in industrial areas</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Limit class B, for use in residential areas</li> </ul>	No
<b>Degree and class of protection</b>	
IP (at the front)	IP65
IP (rear)	IP20
NEMA (front)	
<ul style="list-style-type: none"> <li>• Enclosure Type 4 at the front</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Enclosure Type 4x at the front</li> </ul>	Yes
<b>Standards, approvals, certificates</b>	
CE mark	Yes
cULus	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
<b>Use in hazardous areas</b>	
<ul style="list-style-type: none"> <li>• ATEX Zone 2</li> </ul>	No
<ul style="list-style-type: none"> <li>• ATEX Zone 22</li> </ul>	No
<ul style="list-style-type: none"> <li>• cULus Class I Zone 1</li> </ul>	No
<ul style="list-style-type: none"> <li>• cULus Class I Zone 2, Division 2</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• FM Class I Division 2</li> </ul>	No
<b>Marine approval</b>	
<ul style="list-style-type: none"> <li>• Germanischer Lloyd (GL)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• American Bureau of Shipping (ABS)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Bureau Veritas (BV)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Det Norske Veritas (DNV)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Lloyds Register of Shipping (LRS)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Nippon Kaiji Kyokai (Class NK)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Polski Rejestr Statkow (PRS)</li> </ul>	No
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
Operation (vertical installation)	
— For vertical installation, min.	0 °C
— For vertical installation, max.	50 °C
Operation (max. tilt angle)	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, max.	40 °C
<b>Ambient temperature during storage/transportation</b>	
<ul style="list-style-type: none"> <li>• min.</li> </ul>	-20 °C
<ul style="list-style-type: none"> <li>• max.</li> </ul>	60 °C
<b>Relative humidity</b>	
<ul style="list-style-type: none"> <li>• Operation, max.</li> </ul>	90 %; no condensation
<b>Operating systems</b>	
proprietary	Yes
pre-installed operating system	
<ul style="list-style-type: none"> <li>• Windows CE</li> </ul>	No
<b>Configuration</b>	
Message indicator	Yes
Alarm system (incl. buffer and acknowledgment)	Yes
Process value display (output)	Yes
Process value default (input) possible	Yes
Recipe management	Yes
<b>Configuration software</b>	
<ul style="list-style-type: none"> <li>• STEP 7 Basic (TIA Portal)</li> </ul>	Yes; via integrated WinCC Basic (TIA Portal)
<ul style="list-style-type: none"> <li>• STEP 7 Professional (TIA Portal)</li> </ul>	Yes; via integrated WinCC Basic (TIA Portal)
<ul style="list-style-type: none"> <li>• WinCC flexible Compact</li> </ul>	No
<ul style="list-style-type: none"> <li>• WinCC flexible Standard</li> </ul>	No
<ul style="list-style-type: none"> <li>• WinCC flexible Advanced</li> </ul>	No
<ul style="list-style-type: none"> <li>• WinCC Basic (TIA Portal)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• WinCC Comfort (TIA Portal)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• WinCC Advanced (TIA Portal)</li> </ul>	Yes

• WinCC Professional (TIA Portal)	Yes
<b>Languages</b>	
Online languages	
• Number of online/runtime languages	5
Project languages	
• Languages per project	32
<b>Functionality under WinCC (TIA Portal)</b>	
Libraries	Yes
Applications/options	none
• Web browser	No
• SIMATIC WinCC Sm@rtServer	No
Task planner	
• time-controlled	No
• task-controlled	Yes
Help system	Yes
• Number of characters per info text	320
<b>Message system</b>	
• Number of alarm classes	32
• Bit messages	Yes
— Number of bit messages	200
• Analog messages	Yes
— Number of analog messages	15
• System messages HMI	Yes
• System event, more (SIMATIC S7, SINUMERIK, SIMOTION, ...)	No
• Number of characters per message	80
• Number of process values per message	8
• Message indicator	Yes
• Message buffer	
— Number of entries	256
— Circulating buffer	Yes
— retentive	Yes
— maintenance-free	Yes
<b>Recipe management</b>	
• Number of recipes	5
• Data records per recipe	20
• Entries per data record	20
• Size of internal recipe memory	40 kbyte
• Recipe memory expandable	No
<b>Variables</b>	
• Number of variables per device	250
• Number of variables per screen	30
• Limit values	Yes
• Multiplexing	Yes
• Structures	No
• Arrays	Yes
<b>Images</b>	
• Number of configurable images	50
• Permanent window/default	Yes
• Global image	Yes
• Image selection by PLC	Yes
• Image number in the PLC	Yes
<b>Image objects</b>	
• Number of objects per image	30
• Text fields	Yes
• I/O fields	Yes
• Graphic I/O fields (graphics list)	Yes
• Symbolic I/O fields (text list)	Yes
• Date/time fields	Yes

• Switches	Yes
• Buttons	Yes
• Graphic display	Yes
• Icons	Yes
• Geometric objects	Yes
<b>Complex image objects</b>	
• Number of complex objects per screen	5
• Alarm view	Yes
• Trend view	Yes
• User view	Yes
• Status/control	No
• Sm@rtClient view	No
• Recipe view	Yes
• f(x) trend view	No
• System diagnostics view	No
• Media Player	No
• Bar graphs	Yes
• Sliders	No
• Pointer instruments	No
• Analog/digital clock	No
<b>Lists</b>	
• Number of text lists per project	150
• Number of entries per text list	30
• Number of graphics lists per project	100
• Number of entries per graphics list	30
<b>Archiving</b>	
• Number of archives per device	0
<b>Security</b>	
• Number of user groups	50
• Number of user rights	32
• Number of users	50
• Password export/import	No
• SIMATIC Logon	No
<b>Character sets</b>	
• Keyboard fonts — US English	Yes
<b>Transfer (upload/download)</b>	
• MPI/PROFIBUS DP	No
• USB	No
• Ethernet	Yes
• using external storage medium	No
<b>Process coupling</b>	
• S7-1200	Yes
• S7-1500	Yes
• S7-200	Yes
• S7-300/400	Yes
• LOGO!	Yes
• WinAC	Yes
• SINUMERIK	No
• SIMOTION	No
• Allen Bradley (EtherNet/IP)	Yes
• Allen Bradley (DF1)	No
• Mitsubishi (MC TCP/IP)	Yes
• Mitsubishi (FX)	No
• OMRON (FINS TCP)	No
• OMRON (LINK/Multilink)	No
• Modicon (Modbus TCP/IP)	Yes
• Modicon (Modbus)	No
<b>Service tools/configuration aids</b>	

- Backup/Restore manually Yes
- Backup/Restore automatically No
- Simulation Yes
- Device switchover Yes

#### Peripherals/Options

Printer	No
SIMATIC HMI MM memory card: Multi Media Card	No
SIMATIC HMI SD memory card: Secure Digital memory card	No
USB memory	No

#### Mechanics/material

Enclosure material (front)	
• Plastic	Yes
• Aluminum	No
• Stainless steel	No

#### Dimensions

Width of the housing front	165 mm
Height of housing front	97 mm
Mounting cutout, width	149 mm
Mounting cutout, height	82 mm
mounting depth	30 mm

#### Weights

Weight (without packaging)	0.25 kg
Weight (with packaging)	0.38 kg

#### Classifications

	Version	Classification
eClass	14	27-33-02-01
eClass	12	27-33-02-01
eClass	9.1	27-33-02-01
eClass	9	27-33-02-01
eClass	8	27-24-23-02
eClass	7.1	27-24-23-02
eClass	6	27-24-23-02
ETIM	10	EC001412
ETIM	9	EC001412
ETIM	8	EC001412
ETIM	7	EC001412

#### Approvals / Certificates

##### General Product Approval



[Miscellaneous](#)

[Manufacturer Declaration](#)



##### General Product Approval

##### Maritime application



[China RoHS](#)



[NK / Nippon Kaiji Kyokai](#)

##### Maritime application

[CCS \(China Classification Society\)](#)

---

last modified:

3/12/2024 