



SIMATIC IPC PX-32A 19" ST Singletouch 4 x USB 3.2 (back), Ethernet (10/100/1000) Intel Xeon W-11155MLE (1.8/3.1 GHz, 4C/8T); 8 GB; M.2 SSD 256 GB Eco; without 2nd mass storage; Windows 10 IoT Enterprise 2021 LTSC for Celeron processors, W-11155MLE, W-11555MLE; without option 1 USB restore stick with D&D and software image (if selected) 9-36 V DC industrial power supply (wide range)

General information	
Product type designation	PX-32A
Display	
Design of display	19" TFT touch
Screen diagonal	19.1 in
Resolution (pixels)	
• Horizontal image resolution	1 366 pixel
• Vertical image resolution	768 pixel
Backlighting	
• MTBF backlighting (at 25 °C)	50 000 h
Control elements	
Keyboard	
• Function keys	No
• alphanumeric keyboard	No
Touch operation	
• Design as touch screen	Yes
Installation type/mounting	
Mounting	For horizontal and vertical mounting
Design	Panel PC, built-in unit
central design	Yes
distributed design	No
Mounting in portrait format possible	No
Supply voltage	
Type of supply voltage	9 - 36 V DC
Mains buffering	
• Mains/voltage failure stored energy time	20 ms
Processor	
Processor type	Intel® Celeron 6600HLE (2.1 GHz, 2C/2T) Intel® Xeon W-11155MLE (1.8/3.1 GHz, 4C/8T) Intel® Xeon W-11555MLE (1.9/4.4 GHz, 6C/12T) Intel® Xeon W-11865MLE (1.5/4.5 GHz, 8C/16T)
Chipset	Intel® RM590E
Graphic	
Graphics controller	Intel® UHD Graphics 16 EUs (for Intel® Celeron® 6600HLE and Intel® Xeon® W-11155MLE) / Intel® UHD Graphics 32 EUs (for Intel® Xeon® W-11555MLE and Intel® Xeon® W-11865MLE)
Drives	
Hard disk	M.2 SSD ≥ 240 GB
SSD	Yes; ≥ 240 GB optional
Storage	
Type of memory	DDR4-3200 SO-DIMM
Main memory	4 / 8 / 16 / 32 GB
Capacity of main memory, max.	32 Gbyte
Hardware configuration	
Slots	
• Number of PCI slots	0
• Number of compact flash slots	0
Interfaces	

Number of industrial Ethernet interfaces	2; 2x Gigabit Ethernet (IE/PN), RJ45
serial interface	2x / 4x (optional) COM (RS 232 / 485 / 422; selectable)
Video interfaces	
• Graphics interface	2x DisplayPort (DP1.4-capable): maximum 4096 × 2304 / 60 Hz / 36 bit
Industrial Ethernet	
• Industrial Ethernet interface	
— 100 Mbps	Yes
— 1000 Mbps	Yes
Interrupts/diagnostics/status information	
LED status display	No
Bus diagnostics	No
Integrated Functions	
Monitoring functions	
• Temperature monitoring	No
• Fan	No
• Monitoring function via network	Optional
Degree and class of protection	
IP (at the front)	IP65
IP (rear)	IP20
Standards, approvals, certificates	
CE mark	Yes
UKCA mark	Yes
CSA approval	Yes
UL approval	Yes; UL 61010-2-201 Second Edition, File E472609
• UL 508	No
cULus	Yes
RCM (formerly C-TICK)	Yes
KC approval	No; in preparation
EAC (formerly Gost-R)	No
FCC	Yes
BSMI	No; in preparation
BIS	Yes
Use in hazardous areas	
• ATEX Zone 2	No
• IECEx Zone 2	No
• cULus Class I Zone 2, Division 2	No
Marine approval	
• Germanischer Lloyd (GL)	No
• American Bureau of Shipping (ABS)	No
• Bureau Veritas (BV)	No
• Det Norske Veritas (DNV)	No
• Korean Register of Shipping (KRS)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (Class NK)	No
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	50 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	60 °C
Relative humidity	
• Operation, max.	85 %
Vibrations	
• Vibration resistance during operation acc. to IEC 60068-2-6	tested according to IEC 60068-2-6; 5 Hz to 9 Hz: 3.5 mm; 9 Hz to 500 Hz: 9.8 m/s ²
Operating systems	
pre-installed operating system	Windows 10 IoT Enterprise 2021 LTSC, Industrial OS
without operating system	Yes; Optional

pre-installed operating system

- Windows 7 No
- Windows 10 Enterprise Yes; Windows 10 IoT Enterprise 2021 LTSC

Dimensions

Width of the housing front	473 mm
Height of housing front	297 mm
Mounting cutout, width	455 mm
Mounting cutout, height	279.19999 mm
mounting depth	96 mm

Weights

Weight, approx.	7 kg
-----------------	------

Approvals / Certificates

General Product Approval	Test Certificates
--------------------------	-------------------



[Type Test Certificates/Test Report](#)

Maritime application other



[Confirmation](#)



Environment

[Environmental Confirmations](#)



last modified:

6/11/2026