



SIMATIC ET 200SP, Digital output module, DQ 8x 24V DC/0.5A Basic, Source output (PNP,P-switching) Packing unit: 10 pieces, fits to BU-type A0, Colour Code CC02, substitute value output, module diagnostics for: supply voltage

General information	
Product type designation	DQ 8x24VDC/0.5A BA
HW functional status	From FS02
Firmware version	V0.0
• FW update possible	No
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC02
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14
• STEP 7 configurable/integrated from version	V5.5 SP3
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	45 mA; without load
Output voltage	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	1 W
Address area	
Address space per module	
• Address space per module, max.	1 byte
Hardware configuration	

Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0
• 2-wire connection	BU type A0
• 3-wire connection	BU type A0 with AUX terminals or potential distributor module
• 4-wire connection	BU type A0 + Potential distributor module
Digital outputs	
Type of digital output	Source output (PNP, current-sourcing)
Number of digital outputs	8
Current-sinking	No
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes; per channel, electronic
• Response threshold, typ.	1 A
Limitation of inductive shutdown voltage to	Typ. L+ (-50 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
• on lamp load, max.	5 W
Load resistance range	
• lower limit	48 Ω
• upper limit	100 kΩ
Output current	
• for signal "1" rated value	0.5 A
• for signal "1" permissible range, max.	0.5 A
• for signal "0" residual current, max.	10 μA
Output delay with resistive load	
• "0" to "1", max.	100 μs; at rated load
• "1" to "0", max.	150 μs; at rated load
Parallel switching of two outputs	
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per channel, max.	0.5 A
• Current per module, max.	4 A
Total current of the outputs (per module)	
horizontal installation	
— up to 60 °C, max.	4 A
vertical installation	
— up to 50 °C, max.	4 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire break	No
• Short-circuit	No
• Group error	Yes

Diagnostics indication LED			
Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED		
Channel status display	Yes; green LED		
for channel diagnostics	No		
for module diagnostics	Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
between the channels	No		
between the channels and backplane bus	Yes		
between the channels and the power supply of the electronics	No		
Isolation			
Isolation tested with	707 V DC (type test)		
Standards, approvals, certificates			
Suitable for safety functions	No		
Suitable for safety-related tripping of standard modules	Yes; see FAQ Entry ID: 39198632		
Ecological footprint			
environmental product declaration	Yes		
Global warming potential			
— global warming potential, (total) [CO2 eq]	20.4 kg		
— global warming potential, (during production) [CO2 eq]	3.16 kg		
— global warming potential, (during operation) [CO2 eq]	17.5 kg		
— global warming potential, (after end of life cycle) [CO2 eq]	-0.221 kg		
Highest safety class achievable in safety mode			
Performance level according to ISO 13849-1	PL d		
SIL acc. to IEC 61508	SIL 2		
Ambient conditions			
Ambient temperature during operation			
horizontal installation, min.	-30 °C; < 0 °C as of FS02		
horizontal installation, max.	60 °C		
vertical installation, min.	-30 °C; < 0 °C as of FS02		
vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual		
Dimensions			
Width	15 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	30 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-04
	eClass	12	27-24-26-04
	eClass	9.1	27-24-26-04
	eClass	9	27-24-26-04
	eClass	8	27-24-26-04
	eClass	7.1	27-24-26-04
	eClass	6	27-24-26-04
	ETIM	10	EC001599
	ETIM	9	EC001599
	ETIM	8	EC001599
	ETIM	7	EC001599
	IDEA	4	3566

Approvals / Certificates

General Product Approval



General Product Approval	Maritime application	Environment
--------------------------	----------------------	-------------



last modified: 10/23/2025