


### product type designation

product description



### Energy cable 4 x 1.5

Power cable (4-core), sold by the meter, unassembled

Energy cable, 4-core power line, stranded wire, 4x 1.5 mm<sup>2</sup>, trailable Delivery unit: max. 1000 m, minimum order quantity 20 m sold by the meter

Technical Product Detail Page	<a href="https://l.siemens.com/1P6XV1801-2B">https://l.siemens.com/1P6XV1801-2B</a>
suitability for use	connection of 24 V power supply
cable designation	LIYY 4X1X1.5 BK
<b>electrical data</b>	
operating voltage / RMS value	600 V
conductor cross section / of the power line	1.5 mm <sup>2</sup>
continuous current / of the power lines	15 A; at 40°C according to DIN VDE 0891-1 (17 A at 20°C according to DIN VDE 0891-1)
<b>mechanical data</b>	
number of electrical cores	4
outer diameter	
• of inner conductor	1.6 mm
• of the wire insulation	2.3 mm
• of cable sheath	7.7 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.3 mm
conductor class	5
material	
• of the conductor	CU, blank
• of the wire insulation	PVC
• of cable sheath	PVC
product component / PE connection	No
marking / of cores	Color
color	
• of the power line insulation	brown / white / blue / black
• of cable sheath	Black
bending radius	
• with single bend / minimum permissible	31 mm
• with multiple bends / minimum permissible	62 mm
• with continuous bending	62 mm
number of bending cycles	2000000
tensile load / maximum	100 N
weight per length	97 kg/km
<b>ambient conditions</b>	
ambient temperature	
• during operation	-20 ... +90 °C
• during storage	-30 ... +90 °C
• during transport	-30 ... +90 °C

• during installation	-20 ... +90 °C
ambient condition / for operation	temperature range for permanent installation -30 °C to 90 °C
fire behavior	Flame-resistant acc. to IEC 60332-1-2
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	Oil resistant according to EN 50290-2-22 (VDE 0819), compound type TM55 (7x24h/90 °C)
• to grease	Conditional resistance
• to water	resistant according to UL 758 (75°C)
radiological resistance / to UV radiation	resistant

**product features, product functions, product components / general**

product feature	
• halogen-free	No
• silicon-free	Yes

**standards, specifications, approvals**

UL/ETL listing / 300 V Rating	Yes; c(ETL)us 3047254 CM 75°C
UL/ETL style / 600 V Rating	Yes; E502506 AWM STYLE 21216 90°C
certificate of suitability	wet-resistant according to UL Style 22374
• EAC approval	Yes
• RoHS conformity	Yes

**further information / internet links**

internet link	
• to website: Selection guide for cables and connectors	<a href="https://support.industry.siemens.com/cs/ww/en/view/109766358">https://support.industry.siemens.com/cs/ww/en/view/109766358</a>
• to web page: selection aid TIA Selection Tool	<a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a>
• to website: Industrial communication	<a href="https://www.siemens.com/simatic-net">https://www.siemens.com/simatic-net</a>
• to web page: SiePortal	<a href="https://sieportal.siemens.com/">https://sieportal.siemens.com/</a>
• to website: Image database	<a href="https://www.automation.siemens.com/bilddb">https://www.automation.siemens.com/bilddb</a>
• to website: CAx-Download-Manager	<a href="https://www.siemens.com/cax">https://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

**security information**

security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit <a href="http://www.siemens.com/cybersecurity-industry">www.siemens.com/cybersecurity-industry</a> . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <a href="https://www.siemens.com/cert">https://www.siemens.com/cert</a> . (V4.7)
----------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

**Approvals / Certificates**

<b>General Product Approval</b>	<b>other</b>	<b>Environment</b>
---------------------------------	--------------	--------------------

[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[Fire safety / Physical security](#)

[Miscellaneous](#)

[Environmental Conformations](#)

<b>Environment</b>	<b>Industrial Communication</b>
--------------------	---------------------------------

[Environmental Conformations](#)

[PROFINET](#)

---

last modified:

5/9/2026 