



Reversing motor starter, Size 2 1/2, Three phase full voltage, Solid-state overload relay, OLR amp range 25-100A, 24VAC 50-60Hz coil, Non-combination type, Enclosure type 4X fiberglass, Water/dust tight noncorrosive, Standard width enclosure

|   |  |
|---|--|
| product brand name  | Class 22                                 |
| design of the product   | Full-voltage reversing motor starter     |
| special product feature   | ESP200 overload relay; Half-size starter |
| <b>General technical data</b>   |  |
| weight [lb]   | 19 lb                                    |
| Height x Width x Depth [in]   | 24 × 15 × 7 in                           |
| touch protection against electrical shock                               | NA for enclosed products                 |
| installation altitude [ft] at height above sea level maximum            | 6560 ft                                  |
| ambient temperature [°F]  |  |
| • during storage  | -22 ... +149 °F                          |
| • during operation  | -4 ... +104 °F                           |
| ambient temperature   |  |
| • during storage  | -30 ... +65 °C                           |
| • during operation  | -20 ... +40 °C                           |
| country of origin   | USA                                      |
| <b>Horsepower ratings</b>   |  |
| yielded mechanical performance [hp] for 3-phase AC motor                |  |
| • at 200/208 V rated value  | 15 hp                                    |
| • at 220/230 V rated value  | 20 hp                                    |
| • at 460/480 V rated value  | 30 hp                                    |
| • at 575/600 V rated value  | 30 hp                                    |
| <b>Contactors</b>   |  |
| size of contactor   | Controller half size 2 1/2               |
| number of NO contacts for main contacts                                 | 3  |
| operating voltage for main current circuit at AC at 60 Hz maximum       | 600 V                                    |
| operational current at AC at 600 V rated value                          | 60 A                                     |
| mechanical service life (operating cycles) of the main contacts typical | 10000000                                 |
| <b>Auxiliary contact</b>  |  |
| number of NC contacts at contactor for auxiliary contacts               | 0  |
| number of NO contacts at contactor for auxiliary contacts               | 1  |
| number of total auxiliary contacts maximum                              | 7  |
| contact rating of auxiliary contacts of contactor according to UL       | 10A@600VAC (A600), 2.5A@300VDC (Q300)    |
| <b>Coil</b>   |  |
| type of voltage of the control supply voltage                           | AC                                       |
| control supply voltage  |  |
| • at AC at 50 Hz rated value  | 24 V                                     |
| • at AC at 60 Hz rated value  | 24 V                                     |

|  |  |
|--|--|
| holding power at AC minimum  | 8.6 W  |
| apparent pick-up power of magnet coil at AC  | 218 VA   |
| apparent holding power of magnet coil at AC  | 25 VA  |
| operating range factor control supply voltage rated value of magnet coil   | 0.85 ... 1.1                                   |
| percentual drop-out voltage of magnet coil related to the input voltage  | 50 %   |
| ON-delay time  | 19 ... 29 ms                                   |
| OFF-delay time   | 10 ... 24 ms                                   |
| <b>Overload relay</b>  |  |
| product function   |  |
| • overload protection  | Yes  |
| • phase failure detection  | Yes  |
| • asymmetry detection  | Yes  |
| • ground fault detection   | Yes  |
| • test function  | Yes  |
| • external reset   | Yes  |
| reset function   | Manual, automatic and remote                   |
| trip class   | CLASS 5 / 10 / 20 (factory set) / 30           |
| adjustable current response value current of the current-dependent overload release                                | 25 ... 100 A                                   |
| make time with automatic start after power failure maximum   | 3 s  |
| relative repeat accuracy   | 1 %  |
| product feature protective coating on printed-circuit board  | Yes  |
| number of NC contacts of auxiliary contacts of overload relay  | 1  |
| number of NO contacts of auxiliary contacts of overload relay  | 1  |
| operational current of auxiliary contacts of overload relay  |  |
| • at AC at 600 V   | 5 A  |
| • at DC at 250 V   | 1 A  |
| contact rating of auxiliary contacts of overload relay according to UL   | 5A@600VAC (B600), 1A@250VDC (R300)             |
| insulation voltage (Ui)  |  |
| • with single-phase operation at AC rated value  | 600 V  |
| • with multi-phase operation at AC rated value   | 300 V  |
| <b>Enclosure</b>   |  |
| design of the housing  | dustproof, waterproof & resistant to corrosion |
| <b>Mounting/wiring</b>   |  |
| mounting position  | Vertical                                       |
| fastening method   | Surface mounting and installation              |
| type of electrical connection for supply voltage line-side   | Box lug  |
| tightening torque [lbf-in] for supply  | 45 lbf-in                                      |
| type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded                  | 1x (14 ... 2 AWG)                              |
| temperature of the conductor for supply maximum permissible  | 75 °C  |
| material of the conductor for supply   | AL or CU                                       |
| type of electrical connection for load-side outgoing feeder  | Box lug  |
| tightening torque [lbf-in] for load-side outgoing feeder   | 45 lbf-in                                      |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded | 1x (14 ... 2 AWG)                              |
| temperature of the conductor for load-side outgoing feeder maximum permissible                                     | 75 °C  |
| material of the conductor for load-side outgoing feeder  | AL or CU                                       |
| type of electrical connection of magnet coil   | Screw-type terminals                           |
| tightening torque [lbf-in] at magnet coil  | 5 ... 12 lbf-in                                |
| type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded                | 2x (16 ... 12 AWG)                             |
| temperature of the conductor at magnet coil maximum permissible  | 75 °C  |
| material of the conductor at magnet coil   | CU   |
| type of electrical connection for auxiliary contacts   | Screw-type terminals                           |
| tightening torque [lbf-in] at contactor for auxiliary contacts   | 10 ... 15 lbf-in                               |

|   |   |
|---|---|
| type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded      | 1x (12 AWG), 2x (16 ... 14 AWG), 2x (18 ... 16 AWG) |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible  | 75 °C   |
| material of the conductor at contactor for auxiliary contacts   | CU  |
| type of electrical connection at overload relay for auxiliary contacts  | Screw-type terminals                                |
| tightening torque [lbf-in] at overload relay for auxiliary contacts   | 7 ... 10 lbf-in                                     |
| type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded | 2x (20 ... 14 AWG)                                  |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible                                     | 75 °C   |
| material of the conductor at overload relay for auxiliary contacts  | CU  |

### Short-circuit current rating

|   |   |
|---|---|
| design of the fuse link for short-circuit protection of the main circuit required | 10kA@600V (Class H or K); 100kA@600V (Class R or J) |
| design of the short-circuit trip  | Thermal magnetic circuit breaker                    |
| maximum short-circuit current breaking capacity (I <sub>cu</sub> )                |   |
| • at 240 V  | 14 kA   |
| • at 480 V  | 10 kA   |
| • at 600 V  | 10 kA   |
| certificate of suitability  | NEMA ICS 2; UL 508; CSA 22.2, No.14                 |

### Approvals Certificates

#### Test Certificates



### Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:22GUG32FJ>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:22GUG32FJ>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:22GUG32FJ&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:22GUG32FJ&lang=en)

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/US2:22GUG32FJ/certificate>



D46590003

