



AS-i Compact Module K60 digital A/B device, 8 DI, IP67, 8 x input, maximum 2000 mA sensor supply 24 V DC 8 x M12 socket Y-II assignment mounting plate 3RK1901-0CA00 must be ordered separately

General technical data			
design of the product	digital I/O modules for operation in the field, IP67 - K60		
design of the device type	A/B slave		
type of electrical connection of the inputs and outputs	M12 screw-type terminals		
Sensor supply			
type of voltage supply for sensor supply	via AUX POWER		
input voltage	20 ... 30 V		
property of the sensor supply short-circuit and overload resistant	Yes		
ampacity of the sensor supply for all inputs at ambient temperature 40 °C	2 mA		
Inputs			
number of digital inputs	8		
type of connection technology	2- and 3-wire technology		
type of voltage of the input voltages	DC		
input current at digital input - for signal <1> minimum - with signal <0> maximum	6 mA 1.5 mA		
design of the pin assignment of the inputs	Y-II assignement		
Outputs			
number of digital outputs	0		
Ambient conditions			
ambient temperature - during operation - during storage	-25 ... +85 °C -40 ... +85 °C		
protection class IP	IP67		
Mechanical data			
width	60 mm		
height	152 mm		
depth	29 mm		
fastening method	standard rail mounting/wall mounting using mounting plate for K60 compact module		
shock resistance	15 g / 11 ms		
Certificates/ approvals			
General Product Approval		EMV	Maritime application



other

Environment

Industrial Communication

[Miscellaneous](#)

[Confirmation](#)



[Environmental Confirmations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK2200-1DQ00-1AA3>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK2200-1DQ00-1AA3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK2200-1DQ00-1AA3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK2200-1DQ00-1AA3&lang=en



last modified:

4/4/2026