



power contactor, AC-3e/AC-3, 9 A, 4 kW / 400 V, 3-pole, 400 V AC, 50 Hz / 400-440 V, 60 Hz, auxiliary contacts: 1 NC, ring cable lug connection, size: S00

|                                                                                                              |                              |
|--------------------------------------------------------------------------------------------------------------|------------------------------|
| product brand name                                                                                           | SIRIUS                       |
| product designation                                                                                          | Power contactor              |
| product type designation                                                                                     | 3RT2                         |
| <b>General technical data</b>                                                                                |                              |
| size of contactor                                                                                            | S00                          |
| product extension                                                                                            |                              |
| • function module for communication                                                                          | No                           |
| • auxiliary switch                                                                                           | Yes                          |
| power loss [W] for rated value of the current                                                                |                              |
| • at AC in hot operating state                                                                               | 0.9 W                        |
| • at AC in hot operating state per pole                                                                      | 0.3 W                        |
| • without load current share typical                                                                         | 1.2 W                        |
| type of calculation of power loss current-dependent                                                          | quadratic                    |
| insulation voltage                                                                                           |                              |
| • of main circuit with degree of pollution 3 rated value                                                     | 690 V                        |
| • of auxiliary circuit with degree of pollution 3 rated value                                                | 690 V                        |
| surge voltage resistance                                                                                     |                              |
| • of main circuit rated value                                                                                | 6 kV                         |
| • of auxiliary circuit rated value                                                                           | 6 kV                         |
| maximum permissible voltage for protective separation between coil and main contacts according to EN 60947-1 | 400 V                        |
| shock resistance at rectangular impulse                                                                      |                              |
| • at AC                                                                                                      | 6,7 g / 5 ms, 4,2 g / 10 ms  |
| shock resistance with sine pulse                                                                             |                              |
| • at AC                                                                                                      | 10,5 g / 5 ms, 6,6 g / 10 ms |
| mechanical service life (operating cycles)                                                                   |                              |
| • of contactor typical                                                                                       | 30 000 000                   |
| • of the contactor with added electronically optimized auxiliary switch block typical                        | 5 000 000                    |
| • of the contactor with added auxiliary switch block typical                                                 | 10 000 000                   |
| reference code according to IEC 81346-2                                                                      | Q                            |
| Substance Prohibitance (day/month/year)                                                                      | 10/01/2009                   |
| Net Weight                                                                                                   | 0.222 kg                     |
| <b>Ambient conditions</b>                                                                                    |                              |
| installation altitude at height above sea level maximum                                                      | 2 000 m                      |
| ambient temperature                                                                                          |                              |
| • during operation                                                                                           | -25 ... +60 °C               |
| • during storage                                                                                             | -55 ... +80 °C               |
| relative humidity minimum                                                                                    | 10 %                         |
| relative humidity at 55 °C according to IEC 60068-2-30                                                       | 95 %                         |

|                                                                   |                   |
|-------------------------------------------------------------------|-------------------|
| maximum                                                           |                   |
| <b>Main circuit</b>                                               |                   |
| number of poles for main current circuit                          | 3                 |
| number of NO contacts for main contacts                           | 3                 |
| number of NC contacts for main contacts                           | 0                 |
| operating voltage                                                 |                   |
| • at AC-3 rated value maximum                                     | 690 V             |
| • at AC-3e rated value maximum                                    | 690 V             |
| operational current                                               |                   |
| • at AC-1 at 400 V at ambient temperature 40 °C rated value       | 22 A              |
| • at AC-1                                                         |                   |
| — up to 690 V at ambient temperature 40 °C rated value            | 22 A              |
| — up to 690 V at ambient temperature 60 °C rated value            | 20 A              |
| • at AC-3                                                         |                   |
| — at 400 V rated value                                            | 9 A               |
| — at 500 V rated value                                            | 7.7 A             |
| — at 690 V rated value                                            | 6.7 A             |
| • at AC-3e                                                        |                   |
| — at 400 V rated value                                            | 9 A               |
| — at 500 V rated value                                            | 7.7 A             |
| — at 690 V rated value                                            | 6.7 A             |
| • at AC-4 at 400 V rated value                                    | 8.5 A             |
| • at AC-5a up to 690 V rated value                                | 19.4 A            |
| • at AC-5b up to 400 V rated value                                | 7.4 A             |
| • at AC-6a                                                        |                   |
| — up to 230 V for current peak value n=20 rated value             | 5.3 A             |
| — up to 400 V for current peak value n=20 rated value             | 5.3 A             |
| — up to 500 V for current peak value n=20 rated value             | 5.3 A             |
| — up to 690 V for current peak value n=20 rated value             | 5 A               |
| • at AC-6a                                                        |                   |
| — up to 230 V for current peak value n=30 rated value             | 3.5 A             |
| — up to 400 V for current peak value n=30 rated value             | 3.5 A             |
| — up to 500 V for current peak value n=30 rated value             | 3.6 A             |
| — up to 690 V for current peak value n=30 rated value             | 3.3 A             |
| minimum cross-section in main circuit at maximum AC-1 rated value | 4 mm <sup>2</sup> |
| operational current for approx. 200000 operating cycles at AC-4   |                   |
| • at 400 V rated value                                            | 4.1 A             |
| • at 690 V rated value                                            | 3.3 A             |
| operational current                                               |                   |
| • at 1 current path at DC-1                                       |                   |
| — at 24 V rated value                                             | 20 A              |
| — at 60 V rated value                                             | 20 A              |
| — at 110 V rated value                                            | 2.1 A             |
| — at 220 V rated value                                            | 0.8 A             |
| — at 440 V rated value                                            | 0.6 A             |
| — at 600 V rated value                                            | 0.6 A             |
| • with 2 current paths in series at DC-1                          |                   |
| — at 24 V rated value                                             | 20 A              |
| — at 60 V rated value                                             | 20 A              |
| — at 110 V rated value                                            | 12 A              |
| — at 220 V rated value                                            | 1.6 A             |
| — at 440 V rated value                                            | 0.8 A             |
| — at 600 V rated value                                            | 0.7 A             |
| • with 3 current paths in series at DC-1                          |                   |
| — at 24 V rated value                                             | 20 A              |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                                            |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>— at 60 V rated value</li> <li>— at 110 V rated value</li> <li>— at 220 V rated value</li> <li>— at 440 V rated value</li> <li>— at 600 V rated value</li> </ul>                                                                                                                                                                                                                                                    | 20 A<br>20 A<br>20 A<br>1.3 A<br>1 A                                                                                                                                                                                                                                                                       |
| <ul style="list-style-type: none"> <li>● <b>at 1 current path at DC-3 at DC-5</b> <ul style="list-style-type: none"> <li>— at 24 V rated value</li> <li>— at 60 V rated value</li> <li>— at 110 V rated value</li> </ul> </li> </ul>                                                                                                                                                                                                                       | 20 A<br>0.5 A<br>0.15 A                                                                                                                                                                                                                                                                                    |
| <ul style="list-style-type: none"> <li>● <b>with 2 current paths in series at DC-3 at DC-5</b> <ul style="list-style-type: none"> <li>— at 24 V rated value</li> <li>— at 60 V rated value</li> <li>— at 110 V rated value</li> </ul> </li> </ul>                                                                                                                                                                                                          | 20 A<br>5 A<br>0.35 A                                                                                                                                                                                                                                                                                      |
| <ul style="list-style-type: none"> <li>● <b>with 3 current paths in series at DC-3 at DC-5</b> <ul style="list-style-type: none"> <li>— at 24 V rated value</li> <li>— at 60 V rated value</li> <li>— at 110 V rated value</li> <li>— at 220 V rated value</li> <li>— at 440 V rated value</li> <li>— at 600 V rated value</li> </ul> </li> </ul>                                                                                                          | 20 A<br>20 A<br>20 A<br>1.5 A<br>0.2 A<br>0.2 A                                                                                                                                                                                                                                                            |
| <b>operating power</b> <ul style="list-style-type: none"> <li>● at AC-3 <ul style="list-style-type: none"> <li>— at 230 V rated value</li> <li>— at 400 V rated value</li> <li>— at 500 V rated value</li> <li>— at 690 V rated value</li> </ul> </li> <li>● at AC-3e <ul style="list-style-type: none"> <li>— at 230 V rated value</li> <li>— at 400 V rated value</li> <li>— at 500 V rated value</li> <li>— at 690 V rated value</li> </ul> </li> </ul> | 2.2 kW<br>4 kW<br>4 kW<br>5.5 kW<br><br>2.2 kW<br>4 kW<br>4 kW<br>5.5 kW                                                                                                                                                                                                                                   |
| <b>operating power for approx. 200000 operating cycles at AC-4</b> <ul style="list-style-type: none"> <li>● at 400 V rated value</li> <li>● at 690 V rated value</li> </ul>                                                                                                                                                                                                                                                                                | 2 kW<br>2.5 kW                                                                                                                                                                                                                                                                                             |
| <b>operating apparent power at AC-6a</b> <ul style="list-style-type: none"> <li>● up to 230 V for current peak value n=20 rated value</li> <li>● up to 400 V for current peak value n=20 rated value</li> <li>● up to 500 V for current peak value n=20 rated value</li> <li>● up to 690 V for current peak value n=20 rated value</li> </ul>                                                                                                              | 2 kVA<br>3.6 kVA<br>4.6 kVA<br>5.9 kVA                                                                                                                                                                                                                                                                     |
| <b>operating apparent power at AC-6a</b> <ul style="list-style-type: none"> <li>● up to 230 V for current peak value n=30 rated value</li> <li>● up to 400 V for current peak value n=30 rated value</li> <li>● up to 500 V for current peak value n=30 rated value</li> <li>● up to 690 V for current peak value n=30 rated value</li> </ul>                                                                                                              | 1.3 kVA<br>2.4 kVA<br>3.1 kVA<br>4 kVA                                                                                                                                                                                                                                                                     |
| <b>short-time withstand current in cold operating state up to 40 °C</b> <ul style="list-style-type: none"> <li>● limited to 1 s switching at zero current maximum</li> <li>● limited to 5 s switching at zero current maximum</li> <li>● limited to 10 s switching at zero current maximum</li> <li>● limited to 30 s switching at zero current maximum</li> <li>● limited to 60 s switching at zero current maximum</li> </ul>                            | 155 A; Use minimum cross-section acc. to AC-1 rated value<br>111 A; Use minimum cross-section acc. to AC-1 rated value<br>86 A; Use minimum cross-section acc. to AC-1 rated value<br>66 A; Use minimum cross-section acc. to AC-1 rated value<br>55 A; Use minimum cross-section acc. to AC-1 rated value |
| <b>no-load switching frequency</b> <ul style="list-style-type: none"> <li>● at AC</li> </ul>                                                                                                                                                                                                                                                                                                                                                               | 10 000 1/h                                                                                                                                                                                                                                                                                                 |
| <b>operating frequency</b> <ul style="list-style-type: none"> <li>● at AC-1 maximum</li> <li>● at AC-2 maximum</li> <li>● at AC-3 maximum</li> <li>● at AC-3e</li> </ul>                                                                                                                                                                                                                                                                                   | 1 000 1/h<br>750 1/h<br>750 1/h                                                                                                                                                                                                                                                                            |

|                                                                                       |                                                 |
|---------------------------------------------------------------------------------------|-------------------------------------------------|
| — maximum                                                                             | 750 1/h                                         |
| • at AC-4 maximum                                                                     | 250 1/h                                         |
| <b>Control circuit/ Control</b>                                                       |                                                 |
| <b>type of voltage of the control supply voltage</b>                                  | AC                                              |
| <b>control supply voltage at AC</b>                                                   |                                                 |
| • at 50 Hz rated value                                                                | 400 V                                           |
| • at 60 Hz rated value                                                                | 440 V                                           |
| <b>operating range factor control supply voltage rated value of magnet coil at AC</b> |                                                 |
| • at 50 Hz                                                                            | 0.8 ... 1.1                                     |
| • at 60 Hz                                                                            | 0.85 ... 1.1                                    |
| <b>apparent pick-up power of magnet coil at AC</b>                                    |                                                 |
| • at 50 Hz                                                                            | 26.4 VA                                         |
| • at 60 Hz                                                                            | 31.7 VA                                         |
| <b>inductive power factor with closing power of the coil</b>                          |                                                 |
| • at 50 Hz                                                                            | 0.81                                            |
| • at 60 Hz                                                                            | 0.81                                            |
| <b>apparent holding power of magnet coil at AC</b>                                    |                                                 |
| • at 50 Hz                                                                            | 4.4 VA                                          |
| • at 60 Hz                                                                            | 4.8 VA                                          |
| <b>inductive power factor with the holding power of the coil</b>                      |                                                 |
| • at 50 Hz                                                                            | 0.24                                            |
| • at 60 Hz                                                                            | 0.25                                            |
| <b>closing delay</b>                                                                  |                                                 |
| • at AC                                                                               | 9 ... 35 ms                                     |
| <b>opening delay</b>                                                                  |                                                 |
| • at AC                                                                               | 4 ... 15 ms                                     |
| <b>arcing time</b>                                                                    | 10 ... 15 ms                                    |
| <b>control version of the switch operating mechanism</b>                              | Standard A1 - A2                                |
| <b>Auxiliary circuit</b>                                                              |                                                 |
| number of NC contacts for auxiliary contacts instantaneous contact                    | 1                                               |
| number of NO contacts for auxiliary contacts instantaneous contact                    | 0                                               |
| operational current at AC-12 maximum                                                  | 10 A                                            |
| <b>operational current at AC-15</b>                                                   |                                                 |
| • at 230 V rated value                                                                | 10 A                                            |
| • at 400 V rated value                                                                | 3 A                                             |
| • at 500 V rated value                                                                | 2 A                                             |
| • at 690 V rated value                                                                | 1 A                                             |
| <b>operational current at DC-12</b>                                                   |                                                 |
| • at 24 V rated value                                                                 | 10 A                                            |
| • at 48 V rated value                                                                 | 6 A                                             |
| • at 60 V rated value                                                                 | 6 A                                             |
| • at 110 V rated value                                                                | 3 A                                             |
| • at 125 V rated value                                                                | 2 A                                             |
| • at 220 V rated value                                                                | 1 A                                             |
| • at 600 V rated value                                                                | 0.15 A                                          |
| <b>operational current at DC-13</b>                                                   |                                                 |
| • at 24 V rated value                                                                 | 10 A                                            |
| • at 48 V rated value                                                                 | 2 A                                             |
| • at 60 V rated value                                                                 | 2 A                                             |
| • at 110 V rated value                                                                | 1 A                                             |
| • at 125 V rated value                                                                | 0.9 A                                           |
| • at 220 V rated value                                                                | 0.3 A                                           |
| • at 600 V rated value                                                                | 0.1 A                                           |
| <b>contact reliability of auxiliary contacts</b>                                      | 1 faulty switching per 100 million (17 V, 1 mA) |
| <b>UL/CSA ratings</b>                                                                 |                                                 |
| <b>full-load current (FLA) for 3-phase AC motor</b>                                   |                                                 |
| • at 480 V rated value                                                                | 7.6 A                                           |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                                                                                                                                                                          |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at 600 V rated value</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | 9 A                                                                                                                                                                                      |
| <b>yielded mechanical performance [hp]</b> <ul style="list-style-type: none"> <li>• for single-phase AC motor <ul style="list-style-type: none"> <li>— at 110/120 V rated value</li> <li>— at 230 V rated value</li> </ul> </li> <li>• for 3-phase AC motor <ul style="list-style-type: none"> <li>— at 200/208 V rated value</li> <li>— at 220/230 V rated value</li> <li>— at 460/480 V rated value</li> <li>— at 575/600 V rated value</li> </ul> </li> </ul>                                                                                      | 0.33 hp<br>1 hp<br><br>2 hp<br>3 hp<br>5 hp<br>7.5 hp                                                                                                                                    |
| <b>contact rating of auxiliary contacts according to UL</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | A600 / Q600                                                                                                                                                                              |
| <b>Short-circuit protection</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |                                                                                                                                                                                          |
| design of the miniature circuit breaker for short-circuit protection of the auxiliary circuit up to 230 V                                                                                                                                                                                                                                                                                                                                                                                                                                             | C characteristic: 10 A; 0.4 kA                                                                                                                                                           |
| <b>design of the fuse link</b> <ul style="list-style-type: none"> <li>• for short-circuit protection of the main circuit <ul style="list-style-type: none"> <li>— with type of coordination 1 required</li> <li>— with type of coordination 2 required</li> </ul> </li> <li>• for short-circuit protection of the auxiliary switch required</li> </ul>                                                                                                                                                                                                | gG: 35 A (690 V, 100 kA), aM: 20 A (690 V, 100 kA), BS88: 35 A (415 V, 80 kA)<br>gG: 20 A (690 V, 100 kA), aM: 16 A (690 V, 100 kA), BS88: 20 A (415 V, 80 kA)<br>gG: 10 A (500 V, 1 kA) |
| <b>Installation/ mounting/ dimensions</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                          |
| <b>mounting position</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | +/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface                                                     |
| fastening method side-by-side mounting                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | Yes                                                                                                                                                                                      |
| <b>fastening method</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               | screw and snap-on mounting onto 35 mm DIN rail according to DIN EN 60715                                                                                                                 |
| <b>height</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | 58 mm                                                                                                                                                                                    |
| <b>width</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | 45 mm                                                                                                                                                                                    |
| <b>depth</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | 73 mm                                                                                                                                                                                    |
| <b>required spacing</b> <ul style="list-style-type: none"> <li>• with side-by-side mounting <ul style="list-style-type: none"> <li>— forwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> <li>• for grounded parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— upwards</li> <li>— at the side</li> <li>— downwards</li> </ul> </li> <li>• for live parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> </ul> | 10 mm<br>10 mm<br>10 mm<br>0 mm<br><br>10 mm<br>10 mm<br>6 mm<br>10 mm<br><br>10 mm<br>10 mm<br>10 mm<br>6 mm                                                                            |
| <b>Connections/ Terminals</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |                                                                                                                                                                                          |
| <b>type of electrical connection</b> <ul style="list-style-type: none"> <li>• for main current circuit</li> <li>• for auxiliary and control circuit</li> <li>• at contactor for auxiliary contacts</li> <li>• of magnet coil</li> </ul>                                                                                                                                                                                                                                                                                                               | Ring cable lug connection<br>ring terminal lug connection<br>Ring cable lug connection<br>Ring cable lug connection                                                                      |
| <b>Safety related data</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                          |
| <b>product function</b> <ul style="list-style-type: none"> <li>• mirror contact according to IEC 60947-4-1</li> <li>• positively driven operation according to IEC 60947-5-1</li> <li>• suitable for safety function</li> </ul>                                                                                                                                                                                                                                                                                                                       | Yes<br>No<br>Yes                                                                                                                                                                         |
| suitability for use safety-related switching OFF                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | Yes                                                                                                                                                                                      |
| <b>service life maximum</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | 20 a                                                                                                                                                                                     |
| <b>test wear-related service life necessary</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | Yes                                                                                                                                                                                      |
| <b>proportion of dangerous failures</b> <ul style="list-style-type: none"> <li>• with low demand rate according to SN 31920</li> </ul>                                                                                                                                                                                                                                                                                                                                                                                                                | 40 %                                                                                                                                                                                     |

|                                                                      |           |
|----------------------------------------------------------------------|-----------|
| • with high demand rate according to SN 31920                        | 73 %      |
| <b>B10 value with high demand rate according to SN 31920</b>         | 1 000 000 |
| <b>failure rate [FIT] with low demand rate according to SN 31920</b> | 100 FIT   |
| ISO 13849                                                            |           |
| <b>device type according to ISO 13849-1</b>                          | 3         |
| <b>overdimensioning according to ISO 13849-2 necessary</b>           | Yes       |
| IEC 61508                                                            |           |
| <b>safety device type according to IEC 61508-2</b>                   | Type A    |
| Electrical Safety                                                    |           |
| <b>protection class IP on the front according to IEC 60529</b>       | IP00      |

#### Approvals Certificates

|                                                            |                          |
|------------------------------------------------------------|--------------------------|
| Environmental Product Declaration                          |                          |
| • global warming potential [CO2 eq] / during manufacturing | 1.18 kg                  |
| • global warming potential [CO2 eq] / during operation     | 38.5 kg                  |
| • global warming potential [CO2 eq] / after end of life    | -0.155 kg                |
| • global warming potential [CO2 eq] / total                | 39.6 kg                  |
| Environment                                                | General Product Approval |

[Environmental Confirmations](#)



|                          |     |                                          |
|--------------------------|-----|------------------------------------------|
| General Product Approval | EMV | Test Certificates                        |
|                          |     |                                          |
|                          |     | <a href="#">Special Test Certificate</a> |

|                                                    |                      |
|----------------------------------------------------|----------------------|
| Test Certificates                                  | Maritime application |
| <a href="#">Type Test Certificates/Test Report</a> |                      |
|                                                    |                      |
|                                                    |                      |
|                                                    |                      |
|                                                    |                      |

|                               |                               |
|-------------------------------|-------------------------------|
| Maritime application          | other                         |
|                               |                               |
| <a href="#">Miscellaneous</a> | <a href="#">Confirmation</a>  |
| <a href="#">Confirmation</a>  | <a href="#">Miscellaneous</a> |

|       |                                          |
|-------|------------------------------------------|
| other | Railway                                  |
|       | <a href="#">Special Test Certificate</a> |

#### Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
Information for data generation and storage  
<https://support.industry.siemens.com/cs/ww/en/view/109995012>  
Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>  
Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT2016-4AR62>  
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT2016-4AR62>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RT2016-4AR62&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT2016-4AR62&lang=en)

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT2016-4AR62>

Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP='HAUPT'></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>)



