

Siemens  
EcoTech



mushroom pushbutton, 22 mm, round, metal, shiny, black, 40 mm, with Siemens lock, C, lock number VL5, positive latching, key-operated release



|                                                    |                                   |
|----------------------------------------------------|-----------------------------------|
| product brand name                                 | SIRIUS ACT                        |
| product designation                                | Mushroom pushbuttons              |
| design of the product                              | Actuating/signaling element       |
| product type designation                           | 3SU1                              |
| product line                                       | Metal, shiny, 22 mm               |
| Enclosure                                          |                                   |
| number of command points                           | 1                                 |
| Actuator                                           |                                   |
| design of the actuating element                    | positive latching                 |
| principle of operation of the actuating element    | latching                          |
| product extension optional light source            | No                                |
| color of the actuating element                     | black                             |
| material of the actuating element                  | plastic                           |
| shape of the actuating element                     | round                             |
| outer diameter of the actuating element            | 40 mm                             |
| type of unlocking device                           | Unlocking                         |
| number of switching positions                      | 2                                 |
| Front ring                                         |                                   |
| product component front ring                       | No                                |
| design of the front ring                           | without                           |
| General technical data                             |                                   |
| product function                                   |                                   |
| • EMERGENCY OFF function                           | No                                |
| • EMERGENCY STOP function                          | No                                |
| protection class IP                                | IP66, IP67, IP69(IP69K)           |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13        |
| shock resistance                                   |                                   |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15 g / 11 ms |
| vibration resistance                               |                                   |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5 g                |
| operating frequency maximum                        | 600 1/h                           |
| mechanical service life (operating cycles) typical | 300 000                           |
| reference code according to IEC 81346-2            | S                                 |
| Substance Prohibitance (day/month/year)            | 10/01/2014                        |
| SVHC substance name                                | Lead CAS-No. 7439-92-1            |
| Net Weight                                         | 164 g                             |

| Ambient conditions                                             |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>ambient temperature</b>                                     |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

| Installation/ mounting/ dimensions                 |          |
|----------------------------------------------------|----------|
| <b>height</b>                                      | 40 mm    |
| <b>width</b>                                       | 40 mm    |
| <b>shape of the installation opening</b>           | round    |
| <b>mounting diameter</b>                           | 22.3 mm  |
| <b>positive tolerance of installation diameter</b> | 0.4 mm   |
| <b>mounting height</b>                             | 85.09 mm |
| <b>installation width</b>                          | 40 mm    |
| <b>installation depth</b>                          | 26.3 mm  |

| Approvals Certificates                                     |                                 |
|------------------------------------------------------------|---------------------------------|
| Environmental Product Declaration                          |                                 |
| • global warming potential [CO2 eq] / during manufacturing | 0.625 kg                        |
| • global warming potential [CO2 eq] / during operation     | 0.235 kg                        |
| • global warming potential [CO2 eq] / after end of life    | -0.267 kg                       |
| • global warming potential [CO2 eq] / total                | 0.593 kg                        |
| <b>Environment</b>                                         | <b>General Product Approval</b> |

[Environmental Con-  
firmations](#)

Siemens  
EcoTech



|                                       |                          |                             |
|---------------------------------------|--------------------------|-----------------------------|
| <b>General Product Ap-<br/>proval</b> | <b>Test Certificates</b> | <b>Maritime application</b> |
|---------------------------------------|--------------------------|-----------------------------|



[Type Test Certific-  
ates/Test Report](#)

[Special Test Certific-  
ate](#)



|                             |              |
|-----------------------------|--------------|
| <b>Maritime application</b> | <b>other</b> |
|-----------------------------|--------------|



[Confirmation](#)



| Further information |
|---------------------|
|---------------------|

#### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

#### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-1HU10-0AA0>

#### Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1050-1HU10-0AA0>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1050-1HU10-0AA0>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1050-1HU10-0AA0&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1050-1HU10-0AA0&lang=en)



---

last modified:

5/8/2026 