

Siemens  
EcoTech



Illuminated mushroom pushbutton, 22 mm, round, metal, shiny, amber, 40 mm, momentary contact type



|                                                    |                                   |
|----------------------------------------------------|-----------------------------------|
| product brand name                                 | SIRIUS ACT                        |
| product designation                                | Mushroom pushbuttons              |
| design of the product                              | Actuating/signaling element       |
| product type designation                           | 3SU1                              |
| product line                                       | Metal, shiny, 22 mm               |
| <b>Enclosure</b>                                   |                                   |
| number of command points                           | 1                                 |
| <b>Actuator</b>                                    |                                   |
| design of the actuating element                    | illuminated                       |
| principle of operation of the actuating element    | momentary contact type            |
| product extension optional light source            | Yes                               |
| color of the actuating element                     | amber                             |
| material of the actuating element                  | plastic                           |
| shape of the actuating element                     | round                             |
| outer diameter of the actuating element            | 40 mm                             |
| number of switching positions                      | 2                                 |
| <b>Front ring</b>                                  |                                   |
| product component front ring                       | Yes                               |
| design of the front ring                           | Standard                          |
| material of the front ring                         | Metal, high gloss                 |
| color of the front ring                            | silver                            |
| <b>General technical data</b>                      |                                   |
| product function                                   |                                   |
| • EMERGENCY OFF function                           | No                                |
| • EMERGENCY STOP function                          | No                                |
| protection class IP                                | IP66, IP67, IP69(IP69K)           |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13        |
| shock resistance                                   |                                   |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15 g / 11 ms |
| vibration resistance                               |                                   |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5 g                |
| operating frequency maximum                        | 3 600 1/h                         |
| mechanical service life (operating cycles) typical | 3 000 000                         |
| reference code according to IEC 81346-2            | S                                 |
| Substance Prohibitance (day/month/year)            | 10/01/2014                        |
| Net Weight                                         | 49 g                              |

| Ambient conditions                                             |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>ambient temperature</b>                                     |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

| Installation/ mounting/ dimensions                 |         |
|----------------------------------------------------|---------|
| <b>height</b>                                      | 40 mm   |
| <b>width</b>                                       | 40 mm   |
| <b>shape of the installation opening</b>           | round   |
| <b>mounting diameter</b>                           | 22.3 mm |
| <b>positive tolerance of installation diameter</b> | 0.4 mm  |
| <b>mounting height</b>                             | 27.5 mm |
| <b>installation width</b>                          | 40 mm   |
| <b>installation depth</b>                          | 24.4 mm |

| Approvals Certificates                                     |                                 |
|------------------------------------------------------------|---------------------------------|
| Environmental Product Declaration                          |                                 |
| • global warming potential [CO2 eq] / during manufacturing | 0.625 kg                        |
| • global warming potential [CO2 eq] / during operation     | 0.235 kg                        |
| • global warming potential [CO2 eq] / after end of life    | -0.267 kg                       |
| • global warming potential [CO2 eq] / total                | 0.593 kg                        |
| <b>Environment</b>                                         | <b>General Product Approval</b> |

[Environmental Conformations](#)



| Test Certificates | Maritime application | other |
|-------------------|----------------------|-------|
|-------------------|----------------------|-------|

[Type Test Certificates/Test Report](#)



[Confirmation](#)

other



#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1051-1BD00-0AA0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1051-1BD00-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1051-1BD00-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1051-1BD00-0AA0&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1051-1BD00-0AA0&lang=en)



---

last modified:

4/4/2026 