



basic device SIMOCODE pro V PN, Ethernet/PROFINET IO, PN system redundancy, OPC UA server, web server, transfer rate 100 Mbps, 2 x bus connection via RJ45, 4 I/O freely configurable, Us: 24 V DC, input for thermistor connection monostable relay outputs, expandable by expansion modules

product brand name	SIMOCODE
product designation	Motor management system
design of the product	basic unit 3
product type designation	pro V PN
General technical data	
product function	
• current measurement	No
• voltage measurement	No
• active power measurement	Yes
• energy measurement	No
• frequency measurement	No
• bus communication	Yes
• data acquisition function	Yes
• diagnostics function	Yes
• password protection	Yes
• test function	Yes
• maintenance function	Yes
product component	
• input for thermistor connection	Yes
• digital input	Yes
• input for analog temperature sensors	No
• input for ground fault detection	No
• relay output	Yes
product extension	
• temperature monitoring module	Yes
• current measuring module	Yes
• current/voltage measuring module	Yes
• fail-safe digital I/O module	Yes
• ground-fault monitoring module	Yes
• decoupling module	Yes
• analog I/O module	Yes
• digital I/O module with monostable outputs	Yes
• digital I/O module with bistable outputs	Yes
• control unit with display	Yes
• control unit	Yes
consumed active power	3.6 W
insulation voltage with degree of pollution 3 at AC rated value	300 V
surge voltage resistance rated value	4 000 V
shock resistance	

• according to IEC 60068-2-27	15 g / 11 ms
• vibration resistance	1 ... 6 Hz / 15 mm; 6 ... 500 Hz / 2 g
switching capacity current of the NO contacts of the relay outputs at AC-15	
• at 24 V	6 A
• at 120 V	6 A
• at 230 V	3 A
switching capacity current of the NO contacts of the relay outputs at DC-13	
• at 24 V	2 A
• at 60 V	0.55 A
• at 125 V	0.25 A
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) typical	100 000
buffering time in the event of power failure	0.02 s
reference code according to IEC 81346-2	F
continuous current of the NO contacts of the relay outputs	
• at 50 °C	6 A
• at 60 °C	5 A
type of input characteristic	Type 1 in accordance with EN 61131-2
Substance Prohibitance (day/month/year)	03/01/2017
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 4,4'-isopropylidenediphenol (Bisphenol A, BPA) CAS-No. 80-05-7
Net Weight	0.318 kg
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV (power ports) / 1 kV (signal ports)
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
• due to high-frequency radiation according to IEC 61000-4-6	10 V
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
conducted HF interference emissions according to CISPR11	corresponds to degree of severity A
field-bound HF interference emission according to CISPR11	corresponds to degree of severity A
Inputs/ Outputs	
product function	
• parameterizable inputs	Yes
• parameterizable outputs	Yes
number of inputs	4
• for thermistor connection	1
number of digital inputs with a common reference potential	4
digital input version	
• type 1 acc. to IEC 61131	Yes
input voltage at digital input at DC	
• rated value	24 V
number of outputs	3
number of semiconductor outputs	0
number of outputs as contact-affected switching element	3
switching behavior	monostable
number of relay outputs	3
type of relay outputs	Monostable
wire length for digital signals maximum	300 m

wire length for thermistor connection	
• with conductor cross-section = 0.5 mm ² maximum	50 m
• with conductor cross-section = 1.5 mm ² maximum	150 m
• with conductor cross-section = 2.5 mm ² maximum	250 m
Protective and monitoring functions	
product function	
• asymmetry detection	Yes
• blocking current evaluation	Yes
• power factor monitoring	Yes
• ground fault detection	Yes
• ground-fault monitoring	No
• phase failure detection	Yes
• phase sequence recognition	Yes
• voltage detection	Yes
• monitoring of number of start operations	Yes
• overvoltage detection	Yes
• overcurrent detection 1 phase	Yes
• undervoltage detection	Yes
• undercurrent detection 1 phase	Yes
• active power monitoring	Yes
product function	
• current detection	Yes
• overload protection	Yes
• evaluation of thermistor motor protection	Yes
total cold resistance number of sensors in series maximum	1.5 kΩ
response value of thermoresistor	3 400 ... 3 800 Ω
• of the short-circuit control	9 Ω
release value of thermoresistor	1 500 ... 1 650 Ω
Motor control functions	
product function	
• parameterizable overload relay	Yes
• circuit breaker control	Yes
• direct start	Yes
• reverse starting	Yes
• star-delta circuit	Yes
• star-delta reversing circuit	Yes
• Dahlander circuit	Yes
• Dahlander reversing circuit	Yes
• pole-changing switch circuit	Yes
• pole-changing switch reversing circuit	Yes
• slide control	Yes
• valve control	Yes
Communication/ Protocol	
protocol is supported	
• PROFIBUS DP protocol	No
• PROFINET IO protocol	Yes
• PROFIsafe protocol	Yes
• Modbus RTU	No
• EtherNet/IP	No
• OPC UA Server	Yes
• LLDP	Yes
• Address Resolution Protocol (ARP)	Yes
• SNMP	Yes
• HTTPS	Yes
• NTP	Yes
• Media Redundancy Protocol (MRP)	Yes
product function	
• web server	Yes
• shared device	Yes

• at the Ethernet interface Autocrossover • at the Ethernet interface Autonegotiation • at the Ethernet interface Autosensing • Media Redundancy Protocol for Planned Duplication (MRPD) • is supported Device Level Ring (DLR) • is supported PROFINET system redundancy (S2) • supports PROFINET energy measured values • supports PROFINET energy shutdown	Yes Yes Yes Yes No Yes Yes Yes
transfer rate	100 Mbit/s
transfer rate maximum	100 Mbit/s
PROFINET conformity class	C
identification & maintenance function • I&M0 - device-specific information • I&M1 - higher level designation/location designation • I&M2 - installation date • I&M3 - comment	Yes Yes Yes Yes
type of electrical connection of the communication interface	2x RJ45
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting
height	111 mm
width	45 mm
depth	124 mm
required spacing • top • bottom • left • right	40 mm 40 mm 0 mm 0 mm
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes
type of electrical connection • for auxiliary and control circuit	screw-type terminals
type of connectable conductor cross-sections • solid • finely stranded with core end processing • for AWG cables solid • for AWG cables stranded	1x (0.5 ... 4.0mm ²), 2x (0.5 ... 2.5 mm ²) 1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.5 mm ²) 1x (20 ... 12), 2x (20 ... 14) 1x (20 ... 14), 2x (20 ... 16)
tightening torque with screw-type terminals	0.8 ... 1.2 N·m
tightening torque [lbf·in] with screw-type terminals	7 ... 10.3 lbf·in
Ambient conditions	
installation altitude at height above sea level maximum • note	2 000 m Restrictions apply to higher installation altitudes, see: https://support.industry.siemens.com/cs/document/109995153
ambient temperature • during operation • during storage • during transport	-25 ... +60 °C -40 ... +80 °C -40 ... +80 °C
environmental category • during operation according to IEC 60721 • during storage according to IEC 60721 • during transport according to IEC 60721	3K6 (no formation of ice, no condensation, relative humidity 10 ... 95%), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6 1K6 (no condensation, relative humidity 10 ... 95%), 1C2 (no salt mist), 1S2 (sand must not get into the devices), 1M4 2K2, 2C1, 2S1, 2M2
relative humidity • during operation	5 ... 95 %
contact rating of auxiliary contacts according to UL	B300 / R300
Short-circuit protection	
design of short-circuit protection per output	Fuse links: gG 6 A, quick-response 10 A (IEC 60947-5-1), miniature circuit-

		breaker C char.: 1.6 A (IEC 60947-5-1) or 6 A ($I_K < 500$ A)
Electrical Safety		
touch protection against electrical shock		finger-safe
ATEX		
certificate of suitability • IECEx • according to ATEX directive 2014/34/EU • according to UKCA		Yes; IECEx BVS 20.0020 / IECEx PTB 18.0004X BVS 06 ATEX F001, PTB 18 ATEX 5003 X ITS21UKEX0464, ITS21UKEX0455X
Galvanic isolation		
(electrically) protective separation according to IEC 60947-1		All circuits with protective separation (double creepage paths and clearances), the information in the "Protective Separation" test report, No. A0258, must be observed (link see further information)
design of the electrical isolation • note		Protective separation in accordance with IEC 60947-1 for all circuits Test report No. A0258 must be observed (https://support.industry.siemens.com/cs/document/109748152)
Control circuit/ Control		
product function soft starter control		Yes
type of voltage of the control supply voltage		DC
control supply voltage at DC rated value		24 V
control supply voltage 1 at DC rated value		24 V
operating range factor control supply voltage rated value at DC • initial value • full-scale value		0.85 1.2
inrush current peak • at 24 V		17 A
duration of inrush current peak • at 24 V		1.1 ms
Approvals Certificates		
Environment		General Product Approval
Environmental Confirmations     		
General Product Approval		EMV
     		
For use in hazardous locations		Test Certificates
 		Miscellaneous Special Test Certificate Type Test Certificates/Test Report Special Test Certificate
Maritime application		other
    		Confirmation
other		Industrial Communication



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7011-1AB00-0>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7011-1AB00-0>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UF7011-1AB00-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7011-1AB00-0&lang=en





last modified:

4/4/2026