

Siemens
EcoTech



communication module PROFINET High-Feature with integrated switch



product brand name	SIRIUS
product category	Communication modules
product designation	Communication module
design of the product	PROFINET High Feature with integrated switch
product type designation	3RW59
manufacturer's article number of soft starter	3RW55
General technical data	
reference code according to IEC 81346-2	A
Substance Prohibitance (day/month/year)	02/11/2019
SVHC substance name	Lead monoxide (lead oxide) CAS-No. 1317-36-8 4,4'-isopropylidenediphenol (Bisphenol A, BPA) CAS-No. 80-05-7
Net Weight	0.125 kg
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw fixing
height	126 mm
width	28 mm
depth	82 mm
weight without packaging	0.1 kg
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m
ambient temperature	
• during operation	-25 ... +60 °C; observe derating of basic unit above 40 °C
• during storage and transport	-40 ... +80 °C
environmental category	
• during operation according to IEC 60721	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
• during storage according to IEC 60721	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
• during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2 (max. height of fall 0.8 m)
Electrical Safety	
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
Approvals Certificates	
Environment	General Product Approval

EMV	For use in hazard- ous locations	Test Certificates	Maritime application
-----	-------------------------------------	-------------------	----------------------



[Miscellaneous](#)

[Type Test Certific-
ates/Test Report](#)



Maritime application	other	Industrial Communication
----------------------	-------	--------------------------



[Confirmation](#)

[Confirmation](#)



[PROFINET](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5950-0CH00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RW5950-0CH00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5950-0CH00&lang=en

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5950-0CH00>

Characteristic curves

https://curves.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>

Characteristic: Tripping characteristics, I²t, Let-through current



<https://support.industry.siemens.com/cs/ww/en/ps/3RW5950-0CH00/char>

Characteristic: Installation altitude


https://www.automation.siemens.com/bilddb/index.aspx?gridview=view2&objkey=G_NSB0_XX_01704&showdetail=true&view=Search

Simulation Tool for Soft Starters (STS)

<https://support.industry.siemens.com/cs/ww/en/view/101494917>



-A



-X31

-X1:P1

-X1:P2

