



SIRIUS safety relay Power supply for 3SK1 Advanced series $U_s = 110-240\text{ V}$
AC/DC screw terminal

product brand name	SIRIUS
product category	Safety relays
product designation	Power supply
product type designation	3SK1
Product Function	
suitability for use safety-related function	Yes
General technical data	
certificate of suitability UL approval	Yes
power loss [W] maximum	2.5 W
insulation voltage rated value	300 V
degree of pollution	3
overvoltage category	3
surge voltage resistance rated value	4 000 V
consumed current maximum	0.25 A
protection class IP of the enclosure	IP20
shock resistance	10 g / 11 ms
vibration resistance according to IEC 60068-2-6	5 ... 500 Hz: 0.75 mm
reference code according to IEC 81346-2	T
Substance Prohibitance (day/month/year)	11/05/2012
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol CAS-No. 79-94-7 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol CAS-No. 119-47-1
Net Weight	0.175 kg
Ambient conditions	
installation altitude at height above sea level maximum	4 000 m
• note	Derating, see Product Notification 109792701
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C
relative humidity during operation	10 ... 95 %
air pressure according to SN 31205	900 ... 1 060 hPa
Electromagnetic compatibility	
EMC emitted interference	IEC 60947-5-1, Class A
Short-circuit protection	
design of short-circuit protection	automatically start-up
Outputs	



property of the output short-circuit proof		Yes
Control circuit/ Control		
type of voltage		AC/DC
control supply voltage at AC		
• at 50 Hz rated value		110 ... 240 V
• at 60 Hz rated value		110 ... 240 V
control supply voltage at DC rated value		110 ... 240 V
operating range factor control supply voltage rated value at DC		
• initial value		0.85
• full-scale value		1.1
operating range factor control supply voltage rated value at AC at 50 Hz		
• initial value		0.85
• full-scale value		1.1
operating range factor control supply voltage rated value at AC at 60 Hz		
• initial value		0.85
• full-scale value		1.1
Installation/ mounting/ dimensions		
mounting position		any
fastening method		screw and snap-on mounting
height		100 mm
width		22.5 mm
depth		121.5 mm
required spacing		
• with side-by-side mounting at the side		0 mm
• for grounded parts at the side		5 mm
Connections/ Terminals		
type of electrical connection		screw terminal
type of connectable conductor cross-sections		
• solid		1x (0.5 ... 2.5 mm²), 2x (1.0 ... 1.5 mm²)
• finely stranded with core end processing		1x (0.5 ... 2.5 mm²), 2x (0.5 ... 1.0 mm²)
• for AWG cables solid		1x (20 ... 14), 2x (18 ... 16)
Approvals Certificates		
Environment	General Product Approval	EMV




[Environmental Confirmations](#)



EMV	Functional Safety	Test Certificates	other
	Type Examination Certificate	Type Test Certificates/Test Report	Confirmation
			Confirmation

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012 Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SK1230-1AW20 Cax online generator https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SK1230-1AW20 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SK1230-1AW20





last modified:

5/8/2026 