



SIRIUS ACT with PROFINET: standard interface module with extended inputs and outputs 24 V DC, spring-loaded terminal, front plate mounting, 1 to 20 terminal modules connectable, with additional 1 DQ + 4 DI + 1 AI

product brand name	SIRIUS ACT
product designation	Interface module for PROFINET
product type designation	3SU1
Display	
display version	
for diagnostic function: Supply voltage monitoring power LED	Yes
status Tx/Rx link	Yes
General technical data	
product function	
reverse polarity protection	Yes
diagnostics function	Yes
alarms	Yes
I&M data	Yes; I&M0 ... I&M3
firmware version	2.1.4
hardware version	1
configuration function with dataset	Yes
software version with STEP 7 required	TIA Portal V13 SP1
software version with STEP 7 in the TIA Portal required	TIA portal V13
number of units per rack maximum	20
number of submodules per station maximum	24
power loss [W] typical	0.6 W
insulation voltage rated value	30 V
degree of pollution	3
type of voltage	
of the operating voltage	DC
of the input voltage	DC
surge voltage resistance rated value	0.8 kV
consumed current	
maximum	150 mA
rated value	28 mA
protection class IP	IP20
shock resistance	
according to IEC 60068-2-27	sinusoidal half-wave 15 g / 11 ms
for railway applications according to EN 61373	Category 1, Class B
vibration resistance	

• according to IEC 60068-2-6 • for railway applications according to EN 61373	10 ... 500 Hz: 5 g Category 1, Class B
reference code according to IEC 81346-2	K
Substance Prohibitance (day/month/year)	08/24/2018
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1
Net Weight	149 g
operating voltage rated value minimum	20.4 V
I2t value	0.008 A²·s
Supply voltage	
supply voltage at DC rated value	24 V
Communication/ Protocol	
protocol is supported	
• PROFINET IO protocol • PROFIsafe protocol	Yes No
product function at the Ethernet interface	
• Autocrossover • Autonegotiation	Yes Yes
protocol at the 1st interface media redundancy protocol	No
product function at the 1st interface PROFINET IO device	Yes
product function of the PROFINET IO device is supported PROFINET system redundancy	No
service as PROFINET IO device	
• prioritized startup • isochronous mode • supports Shared Device • supports PROFIenergy • IRT • MRP • MRPD	No No No No No No No
service for open IE communication	
• LLDP • SNMP • TCP/IP	Yes Yes Yes
GSD version/revision with PROFINET required	V2.34
transmission mode for Industrial Ethernet	PROFINET with 100 Mbps full duplex (100BASE-TX)
network load class according to PROFINET	I
specification for Security Level 1 test according to PROFINET	Resilient to network loading
Control circuit/ Control	
inrush current maximum	16 A
Galvanic isolation	
galvanic isolation between PROFINET and all other circuits	Yes
Inputs/ Outputs	
number of digital inputs	4
• safety-related	0
number of analog inputs	1
number of digital outputs	1
Connections/ Terminals	
type of electrical connection	spring-loaded terminals
connectable conductor cross-section for auxiliary contacts	
• solid or stranded • finely stranded with core end processing maximum	0.2 ... 2.5 mm² 2.5 mm²
connectable conductor cross-section	
• solid • solid with core end processing • finely stranded with core end processing	0.2 ... 2.5 mm² 0.2 ... 2.5 mm² 0.25 ... 2.5 mm²

finely stranded without core end processing	0.2 ... 2.5 mm²	
AWG number as coded connectable conductor cross section	26 ... 12	
Safety related data		
product function suitable for safety function	No	
service life maximum	20 a	
Interfaces		
design of the interface - Ethernet interface - Fast Ethernet interface	Yes; for Ethernet services Yes; PROFINET with 100 Mbps	
interface design 1 - integrated switch - RJ45 (Ethernet)	No Yes	
number of ports at the 1st interface	1	
number of interfaces according to PROFINET	1	
Ambient conditions		
ambient temperature - during operation - during storage	-25 ... +60 °C -40 ... +80 °C	
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted)	
explosion protection marking for intrinsic safety of related equipment EEx ia	No	
explosion protection marking for intrinsic safety of related equipment EEx ib	No	
Installation/ mounting/ dimensions		
fastening method of modules and accessories	Front plate mounting	
height	80 mm	
width	40 mm	
depth	72 mm	
Approvals Certificates		
Environmental Product Declaration		
- global warming potential [CO2 eq] / during manufacturing - global warming potential [CO2 eq] / during operation - global warming potential [CO2 eq] / after end of life - global warming potential [CO2 eq] / total	0.566 kg 0.235 kg -0.0145 kg 0.787 kg	
Environment	General Product Approval	
Environmental Confirmations     		
General Product Approval	Test Certificates	Maritime application
	Type Test Certificates/Test Report Special Test Certificate	  
Maritime application	other	Industrial Communication
	Confirmation 	PROFINET

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1400-1LK10-3BA1>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1400-1LK10-3BA1>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1400-1LK10-3BA1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1400-1LK10-3BA1&lang=en





last modified:

5/8/2026 