



basic device SIMOCODE pro V MR, MODBUS RTU interface 57.6 Kbps, RS-485, 4 I/3 O freely configurable, Us: 24 V DC, input for thermistor connection
monostable relay outputs, expandable by expansion modules

product brand name	SIMOCODE
product designation	Motor management system
design of the product	basic unit 2
product type designation	pro V MR
General technical data	
product function	
• current measurement	No
• voltage measurement	No
• active power measurement	Yes
• energy measurement	No
• frequency measurement	No
• bus communication	Yes
• data acquisition function	Yes
• diagnostics function	Yes
• password protection	Yes
• test function	Yes
• maintenance function	Yes
• MRRT redundancy procedure	No
product component	
• input for thermistor connection	Yes
• digital input	Yes
• input for analog temperature sensors	No
• input for ground fault detection	No
• relay output	Yes
product extension	
• temperature monitoring module	Yes
• current measuring module	Yes
• current/voltage measuring module	Yes
• fail-safe digital I/O module	Yes
• ground-fault monitoring module	Yes
• decoupling module	Yes
• analog I/O module	Yes
• digital I/O module with monostable outputs	Yes
• digital I/O module with bistable outputs	Yes
• control unit with display	Yes
• control unit	Yes
consumed active power	2.6 W
insulation voltage with degree of pollution 3 at AC rated value	300 V
surge voltage resistance rated value	4 000 V

shock resistance	
• according to IEC 60068-2-27	15 g / 11 ms
• vibration resistance	1 ... 6 Hz / 15 mm; 6 ... 500 Hz / 2 g
switching capacity current of the NO contacts of the relay outputs at AC-15	
• at 24 V	6 A
• at 120 V	6 A
• at 230 V	3 A
switching capacity current of the NO contacts of the relay outputs at DC-13	
• at 24 V	2 A
• at 60 V	0.55 A
• at 125 V	0.25 A
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) typical	100 000
buffering time in the event of power failure	0.05 s
reference code according to IEC 81346-2	F
continuous current of the NO contacts of the relay outputs	
• at 50 °C	6 A
• at 60 °C	5 A
type of input characteristic	Type 1 in accordance with EN 61131-2
Substance Prohibitance (day/month/year)	05/01/2012
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol CAS-No. 119-47-1
Net Weight	0.36 kg
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV (power ports) / 1 kV (signal ports)
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
• due to high-frequency radiation according to IEC 61000-4-6	10 V
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
conducted HF interference emissions according to CISPR11	corresponds to degree of severity A
field-bound HF interference emission according to CISPR11	corresponds to degree of severity A
Inputs/ Outputs	
product function	
• parameterizable inputs	Yes
• parameterizable outputs	Yes
number of inputs	4
• for thermistor connection	1
number of digital inputs with a common reference potential	4
digital input version	
• type 1 acc. to IEC 61131	Yes
input voltage at digital input at DC	
• rated value	24 V
number of outputs	3
number of semiconductor outputs	0
number of outputs as contact-affected switching element	3
switching behavior	monostable
number of relay outputs	3
type of relay outputs	Monostable

wire length for digital signals maximum	300 m
wire length for thermistor connection	
• with conductor cross-section = 0.5 mm ² maximum	50 m
• with conductor cross-section = 1.5 mm ² maximum	150 m
• with conductor cross-section = 2.5 mm ² maximum	250 m
Protective and monitoring functions	
product function	
• asymmetry detection	Yes
• blocking current evaluation	Yes
• power factor monitoring	Yes
• ground fault detection	Yes
• ground-fault monitoring	No
• phase failure detection	Yes
• phase sequence recognition	Yes
• voltage detection	Yes
• monitoring of number of start operations	Yes
• overvoltage detection	Yes
• overcurrent detection 1 phase	Yes
• undervoltage detection	Yes
• undercurrent detection 1 phase	Yes
• active power monitoring	Yes
product function	
• current detection	Yes
• overload protection	Yes
• evaluation of thermistor motor protection	Yes
total cold resistance number of sensors in series maximum	1.5 kΩ
response value of thermoresistor	3 400 ... 3 800 Ω
• of the short-circuit control	9 Ω
release value of thermoresistor	1 500 ... 1 650 Ω
Motor control functions	
product function	
• parameterizable overload relay	Yes
• circuit breaker control	Yes
• direct start	Yes
• reverse starting	Yes
• star-delta circuit	Yes
• star-delta reversing circuit	Yes
• Dahlander circuit	Yes
• Dahlander reversing circuit	Yes
• pole-changing switch circuit	Yes
• pole-changing switch reversing circuit	Yes
• slide control	Yes
• valve control	Yes
Communication/ Protocol	
protocol is supported	
• PROFIBUS DP protocol	No
• PROFINET IO protocol	No
• PROFI-safe protocol	No
• Modbus RTU	Yes
• EtherNet/IP	No
• OPC UA Server	No
• LLDP	No
• Address Resolution Protocol (ARP)	No
• SNMP	No
• HTTPS	No
• NTP	No
• Media Redundancy Protocol (MRP)	No
product function	
• web server	No

• shared device • at the Ethernet interface Autocrossover • at the Ethernet interface Autonegotiation • at the Ethernet interface Autosensing • is supported Device Level Ring (DLR) • is supported PROFINET system redundancy (S2) • supports PROFinergy measured values • supports PROFinergy shutdown	No
transfer rate maximum	No
identification & maintenance function	No
• I&M0 - device-specific information • I&M1 - higher level designation/location designation • I&M2 - installation date • I&M3 - comment	No
type of electrical connection of the communication interface	No
Installation/ mounting/ dimensions	No
mounting position	0.057 Mbit/s
fastening method	Yes
height	Yes
width	Yes
depth	Yes
required spacing	9-pin D-sub socket (57.6 Kbit) / screw terminal (57.6 Kbit)
• top • bottom • left • right	
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	any
type of electrical connection	screw and snap-on mounting
• for auxiliary and control circuit	111 mm
type of connectable conductor cross-sections	45 mm
• solid • finely stranded with core end processing • for AWG cables solid • for AWG cables stranded	124 mm
tightening torque with screw-type terminals	40 mm
tightening torque [lbf·in] with screw-type terminals	40 mm
type of connectable conductor cross-sections for PROFIBUS wire	0 mm
	0 mm
installation altitude at height above sea level maximum	
• note	
ambient temperature	
• during operation • during storage • during transport	
environmental category	
• during operation according to IEC 60721 • during storage according to IEC 60721 • during transport according to IEC 60721	
relative humidity	
• during operation	
contact rating of auxiliary contacts according to UL	
Short-circuit protection	
design of short-circuit protection per output	

Electrical Safety					
touch protection against electrical shock	finger-safe				
ATEX					
certificate of suitability • according to ATEX directive 2014/34/EU • acc. to Equipment and Protective System Intended for Use in Potentially Explosive Atmospheres Regulations 2016 (S.I. 2016 No.1107) • according to UKCA	BVS 06 ATEX F001 ITS21UKEX0464, ITS21UKEX0455X ITS21UKEX0464, ITS21UKEX0455X				
Galvanic isolation					
(electrically) protective separation according to IEC 60947-1	All circuits with protective separation (double creepage paths and clearances), the information in the "Protective Separation" test report, No. A0258, must be observed (link see further information)				
design of the electrical isolation • note	Protective separation in accordance with IEC 60947-1 for all circuits Test report No. A0258 must be observed (https://support.industry.siemens.com/cs/document/109748152)				
Control circuit/ Control					
product function soft starter control	Yes				
type of voltage of the control supply voltage	DC				
control supply voltage at DC rated value	24 V				
control supply voltage 1 at DC rated value	24 V				
operating range factor control supply voltage rated value at DC • initial value • full-scale value	0.8 1.2				
inrush current peak • at 24 V	11 A				
duration of inrush current peak • at 24 V	1.1 ms				
Approvals Certificates					
Environment	General Product Approval				
Environmental Confirmations	    				
General Product Approval	EMV	For use in hazardous locations			
 EG-Konf.	     IECEX				
For use in hazardous locations	Test Certificates				
 ATEX	 IECEX	Miscellaneous	Special Test Certificate	Type Test Certificates/Test Report	Special Test Certificate
Maritime application	other				
 ABS	 DNV	 LRS	 RMRS	Confirmation	Confirmation
other	Industrial Communication				



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7012-1AB00-0>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7012-1AB00-0>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UF7012-1AB00-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7012-1AB00-0&lang=en





last modified:

4/4/2026 