



Decoupling module for installation upstream of the current/voltage measuring module at the system interface for application in ungrounded supply systems

product brand name	SIMOCODE
product designation	Decoupling module
product type designation	3UF7
General technical data	
product component	
• input for thermistor connection	No
insulation voltage	
• for wires of main circuit according to IEC 60947-1 rated value	6 kV
surge voltage resistance rated value	4 000 V
vibration resistance	1 ... 6 Hz / 15 mm; 6 ... 500 Hz / 2 g
reference code according to IEC 81346-2	Q
Substance Prohibitance (day/month/year)	05/01/2012
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol CAS-No. 119-47-1
Net Weight	0.135 kg
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	1 kV
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
field-based interference according to IEC 61000-4-3	10 V/m
Inputs/ Outputs	
number of outputs as contact-affected switching element	0
Protective and monitoring functions	
product function	
• voltage detection	No
product function	
• current detection	No
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting
height	92 mm
width	22.5 mm

depth	124 mm
Connections/ Terminals	
type of electrical connection	
- for main current circuit - for auxiliary and control circuit	straight-through transformers screw-type terminals
Ambient conditions	
installation altitude at height above sea level	
3 maximum	4 000 m
ambient temperature	
- during operation - during storage - during transport	-25 ... +60 °C -40 ... +80 °C -40 ... +80 °C
environmental category	
- during operation according to IEC 60721 - during storage according to IEC 60721 - during transport according to IEC 60721	3K6 (no formation of ice, no condensation, relative humidity 10 ... 95%), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6 1K6 (no condensation, relative humidity 10 ... 95%), 1C2 (no salt mist), 1S2 (sand must not get into the devices), 1M4 2K2, 2C1, 2S1, 2M2
relative humidity during operation	5 ... 95 %
IEC 61508	
Safety Integrity Level (SIL) according to IEC 61508	1
Approvals Certificates	
Environment	General Product Approval

[Environmental Con-
firmations](#)



EMV	For use in hazard- ous locations	Test Certificates	Maritime application
-----	-------------------------------------	-------------------	----------------------



[Type Test Certi-
ficates/Test Report](#)



Maritime application	other	Industrial Communication
----------------------	-------	--------------------------



[Confirmation](#)

[Confirmation](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7150-1AA00-0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7150-1AA00-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UF7150-1AA00-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7150-1AA00-0&lang=en



