



Figure similar

SIPLUS LOGO! AM2 based on 6ED1055-1MA00-0BA2 with conformal coating, -40...+70 °C, start up -25 °C, expansion module, PS/: 12/24 V DC, 2 AI, 0-10 V or 0/4-20 mA for LOGO! 8

General information	
based on	6ED1055-1MA00-0BA2
Installation type/mounting	
Mounting	on 35 mm DIN rail, 2 spacing units wide
Supply voltage	
Rated value (DC)	
• 12 V DC	Yes; 10.8 V DC to 28.8 V DC
• 24 V DC	Yes; 10.8 V DC to 28.8 V DC
Input current	
Current consumption, typ.	30 mA
Analog inputs	
Number of analog inputs	2
Input ranges	
• Voltage	Yes
• Current	Yes
• Resistance thermometer	No
Input ranges (rated values), voltages	
• 0 to +10 V	Yes
Input ranges (rated values), currents	
• 0 to 20 mA	Yes; 0 mA or 4 mA to 20 mA
Input ranges (rated values), resistance thermometer	
• Pt 100	No
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes
Degree and class of protection	
IP degree of protection	IP20
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	16.5 kg
— global warming potential, (during production) [CO2 eq]	3.22 kg
— global warming potential, (during operation) [CO2 eq]	13.4 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.124 kg

Ambient conditions			
Ambient temperature during operation			
• min. • max. • At cold restart, min.		-40 °C; = Tmin; Startup @ -25 °C 70 °C; = Tmax -25 °C; incl. condensation / frost permitted (no commissioning under condensation conditions)	
Ambient temperature during storage/transportation			
• min. • max.		-40 °C 70 °C	
Altitude during operation relating to sea level			
• Installation altitude above sea level, max. • Ambient air temperature-barometric pressure-altitude		5 000 m Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax -20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)	
Relative humidity			
• With condensation, tested in accordance with IEC 60068-2-38, max.		100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation	
Resistance			
Coolants and lubricants			
— Resistant to commercially available coolants and lubricants		Yes; Incl. diesel and oil droplets in the air	
Use in stationary industrial systems			
— to biologically active substances according to EN 60721-3-3		Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request	
— to chemically active substances according to EN 60721-3-3		Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *	
— to mechanically active substances according to EN 60721-3-3		Yes; Class 3S4 incl. sand, dust, *	
Use on ships/at sea			
— to biologically active substances according to EN 60721-3-6		Yes; Class 6B2 mold and fungal spores (excluding fauna); Class 6B3 on request	
— to chemically active substances according to EN 60721-3-6		Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *	
— to mechanically active substances according to EN 60721-3-6		Yes; Class 6S3 incl. sand, dust; *	
Usage in industrial process technology			
— Against chemically active substances acc. to EN 60654-4		Yes; Class 3 (excluding trichlorethylene)	
— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04		Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)	
Remark			
— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04		* The supplied plug covers must remain in place over the unused interfaces during operation!	
Conformal coating			
• Coatings for printed circuit board assemblies acc. to EN 61086 • Protection against fouling acc. to EN 60664-3 • Military testing according to MIL-I-46058C, Amendment 7 • Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A		Yes; Class 2 for high reliability Yes; Type 1 protection Yes; Discoloration of coating possible during service life Yes; Conformal coating, Class A	
Dimensions			
Width		35.5 mm	
Height		90 mm	
Depth		58 mm	
Classifications			
		Version	Classification
	eClass	16	27-24-22-01
	eClass	14	27-24-22-01
	eClass	12	27-24-22-01
	eClass	9.1	27-24-22-01

eClass	9	27-24-22-01
eClass	8	27-24-22-01
eClass	7.1	27-24-22-01
eClass	6	27-24-22-01
ETIM	10	EC001420
ETIM	9	EC001420
ETIM	8	EC001420
ETIM	7	EC001420
IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)





[China RoHS](#)





General Product Approval

EMV

Environment

[China RoHS](#)







last modified:

10/9/2024 