



SITOP PSU300S/3AC/24VDC/10A

SITOP PSU300S 24 V/10 A stabilized power supply input: 400-500 V 3 AC output: 24 V DC/10 A

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP1434-2BA20
input	
type of the power supply network	3-phase AC
supply voltage at AC	
• minimum rated value	400 V
• maximum rated value	500 V
• initial value	340 V
• full-scale value	550 V
wide range input	Yes
buffering time for rated value of the output current in the event of power failure minimum	7 ms
operating condition of the mains buffering	at $V_{in} = 400 \text{ V}$
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 400 V	0.7 A
• at rated input voltage 500 V	0.6 A
current limitation of inrush current at 25 °C maximum	20 A
I ² t value maximum	0.5 A ² ·s
fuse protection type	none
fuse protection type in the feeder	Required: 3-pole connected miniature circuit breaker 3 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489-listed, DIVQ)
output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28 V; max. 240 W
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.15 %
residual ripple	
• maximum	200 mV
voltage peak	
• maximum	240 mV

display version for normal operation	Green LED for 24 V OK
type of signal at output	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
behavior of the output voltage when switching on	Overshoot of $V_{out} < 5\%$
response delay maximum	1.5 s
voltage increase time of the output voltage • typical • maximum	50 ms 500 ms
output current • rated value • rated range	10 A 0 ... 10 A; 12 A up to +45°C; +60 ... +70 °C: Derating 5%/K
supplied active power typical	240 W
bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	91 %
power loss [W] • at rated output voltage for rated value of the output current typical	23 W
closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	1 %
setting time • load step 50 to 100% typical • load step 100 to 50% typical	3 ms 3 ms
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	3 %
setting time • load step 10 to 90% typical • load step 90 to 10% typical • maximum	4 ms 4 ms 10 ms
protection and monitoring	
design of the overvoltage protection	protection against overvoltage in case of internal fault $V_{out} < 35\text{ V}$
property of the output short-circuit proof	Yes
design of short-circuit protection • typical	Constant current characteristic 13 A
overcurrent overload capability • in normal operation	overload capability 150 % I_{out} rated up to 5 s/min
enduring short circuit current RMS value • maximum	16 A
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
protection class IP	IP20
EMC	
standard • for emitted interference • for mains harmonics limitation • for interference immunity	EN 55022 Class B EN 61000-3-2 EN 61000-6-2
standards, specifications, approvals	
certificate of suitability • CE marking • UL approval • UKCA marking • EAC approval • NEC Class 2	Yes Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 Yes Yes No
type of certification	

• BIS	Yes; R-41183539
• CB-certificate	Yes
MTBF at 40 °C	500 000 h
standards, specifications, approvals hazardous environments	
certificate of suitability	
• IECEx	No
• ATEX	No
• ULhazloc approval	No
• FM registration	No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	Yes
• Lloyds Register of Shipping (LRS)	No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	642.2 kg
• during manufacturing	18 kg
• during operation	623.6 kg
• after end of life	0.52 kg
ambient conditions	
ambient temperature	
• during operation	-25 ... +70 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	screw terminal
• at input	L1, L2, L3, PE: 1 screw terminal each for 0.05 ... 2.5 mm² single-core/finely stranded
• at output	+, -: 2 screw terminals each for 0.2 ... 2.5 mm²
• for auxiliary contacts	13, 14 (alarm signal): 1 screw terminal each for 0.2 ... 2.5 mm²
mechanical data	
width × height × depth of the enclosure	70 × 125 × 120 mm
installation width × mounting height	70 mm × 225 mm
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
• DIN-rail mounting	Yes
• S7 rail mounting	No
• wall mounting	No
housing can be lined up	Yes
net weight	0.7 kg
accessories	
electrical accessories	Redundancy module, buffer module, selectivity module, DC UPS
mechanical accessories	Device identification label 20 mm × 7 mm, pale turquoise 3RT1900-1SB20
further information internet links	
internet link	
• to website: Industry Mall	https://mall.industry.siemens.com
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to web page: power supplies	https://siemens.com/sitop
• to website: CAX-Download-Manager	https://siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions

that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Classifications			
		Version	Classification
	eClass	16	27-04-07-01
	eClass	14	27-04-07-01
	eClass	12	27-04-07-01
	eClass	9.1	27-04-07-01
	eClass	9	27-04-07-01
	eClass	8	27-04-90-02
	eClass	7.1	27-04-90-02
	eClass	6	27-04-90-02
	ETIM	10	EC002540
	ETIM	9	EC002540
	ETIM	8	EC002540
	ETIM	7	EC002540
	IDEA	4	4130
	UNSPSC	15	39-12-10-04

Approvals Certificates			
Environmental Product Declaration			
● global warming potential [CO2 eq] / during manufacturing		18 kg	
● global warming potential [CO2 eq] / during operation		623.6 kg	
● global warming potential [CO2 eq] / after end of life		0.52 kg	
● global warming potential [CO2 eq] / total		642.2 kg	
Environment	General Product Approval		



[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[China RoHS](#)

General Product Approval			Maritime application		

last modified: 5/5/2026