



SITOP PSE200U/4X0.5-3A/SEO/NECCCLASS2

SITOP PSE200U 3 A NEC CLASS 2 selectivity module 4-channel input: 24 V DC/12 A output: 24 V/4x 3 A NEC class 2 threshold value adjustable 0.5-3 A with status message for each output

General information

Technical Product Detail Page

<https://i.siemens.com/1P6EP1961-2BA61>

input

type of the power supply network	Controlled DC voltage
supply voltage at DC rated value	24 V
input voltage at DC	22 ... 30 V
overvoltage overload capability	35 V
input current at rated input voltage 24 V rated value	12 A

output

voltage curve at output	controlled DC voltage
formula for output voltage	$V_{in} - \text{approx. } 0.2 \text{ V}$
relative overall tolerance of the voltage note	In accordance with the supplying input voltage
number of outputs	4
output current up to 60 °C per output rated value	3 A
adjustable current response value current of the current-dependent overload release	0.5 ... 3 A
type of response value setting	via potentiometer
response delay maximum	5 s
product feature parallel switching of outputs	No
type of outputs connection	simultaneous switch-on of all outputs after power-up of the supply voltage > 20 V, delay time of 25 ms, 100 ms, or "load-optimized" via DIP switch configurable for sequential switch-on

efficiency

efficiency in percent	97 %
power loss [W] at rated output voltage for rated value of the output current typical	9 W

switch-off characteristic

switching characteristic	
- of the excess current - of the current limitation - of the immediate switch-off	$I_{out} = 1.0 \dots 1.1 \times \text{set value}$, switch-off after approx. 5 s $I_{out} = 1.1 \times \text{set value}$, switch-off after typ. 100 ms $I_{out} > \text{set value}$ and $V_{in} < 20 \text{ V}$, switch-off after approx. 0.5 ms
residual current at switch-off typical	1 mA
design of the reset device/resetting mechanism	via sensor per output
remote reset function	non-isolated 24 V input (signal level "high" at > 15 V)

protection and monitoring

fuse protection type at input	5 A per output (not accessible)
display version for normal operation	Three-color LED per output: green LED for "Output switched through"; yellow

	LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"
design of the switching contact for signaling function	Status signal output (pulse/pause signal, can be evaluated via Simatic function block)
safety	
galvanic isolation between input and output at switch-off	No
standard for safety	according to EN 62368-1
operating resource protection class	Class III
protection class IP	IP20
standard	
• for emitted interference	EN 55022 Class B
• for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259
• UKCA marking	Yes
• EAC approval	Yes
• NEC Class 2	Yes; according to UL1310
type of certification	
• CB-certificate	Yes
MTBF at 40 °C	755 915 h
standards, specifications, approvals hazardous environments	
certificate of suitability	
• IECEx	No
• ATEX	No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Det Norske Veritas (DNV)	Yes
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	254.1 kg
• during manufacturing	7.4 kg
• during operation	246.5 kg
• after end of life	0.17 kg
Siemens eco profile (SEP)	Siemens EcoTech
ambient conditions	
ambient temperature	
• during operation	-25 ... +60 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	screw terminal
• at input	+24 V: 2 screw terminals for 0.5 ... 16 mm ² ; 0 V: 2 screw terminals for 0.5 ... 4 mm ²
• at output	Output 1 ... 4: 1 screw terminal each for 0.5 ... 4 mm ²
• for auxiliary contacts	Remote reset: 1 screw terminal for 0.5 ... 4 mm ²
• for signaling contact	1 screw terminal for 0.5 ... 4 mm ²
mechanical data	
width × height × depth of the enclosure	72 × 80 × 72 mm
installation width × mounting height	72 mm × 180 mm
required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm

• right	0 mm		
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15		
• DIN-rail mounting	Yes		
• S7 rail mounting	No		
• wall mounting	No		
housing can be lined up	Yes		
net weight	0.2 kg		
accessories			
mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20		
further information internet links			
internet link			
• to website: Industry Mall	https://mall.industry.siemens.com		
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud		
• to web page: power supplies	https://siemens.com/sitop		
• to website: CAX-Download-Manager	https://siemens.com/cax		
• to website: Industry Online Support	https://support.industry.siemens.com		
identification link	Yes; acc. to IEC 61406-1:2022		
additional information			
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)		
security information			
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)		
Classifications			
		Version	Classification
	eClass	16	27-37-18-02
	eClass	14	27-37-18-02
	eClass	12	27-37-18-02
	eClass	9.1	27-37-18-02
	eClass	9	27-37-18-02
	eClass	8	27-37-18-02
	eClass	7.1	27-37-18-02
	eClass	6	27-37-18-02
	ETIM	10	EC001440
	ETIM	9	EC001440
	ETIM	8	EC001440
	ETIM	7	EC001440
	IDEA	4	4727
	UNSPSC	15	39-12-15-21
Approvals Certificates			
General Product Approval			



[Manufacturer Declaration](#)



EG-Konf.



[Declaration of Conformity](#)

[China RoHS](#)

General Product Approval



[Miscellaneous](#)



Maritime application

Environment

Environment



last modified:

6/28/2026