



SITOP PSU6200/3AC/24VDC/10A

SITOP PSU6200 24 V/10 A stabilized power supply input: 400 - 500 V AC output: 24 V DC/10 A with diagnostics interface

General information

Technical Product Detail Page

<https://i.siemens.com/1P6EP3434-7SB00-3AX0>

input

type of the power supply network	3-phase AC or DC
supply voltage at AC	
• minimum rated value	400 V
• maximum rated value	500 V
• initial value	323 V
• full-scale value	576 V
supply voltage at DC	500 ... 550 V
input voltage at DC	450 ... 600 V
buffering time for rated value of the output current in the event of power failure minimum	30 ms
operating condition of the mains buffering	at $V_{in} = 400 \text{ V}$
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 400 V	0.39 A
• at rated input voltage 500 V	0.32 A
current limitation of inrush current at 25 °C maximum	13 A
fuse protection type in the feeder	three-poled coupled circuit breaker from 4 A characteristic C to 16 A characteristic C or circuit breaker 3RV2011-1EA10 (setting 4 A) or 3RV2711-1ED10 (UL 489)

output

voltage curve at output	Controlled, isolated DC voltage
number of outputs	1
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28 V; max. 240 W (288 W up to 45°C)
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.2 %
• on slow fluctuation of ohm loading	0.1 %
residual ripple	

• maximum • typical	30 mV 20 mV
voltage peak	
• maximum • typical	30 mV 20 mV
display version for normal operation	Green LED for 24 V OK
type of signal at output	Electronic contact (NO contact, contact rating 30 V DC/0.1 A) for DC O.K. or diagnostic interface
behavior of the output voltage when switching on	Overshoot of Vout < 2 %
response delay maximum	0.5 s
voltage increase time of the output voltage	
• typical	100 ms
output current	
• rated value • rated range	10 A 0 ... 10 A; 12 A up to +45°C; +60 ... +70 °C: Derating 3%/K
supplied active power typical	240 W
short-term overload current	
• on short-circuiting during the start-up typical • at short-circuit during operation typical	12 A 12 A
parallel switching of outputs	can be set with DIP switch
bridging of equipment	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	95.4 %
power loss [W]	
• at rated output voltage for rated value of the output current typical • during no-load operation maximum	12 W 2.9 W
closed-loop control	
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	2 %
setting time	
• load step 10 to 90% typical • load step 90 to 10% typical • maximum	1 ms 1 ms 2 ms
protection and monitoring	
design of the overvoltage protection	< 32 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Shutdown and periodic restart attempts
• typical	12 A
overcurrent overload capability	
• in normal operation	overload capability 150 % Iout rated up to 5 s/min
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
protection class IP	IP20
EMC	
standard	
• for emitted interference • for mains harmonics limitation • for interference immunity	EN 55022 Class B EN 61000-3-2 EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
• CE marking • UL approval	Yes Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259

• UKCA marking • EAC approval • Regulatory Compliance Mark (RCM) • NEC Class 2 • SEMI F47	Yes Yes Yes No Yes
type of certification • BIS • CB-certificate	Yes; R-41188271 Yes
standards, specifications, approvals hazardous environments	
certificate of suitability • IECEx • ATEX • ULhazloc approval • FM registration	No No No No
standards, specifications, approvals marine classification	
shipbuilding approval Marine classification association • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Lloyds Register of Shipping (LRS)	Yes Yes No Yes No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration global warming potential [CO2 eq] • total • during manufacturing • during operation • after end of life Siemens eco profile (SEP)	Yes 327.6 kg 23.1 kg 303.8 kg 0.38 kg Siemens EcoTech
ambient conditions	
ambient temperature • during operation • during transport • during storage environmental category according to IEC 60721	-30 ... +70 °C; with natural convection a monotonically increasing start-up from -25 °C, safe start-up from -40 °C -40 ... +85 °C -40 ... +85 °C Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection • at input • at output • for auxiliary contacts	push-in terminals L1, L2, L3, PE: push-in for 0.5 ... 6 mm² +1, +2, -1, -2, -3: push-in for 0.5 ... 2.5 mm² 13, 14 (alarm signal): 1 push-in terminal each for 0.2 ... 1.5 mm²
mechanical data	
width × height × depth of the enclosure	45 × 135 × 155 mm
installation width × mounting height	45 mm × 225 mm
required spacing • top • bottom • left • right	45 mm 45 mm 0 mm 0 mm
fastening method • DIN-rail mounting • S7 rail mounting • wall mounting	Snaps onto DIN rail EN 60715 35x7.5/15 Yes No No
housing can be lined up	Yes
net weight	0.9 kg
accessories	
electrical accessories	Buffer module, redundancy module
mechanical accessories	Identification labels SIMATIC ET 200SP 6ES7193-6LF30-0AW0
further information internet links	

internet link	• to website: Industry Mall https://mall.industry.siemens.com • to web page: selection aid TIA Selection Tool https://www.siemens.com/tstcloud • to web page: power supplies https://siemens.com/sitop • to website: CAX-Download-Manager https://siemens.com/cax • to website: Industry Online Support https://support.industry.siemens.com
identification link	Yes; acc. to IEC 61406-1:2022

additional information

other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
-------------------	---

security information

security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)
----------------------	---

Classifications

	Version	Classification
eClass	16	27-04-07-01
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

Environmental Product Declaration	
• global warming potential [CO2 eq] / during manufacturing	23.1 kg
• global warming potential [CO2 eq] / during operation	303.8 kg
• global warming potential [CO2 eq] / after end of life	0.38 kg
• global warming potential [CO2 eq] / total	327.6 kg

Environment	General Product Approval
-------------	--------------------------



Siemens
EcoTech



[Manufacturer Declaration](#)

[Declaration of Conformity](#)

General Product Approval



[China RoHS](#)



General Product Approval

Maritime application



[BIS CRS](#)



last modified:

5/5/2026