



SITOP PSU2600/1ACDC/24VDC/5A

SITOP PSU2600 24 V/5 A Stabilized power supply input: 230 V AC output: 24 V DC/5 A

General information

Technical Product Detail Page

<https://i.siemens.com/1P6EP4333-0SB00-0AY0>

input

type of the power supply network	1-phase AC or DC
supply voltage at AC	
• minimum rated value	120 V
• maximum rated value	230 V
• initial value	85 V
• full-scale value	264 V
supply voltage at DC	110 ... 220 V
input voltage at DC	88 ... 265 V
wide range input	Yes
buffering time for rated value of the output current in the event of power failure minimum	30 ms
operating condition of the mains buffering	at $V_{in} = 230\text{ V}$
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 120 V	2.5 A
• at rated input voltage 230 V	1.4 A
current limitation of inrush current at 25 °C maximum	36 A
fuse protection type	3.15 A
fuse protection type in the feeder	None required. Fuse protection starting from 6 A Char. C possible

output

voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28.8 V; max. 120 W
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.2 %
residual ripple	
• maximum	50 mV
voltage peak	
• maximum	200 mV
display version for normal operation	Green LED for 24 V OK

type of signal at output	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	1 s
voltage increase time of the output voltage • maximum	500 ms
output current • rated value • rated range	5 A 0 ... 5 A; +60 °C
supplied active power typical	120 W
constant overload current • on short-circuiting during the start-up typical	6 A
bridging of equipment	No
efficiency	
efficiency in percent	89 %
power loss [W] • at rated output voltage for rated value of the output current typical • during no-load operation maximum	15 W 1 W
closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	1 %
setting time • load step 50 to 100% typical • load step 100 to 50% typical	0.2 ms 0.2 ms
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	2 %
setting time • load step 10 to 90% typical • load step 90 to 10% typical • maximum	0.2 ms 0.2 ms 10 ms
protection and monitoring	
design of the overvoltage protection	< 32 V
property of the output short-circuit proof	Yes
design of short-circuit protection • typical	Shutdown and periodic restart attempts 6 A
enduring short circuit current RMS value • typical	6 A
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV
operating resource protection class	Class I
leakage current • maximum • typical	3.5 mA 1.1 mA
protection class IP	IP20
EMC	
standard • for emitted interference • for mains harmonics limitation • for interference immunity	EN 55022 Class B EN 61000-3-2 EN 61000-6-2
standards, specifications, approvals	
certificate of suitability • CE marking • UL approval • EAC approval • NEC Class 2	Yes Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259 Yes No
type of certification	

• BIS • CB-certificate	Yes; R-41282421 Yes
standards, specifications, approvals hazardous environments	
certificate of suitability	
• IECEx • ATEX • ULhazloc approval • FM registration	No No No No
standards, specifications, approvals marine classification	
shipbuilding approval	No
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Lloyds Register of Shipping (LRS)	No No No No
ambient conditions	
ambient temperature	
• during operation • during transport • during storage	0 ... 60 °C; with natural convection -40 ... +85 °C -40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	screw terminal
• at input • at output • for auxiliary contacts	L1, N, PE: 1 screw terminal each for 0.2 ... 2.5 mm ² single-core/finely stranded +, -: 2 screw terminals each for 0.2 ... 2.5 mm ² 13, 14 (alarm signal): 1 screw terminal each for 0.05 ... 2.5 mm ²
mechanical data	
width × height × depth of the enclosure	42 × 125 × 125 mm
installation width × mounting height	42 mm × 225 mm
required spacing	
• top • bottom • left • right	50 mm 50 mm 0 mm 0 mm
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
• DIN-rail mounting • S7 rail mounting • wall mounting	Yes No No
housing can be lined up	Yes
net weight	0.6 kg
further information internet links	
internet link	
• to website: Industry Mall • to web page: selection aid TIA Selection Tool • to web page: power supplies • to website: CAX-Download-Manager • to website: Industry Online Support	https://mall.industry.siemens.com https://www.siemens.com/tstcloud https://siemens.com/sitop https://siemens.com/cax https://support.industry.siemens.com
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial

cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Classifications

	Version	Classification
eClass	16	27-04-07-01
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

General Product Approval



[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[China RoHS](#)



General Product Approval	Food, Pharmaceutical, Medical
--------------------------	-------------------------------

[BIS CRS](#)

[Special Test Certificate](#)

last modified:

5/5/2026