

Siemens
EcoTech



SIMATIC ET 200SP, digital output module, DQ 4x 24VDC/2A Standard, Pack quantity: 10 units, suitable for BU type A0, Color code CC02, Module diagnostics



Figure similar

General information	
Product type designation	DQ 4x24 V DC/2 A ST
HW functional status	From FS08
Firmware version	V1.1
• FW update possible	Yes
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC02
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V11 SP2 / V13
• STEP 7 configurable/integrated from version	V5.5 SP3 / -
• PROFIBUS from GSD version/GSD revision	GSD Revision 5
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	60 mA; without load
Output voltage	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	1 W
Address area	
Address space per module	
• Address space per module, max.	1 byte; + 1 byte for QI information

Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0
• 2-wire connection	BU type A0
• 3-wire connection	BU type A0 with AUX terminals or potential distributor module
• 4-wire connection	BU type A0 + Potential distributor module
Digital outputs	
Type of digital output	Source output (PNP, current-sourcing)
Number of digital outputs	4
Current-sinking	No
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes
• Response threshold, typ.	2.8 to 5.2 A
Limitation of inductive shutdown voltage to	Typ. L+ (-50 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
• with resistive load, max.	2 A
• on lamp load, max.	10 W
Load resistance range	
• lower limit	12 Ω
• upper limit	3 400 Ω
Output current	
• for signal "1" rated value	2 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", typ.	50 μ s
• "0" to "1", max.	50 μ s
• "1" to "0", typ.	100 μ s
• "1" to "0", max.	100 μ s
Parallel switching of two outputs	
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per channel, max.	2 A
• Current per module, max.	8 A
Total current of the outputs (per module)	
horizontal installation	
— up to 40 °C, max.	8 A
— up to 50 °C, max.	6 A
— up to 60 °C, max.	4 A
vertical installation	
— up to 30 °C, max.	8 A
— up to 40 °C, max.	6 A
— up to 50 °C, max.	4 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	

Diagnostic alarm	Yes		
Diagnoses			
- Monitoring the supply voltage - Wire break - Short-circuit - Group error	Yes Yes; module-wise Yes; module-wise Yes		
Diagnostics indication LED			
- Monitoring of the supply voltage (PWR-LED) - Channel status display - for channel diagnostics - for module diagnostics	Yes; green PWR LED Yes; green LED No Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
- between the channels - between the channels and backplane bus - between the channels and the power supply of the electronics	No Yes No		
Isolation			
Isolation tested with	707 V DC (type test)		
Standards, approvals, certificates			
Suitable for safety functions	No		
Suitable for safety-related tripping of standard modules	Yes; see FAQ Entry ID: 39198632		
Ecological footprint			
environmental product declaration	Yes		
Global warming potential			
— global warming potential, (total) [CO2 eq] — global warming potential, (during production) [CO2 eq] — global warming potential, (during operation) [CO2 eq] — global warming potential, (after end of life cycle) [CO2 eq]	29.3 kg 3.98 kg 25.6 kg -0.245 kg		
Highest safety class achievable in safety mode			
- Performance level according to ISO 13849-1 - SIL acc. to IEC 61508	PL d SIL 2		
Ambient conditions			
Ambient temperature during operation			
- horizontal installation, min. - horizontal installation, max. - vertical installation, min. - vertical installation, max.	-30 °C; < 0 °C as of FS08 60 °C -30 °C; < 0 °C as of FS08 50 °C		
Altitude during operation relating to sea level			
Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual		
Dimensions			
Width	15 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	30 g		
Classifications			
		Version	Classification
	eClass	16	27-24-26-04
	eClass	14	27-24-26-04
	eClass	12	27-24-26-04
	eClass	9.1	27-24-26-04
	eClass	9	27-24-26-04
	eClass	8	27-24-26-04
	eClass	7.1	27-24-26-04

eClass	6	27-24-26-04
ETIM	10	EC001599
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599
IDEA	4	3566
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Miscellaneous](#) [Manufacturer Declaration](#)



General Product Approval	Maritime application	Environment
--------------------------	----------------------	-------------



[China RoHS](#)



last modified: 3/10/2026