



Figure similar

*** spare part *** SIMATIC DP, ET 200eco PN, 8 DO 24 V DC/2 A; 8xM12, degree of protection IP67

General information	
Vendor identification (VendorID)	002AH
Device identifier (DeviceID)	0306H
Supply voltage	
Rated value (DC)	24 V
Reverse polarity protection	Yes
power supply according to NEC Class 2 required	Yes
Load voltage 1L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes
Load voltage 2L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes
Input current	
Current consumption, typ.	100 mA
from supply voltage 1L+, max.	4 A
from load voltage 1L+ (unswitched voltage)	4 A
from load voltage 2L+, max.	4 A
Power loss	
Power loss, typ.	5 W
Digital outputs	
Number of digital outputs	8
• in groups of	4
Short-circuit protection	Yes
• Response threshold, typ.	2.8 A
Limitation of inductive shutdown voltage to	Typ. (L1+, L2+) -47 V
Controlling a digital input	Yes
Switching capacity of the outputs	
• on lamp load, max.	10 W
Output current	
• for signal "1" rated value	2 A
• for signal "0" residual current, max.	1.5 mA
Parallel switching of two outputs	
• for uprating	No

• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	0.5 Hz
• on lamp load, max.	1 Hz
Total current of the outputs (per group)	
all mounting positions	
— up to 60 °C, max.	3.9 A
Cable length	
• unshielded, max.	30 m
Interfaces	
Transmission procedure	100BASE-TX
Number of PROFINET interfaces	1
1. Interface	
Interface types	
• integrated switch	Yes
PROFINET IO Device	
Services	
— IRT with the option "high flexibility"	Yes
— Prioritized startup	Yes
Interface types	
M12 port	
• Autonegotiation	Yes
• Autocrossing	Yes
• Transmission rate, max.	100 Mbit/s
Protocols	
PROFINET IO	Yes
PROFINET CBA	No
PROFIsafe	No
Redundancy mode	
Media redundancy	
— MRP	Yes
Open IE communication	
• TCP/IP	No
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
• ping	Yes
• ARP	Yes
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes; green "ON" LED
• Wire-break in actuator cable	Yes
• Short-circuit	Yes
• Group error	Yes; Red/yellow "SF/MT" LED
Potential separation	
between the load voltages	Yes
between load voltage and all other switching components	No
between Ethernet and electronics	Yes
Potential separation channels	
• between the channels	No
Isolation	
tested with	
• 24 V DC circuits	707 V DC (type test)

• Test voltage for interface, rms value [Vrms]	1 500 V; According to IEEE 802.3
Degree and class of protection	
IP degree of protection	IP65/67
Standards, approvals, certificates	
Suitable for safety-related tripping of standard modules	Yes
Highest safety class achievable for safety-related tripping of standard modules	
• Performance level according to ISO 13849-1	PL d
• Category according to ISO 13849-1	Cat. 3
• SIL acc. to IEC 62061	SIL 2
• remark on safety-oriented shutdown	https://support.industry.siemens.com/cs/de/en/view/39198632
Use in hazardous areas	
• Explosion protection category for gas	ATEX II 3G Ex nA II T4
• Explosion protection category for dust	ATEX II 3D Ex tc IIIC T90°C Dc
Connection method	
Design of electrical connection	4/5-pin M12 circular connectors
Dimensions	
Width	60 mm
Height	175 mm
Depth	49 mm
Weights	
Weight, approx.	910 g
Classifications	

	Version	Classification
eClass	16	27-24-26-04
eClass	14	27-24-26-04
eClass	12	27-24-26-04
eClass	9.1	27-24-26-04
eClass	9	27-24-26-04
eClass	8	27-24-26-04
eClass	7.1	27-24-26-04
eClass	6	27-24-26-04
ETIM	10	EC001599
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599
IDEA	4	3566
UNSPSC	15	32-15-17-05

Approvals / Certificates	
General Product Approval	

[Miscellaneous](#)

[Manufacturer Declaration](#)



General Product Approval	EMV	For use in hazardous locations
---------------------------------	------------	---------------------------------------



[China RoHS](#)



For use in hazardous locations	Maritime application
---------------------------------------	-----------------------------

[CCC-Ex](#)



[Miscellaneous](#)

[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)

Industrial Communication

[PROFINET](#)

last modified:

10/23/2025