SIEMENS

Data sheet 6ES7155-6AA02-0BN0

Figure similar

SIMATIC ET 200SP, bundle PROFINET interface module IM 155-6 PN ST, max. 32 I/O modules, and 16 ET 200AL modules, multi hot swap, optional PN strain relief, PN security class 1, bundle consists of: interface module (6ES7155-6AU02-0BN0), server module (6ES7193-6PA00-0AA0), SIMATIC bus adapter BA 2x RJ45 (6ES7193-6AR00-0AA0)

General information	
Product type designation	IM 155-6 PN ST incl. BA 2x RJ45 and server module
Firmware version	V6.4.0
● FW update possible	Yes
Vendor identification (VendorID)	002AH
Device identifier (DeviceID)	0313H
Manufacturer ID according to ODVA (VendorID)	04E3H
Device ID according to ODVA (Product code)	0FA2H
Product function	
● I&M data	Yes; I&M0 to I&M4
● Module swapping during operation (hot swapping)	Yes; Multi-hot swapping
● Isochronous mode	No
● IRT	Yes
● Local coupling, IO data	Yes
— Number of coupling modules	6; 1x output + max. 5x input
Engineering with	
● STEP 7 TIA Portal configurable/integrated from version	V20
● STEP 7 configurable/integrated from version	V5.7 SP3
● PROFINET from GSD version/GSD revision	GSDML V2.45
Configuration control	
via dataset	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Short-circuit protection	Yes
Mains buffering	
● Mains/voltage failure stored energy time	10 ms
Input current	
Current consumption (rated value)	350 mA
Current consumption, max.	450 mA
Inrush current, max.	1 A
I^2t	0.05 $A^2 \cdot s$
Power loss	
Power loss, typ.	1.8 W
Address area	
Address space per module	

Subject to change without notice
© Copyright Siemens

● Address space per module, max.	288 byte; For input and output data respectively
Address space per station	
● Address space per station, max.	1 440 byte
Hardware configuration	
Rack	
● Quantity of operable ET 200SP modules, max.	32
● Quantity of operable ET 200AL modules, max.	16
Submodules	
● Number of submodules per station, max.	256
Interfaces	
Transmission procedure	100BASE-TX
Number of PROFINET interfaces	1; 2 ports (switch)
1. Interface	
Interface types	
● RJ 45 (Ethernet)	Yes; with BusAdapter
● Number of ports	2; with BusAdapter
● integrated switch	Yes
● BusAdapter (PROFINET)	Yes; BA 2x RJ45, BA 2x FC, BA 2x M12
Protocols	
● PROFINET IO device	Yes
● Open IE communication	Yes
● Media redundancy	Yes; PROFINET MRP client
PROFINET IO Device	
Services	
— IRT	Yes; 1 ms to 4 ms at an interval of 125 µs
— Dynamic Frame Packing (DFP)	Yes
— Fast Forwarding	Yes
— Fragmentation	Yes
— PROFIenergy	Yes
— Prioritized startup	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	4
Interface types	
RJ 45 (Ethernet)	
● Transmission procedure	PROFINET with 100 Mbit/s full duplex (100BASE-TX)
● 100 Mbps	Yes
● Autonegotiation	Yes
● Autocrossing	Yes
Protocols	
Supports protocol for PROFINET IO	Yes
PROFIsafe	Yes
PROFIBUS	No
EtherNet/IP	No
Modbus TCP	No
Redundancy mode	
● PROFINET system redundancy (S2)	No
● PROFINET system redundancy (R1)	No
Media redundancy	
— MRP	Yes
— MRPD	Yes
Open IE communication	
● TCP/IP	Yes
● UDP	Yes
● SNMP	Yes
● LLDP	Yes
● ARP	Yes
● IGMP	Yes
● Multicast	Yes
● Broadcast	Yes

Subject to change without notice
© Copyright Siemens

● IPv4	Yes
● IPv6	No
Interrupts/diagnostics/status information	
Status indicator	Yes
Alarms	Yes
Diagnostics function	Yes
Diagnostics indication LED	
● RUN LED	Yes; green LED
● ERROR LED	Yes; red LED
● MAINT LED	Yes; Yellow LED
● Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
● Connection display LINK TX/RX	Yes; 2x green link LEDs on BusAdapter
Potential separation	
between backplane bus and electronics	No
between PROFINET and all other circuits	Yes; 1500 V AC (type test)
between supply and all other circuits	No
Permissible potential difference	
between different circuits	Safety extra low voltage SELV
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Network loading class	3
Security	
PROFINET Security Class	1
signed firmware update	Yes
Secure Boot	No
safely removing data	Yes
data integrity	Yes
Ambient conditions	
Ambient temperature during operation	
● horizontal installation, min.	-30 °C; No condensation
● horizontal installation, max.	60 °C
● vertical installation, min.	-30 °C; No condensation
● vertical installation, max.	50 °C
Altitude during operation relating to sea level	
● Installation altitude above sea level, max.	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual
Absolute humidity	
● dew point, min.	-60 °C; suitable for dry room applications
Connection method	
ET-Connection	
● via BU/BA Send	Yes; + 16 ET 200AL modules
Mechanics/material	
Strain relief	Yes; Optional
Dimensions	
Width	50 mm
Height	117 mm
Depth	74 mm
Weights	
Weight, approx.	120 g; without BusAdapter
Classifications	

	Version	Classification
eClass	16	27-24-26-08
eClass	14	27-24-26-08
eClass	12	27-24-26-08
eClass	9.1	27-24-26-08
eClass	9	27-24-26-08

© Copyright Siemens

eClass	8	27-24-26-08
eClass	7.1	27-24-26-08
eClass	6	27-24-26-08
ETIM	10	EC001604
ETIM	9	EC001604
ETIM	8	EC001604
ETIM	7	EC001604

Approvals / Certificates

General Product Approval

Manufacturer Declaration

Miscellaneous

China RoHS

General Product Approval

Maritime application

last modified: 6/18/2026

Subject to change without notice
© Copyright Siemens