

product type designation

product description



PROFIBUS connector

PROFIBUS bus connector, RS 485, Fast Connect, with programming port, 90°

SIMATIC DP, Connection plug for PROFIBUS up to 12 Mbit/s 90° cable outlet, 15.8x 72.2x 36.4 mm (WxHxD), Insulation displacement method FastConnect, With PG receptacle

product brand name

SIMATIC

Technical Product Detail Page

<https://i.siemens.com/1P6ES7972-0BB70-0XA0>

suitability for use

for connecting PROFIBUS stations to the PROFIBUS bus cable

transfer rate

transfer rate / with PROFIBUS DP

9.6 kbit/s ... 12 Mbit/s

interfaces

number of electrical connections

- for PROFIBUS cables

2

- for network components or terminal equipment

1

type of electrical connection

- for PROFIBUS cables

Integrated insulation displacement terminals for 2-core PB FC installation cables

- for network components or terminal equipment

9-pin sub D connector

type of electrical connection / FastConnect

Yes

mechanical data

design of terminating resistor

Resistor combination integrated and connectable via slide switch

material / of the enclosure

plastic

locking mechanism design

Screwed joint

design, dimensions and weights

type of cable outlet

90 degree cable outlet

width

15.8 mm

height

72 mm

depth

36.4 mm

net weight

45 g

ambient conditions

ambient temperature

- during operation
- during storage
- during transport

-25 ... +60 °C
-40 ... +70 °C
-40 ... +70 °C

protection class IP

IP20

product features, product functions, product components / general

product feature

- silicon-free

Yes

product component

- PG connection socket
- strain relief

Yes
Yes

standards, specifications, approvals

certificate of suitability	
• RoHS conformity • UL approval	Yes Yes
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)
Approvals / Certificates	
General Product Approval	
Miscellaneous	 EG-Konf.  Manufacturer Declaration  CCC  RCM
General Product Approval	EMV
For use in hazardous locations	For use in hazardous locations
 China RoHS Manufacturer Declaration  RCM  ATEX FM	
For use in hazardous locations	
 UL FM  ATEX  IECEx Type Examination Certificate CCC-Ex	
Maritime application	
 LRS	

last modified:

3/10/2026 