



SCALANCE X204RNA EEC; redundant network access 2x 100 Mbit/s RJ45 ports; 2x 100 Mbit/s combo ports; LED diagnostics; error signaling contact with set pushbutton; simple power supply; network management; including electronic manual on CD-ROM, C-PLUG optional for PRP network

product type designation	
product brand name	SCALANCE
product type designation	X204RNA EEC
Technical Product Detail Page	https://l.siemens.com/1P6GK5204-0BS00-3LA3
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	2
number of combo ports / with RJ45 interface for optical plug-in transceiver	2
interfaces / other	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	3-pole terminal block
• for power supply	3-pole terminal block
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at AC / rated value	230 V
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at AC / maximum	0.1 A
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	6 W
• supply voltage / 1 / voltage range	85 ... 276
• consumed current / 1 / maximum	0.25 A
• type of electrical connection / 1 / for power supply	3-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	1,25 A
type of voltage / 2 / of the supply voltage	AC
• supply voltage / 2 / voltage range	85 ... 276
ambient conditions	

ambient temperature	
- during operation - during storage - during transport - note	-40 ... +70 °C -40 ... +70 °C -40 ... +70 °C A maximum operating temperature of +85 °C is permissible for a duration of 16 hours
relative humidity	
at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	70 mm
height	147 mm
depth	123 mm
net weight	0.78 kg
product feature / conformal coating	Yes
fastening method	
35 mm DIN-rail mounting - wall mounting - S7-300 rail mounting - S7-1500 rail mounting	Yes No No No
product functions / management, configuration, engineering	
product function	
- CLI - web-based management - MIB support - TRAPs via email - configuration with STEP 7 - port mirroring - multiport mirroring - with IRT / PROFINET IO switch - PROFINET IO diagnosis - switch-managed	Yes Yes Yes Yes No No No No No No
protocol / is supported	
- Telnet - HTTP - HTTPS - TFTP - FTP - BOOTP - GMRP - DCP - LLDP - SNMP v1 - SNMP v2 - SNMP v3 - IGMP (snooping/querier)	No Yes Yes No No No No Yes No Yes Yes Yes No
identification & maintenance function	
- I&M0 - device-specific information - I&M1 - higher level designation/location designation	Yes Yes
product functions / diagnostics	
product function	
- port diagnostics - statistics Packet Size - statistics packet type - error statistics	Yes Yes Yes Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	No

product function	
• media redundancy protocol (MRP) with redundancy manager	No
• ring redundancy	No
• high speed redundancy protocol (HRP) with redundancy manager	No
• high speed redundancy protocol (HRP) with standby redundancy	No
• High-availability Seamless Redundancy (HSR)	No
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	Yes
• High-availability Seamless Redundancy (HSR) and Parallel Redundancy Protocol (PRP) coupling	No
• passive listening	No
product functions / security	
protocol / is supported	
• SSH	Yes
product functions / time	
product function	
• SICLOCK support	No
protocol / is supported	
• NTP	No
• SNTP	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UKCA marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC	IEC 61850, IEEE 1613
• for EMC interference emission	EN 61000-6-4:2001 (Class A)
• for immunity to EMC	EN 61000-6-4:2001
• for safety / from CSA and UL	UL 508 E85972, CSA C22.2 no. 142-M1987
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50155	Yes
• railway application in accordance with EN 50121-4	Yes
• railway application in accordance with EN 50124-1	No
• fire protection in accordance with EN 45545-2	Yes
• IEC 61850-3	Yes
• IEEE 1613	Yes
• RoHS conformity	Yes
standards, specifications, approvals / marine classification	
Marine classification association	
• Royal Institution of Naval Architects (RINA)	Yes
product functions / general	
MTBF	67.64 a
warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAX-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)

General Product Approval

EMV

For use in hazardous locations

[Manufacturer Declaration](#)

[Miscellaneous](#)



[China RoHS](#)



[FM](#)

Test Certificates

Maritime application

[Type Test Certificates/Test Report](#)



[NK / Nippon Kaiji Kyokai](#)

Maritime application

Railway



[Confirmation](#)

last modified:

4/23/2026