



SCALANCE XC208EEC manageable Layer 2 IE switch; IEC 62443-4-2 certified; 8x 10/100 Mbit/s RJ45 ports; 1x console port; diagnostics LED; redundant power supply; with painted printed-circuit boards; NAMUR NE21-compliant; temperature range -40 °C to +70 °C; assembly: DIN rail/S7 mounting rail/wall; redundancy functions; Office; features (RSTP, VLAN,...); PROFINET IO device; Ethernet/IP-compliant; C-PLUG slot;

product type designation	
product brand name	SCALANCE
product type designation	XC208EEC
Technical Product Detail Page	https://i.siemens.com/1P6GK5208-0BA00-2FC2
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	8; RJ45
number of 10/100/1000 Mbit/s RJ45 ports	
• with securing collar	8
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	4.2 W
• consumed current / 1 / at rated supply voltage / maximum	0.175 A
• supply voltage / 1 / voltage range	9.6 ... 31.2
• consumed current / 1 / maximum	0.35 A
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	2,5 A / 125 V
ambient conditions	
ambient temperature	

- during operation - during storage - during transport	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C
relative humidity at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	60 mm
height	147 mm
depth	125 mm
net weight	0.52 kg
product feature / conformal coating	Yes
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method 35 mm DIN-rail mounting - wall mounting - S7-300 rail mounting - S7-1500 rail mounting	Yes Yes Yes Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <~0.3\~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function QoS according to DSCP	Yes
product feature - Cut Through switching method - Store & Forward switching method	No Yes
product functions / management, configuration, engineering	
product function - CLI - web-based management - MIB support - TRAPs via email - configuration with STEP 7 - RMON - SMTP server - port mirroring - multiport mirroring - CoS - PROFINET IO diagnosis - switch-managed	Yes Yes Yes Yes Yes Yes No Yes Yes Yes Yes Yes
PROFINET conformity class	B
telegram length / for Ethernet / maximum	1632 byte
protocol / is supported - Telnet - HTTP - HTTPS - TFTP - SFTP - BOOTP - GMRP - DCP - LLDP - EtherNet/IP - SNMP v1 - SNMP v2 - SNMP v3	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes

IGMP (snooping/querier)	Yes
identification & maintenance function	
I&M0 - device-specific information	Yes
I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
port diagnostics	Yes
statistics Packet Size	Yes
statistics packet type	Yes
error statistics	Yes
SysLog	Yes
product functions / VLAN	
product function	
VLAN - port based	Yes
VLAN - protocol-based	No
VLAN - IP-based	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
product functions / DHCP	
product function	
DHCP server	Yes
DHCP client	Yes
DHCP Option 82	Yes
DHCP Option 66	Yes
DHCP Option 67	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
media redundancy protocol (MRP) with redundancy manager	Yes
Media Redundancy Protocol Interconnection (MRP-I)	Yes; LC mode
of the PROFINET IO device / is supported / H-Sync forwarding	Yes
of the PROFINET IO device / is supported / PROFINET system redundancy	Yes
ring redundancy	Yes
high speed redundancy protocol (HRP) with redundancy manager	Yes
high speed redundancy protocol (HRP) with standby redundancy	Yes
redundancy procedure STP	Yes
redundancy procedure RSTP	Yes
redundancy procedure RSTP+	Yes
redundancy procedure MSTP	Yes
Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
passive listening	Yes
protocol / is supported	
LACP	Yes
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	Yes
product functions / security	
product function	
IEEE 802.1x (radius)	Yes
RADIUS client	Yes
broadcast/multicast/unicast limiter	Yes
broadcast blocking	Yes

protocol / is supported	
• SSH	Yes
• SSL	Yes
product functions / time	
product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
product conformity / according to EMC-guideline	2014/30/EU
standard	
• for EMC interference emission	EN 61000-6-4, EN 50121-4
• for immunity to EMC	EN 61000-6-2, EN 50121-4
• for safety / from CSA and UL	UL 60950-1 E115352, UL-61010-2 E85972
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50121-4	Yes
• RoHS conformity	Yes
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
standards, specifications, approvals / marine classification	
certificate of suitability / shipbuilding approval / note	Certifications marked 'No' are currently under renewal.
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	No
• Chinese Classification Society (CCS)	No
• Det Norske Veritas (DNV)	Yes
• Korean Register of Shipping (KRS)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	No
• Royal Institution of Naval Architects (RINA)	No
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	135.69999 kg
• during manufacturing	26.3 kg
• during operation	109 kg
• after end of life	0.4 kg
product functions / general	
MTBF	48 a
warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022

further information / internet links

internet link

- to website: Selection guide for cables and connectors
- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to web page: SiePortal
- to website: Image database
- to website: CAx-Download-Manager
- to website: Industry Online Support

<https://support.industry.siemens.com/cs/ww/en/view/109766358>
<https://www.siemens.com/tstcloud>
<https://www.siemens.com/simatic-net>
<https://sieportal.siemens.com/>
<https://www.automation.siemens.com/bilddb>
<https://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

Environmental Product Declaration

• global warming potential [CO2 eq] / during manufacturing	26.3 kg
• global warming potential [CO2 eq] / during operation	109 kg
• global warming potential [CO2 eq] / after end of life	0.4 kg
• global warming potential [CO2 eq] / total	135.7 kg

Environment

General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)



General Product Approval

[Miscellaneous](#)

[Declaration of Conformity](#)



[TUEV](#)



[China RoHS](#)

General Product Approval

EMV

For use in hazardous locations



[FM](#)

[CCC-Ex](#)

Maritime application

Industrial Communication



[NK / Nippon Kaiji Kyokai](#)

[PROFINET](#)

